

N-Channel 60 V (D-S) MOSFET



FEATURES


- TrenchFET® Gen IV power MOSFET
- Very low $R_{DS(on)}$ - Q_g figure-of-merit (FOM)
- Tuned for the lowest $R_{DS(on)}$ - Q_{oss} FOM
- 100 % R_g and UIS tested
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- Synchronous rectification
- Primary side switch
- DC/DC converter
- Solar micro inverter
- Motor drive switch
- Battery and load switch
- Industrial



N-Channel MOSFET

PRODUCT SUMMARY

V_{DS} (V)	60
$R_{DS(on)}$ max. (Ω) at $V_{GS} = 10$ V	0.00175
$R_{DS(on)}$ max. (Ω) at $V_{GS} = 7.5$ V	0.00240
$R_{DS(on)}$ max. (Ω) at $V_{GS} = 6$ V	0.00340
Q_g typ. (nC)	42.5
I_D (A)	165
Configuration	Single

ORDERING INFORMATION

Package	PowerPAK SO-8
Lead (Pb)-free and halogen-free	SiR626ADP-T1-RE3

ABSOLUTE MAXIMUM RATINGS ($T_A = 25$ °C, unless otherwise noted)

PARAMETER	SYMBOL	LIMIT	UNIT	
Drain-source voltage	V_{DS}	60	V	
Gate-source voltage	V_{GS}	± 20		
Continuous drain current ($T_J = 150$ °C)	I_D	$T_C = 25$ °C	165	
		$T_C = 70$ °C	132	
		$T_A = 25$ °C	40.4 ^{b, c}	
		$T_A = 70$ °C	32.4 ^{b, c}	
Pulsed drain current ($t = 100$ μ s)	I_{DM}	300	A	
Continuous source-drain diode current	I_S	$T_C = 25$ °C		100 ^a
		$T_A = 25$ °C		5.6 ^{b, c}
Single pulse avalanche current	I_{AS}	50		mJ
Single pulse avalanche energy	E_{AS}	125		
Maximum power dissipation	P_D	$T_C = 25$ °C	104	
		$T_C = 70$ °C	66.6	
		$T_A = 25$ °C	6.25 ^{b, c}	
		$T_A = 70$ °C	4 ^{b, c}	
Operating junction and storage temperature range	T_J, T_{stg}	-55 to +150	°C	
Soldering recommendations (peak temperature) ^c		260		

Notes

- Package limited
- Surface mounted on 1" x 1" FR4 board
- $t = 10$ s



THERMAL RESISTANCE RATINGS						
PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT	
Maximum junction-to-ambient ^a	$t \leq 10$ s	R_{thJA}	15	20	°C/W	
Maximum junction-to-case (drain)	Steady state	R_{thJC}	0.9	1.2		

Notes

a. Surface mounted on 1" x 1" FR4 board


SPECIFICATIONS ($T_J = 25$ °C, unless otherwise noted)							
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT	
Static							
Drain-source breakdown voltage	V_{DS}	$V_{GS} = 0$ V, $I_D = 250$ μ A	60	-	-	V	
V_{DS} temperature coefficient	$\Delta V_{DS}/T_J$	$I_D = 1$ mA	-	32	-	mV/°C	
$V_{GS(th)}$ temperature coefficient	$\Delta V_{GS(th)}/T_J$	$I_D = 250$ μ A	-	-7.8	-	mV/°C	
Gate-source threshold voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}$, $I_D = 250$ μ A	2	-	3.5	V	
Gate-source leakage	I_{GSS}	$V_{DS} = 0$ V, $V_{GS} = \pm 20$ V	-	-	100	nA	
Zero gate voltage drain current	I_{DSS}	$V_{DS} = 60$ V, $V_{GS} = 0$ V	-	-	1	μ A	
		$V_{DS} = 60$ V, $V_{GS} = 0$ V, $T_J = 70$ °C	-	-	15		
On-state drain current ^a	$I_{D(on)}$	$V_{DS} \geq 10$ V, $V_{GS} = 10$ V	40	-	-	A	
Drain-source on-state resistance ^a	$R_{DS(on)}$	$V_{GS} = 10$ V, $I_D = 20$ A	-	0.00145	0.00175	Ω	
		$V_{GS} = 7.5$ V, $I_D = 20$ A	-	0.00190	0.00240		
		$V_{GS} = 6$ V, $I_D = 20$ A	-	0.00260	0.00340		
Forward transconductance ^a	g_{fs}	$V_{DS} = 15$ V, $I_D = 20$ A	-	84	-	S	
Dynamic ^b							
Input capacitance	C_{iss}	$V_{DS} = 30$ V, $V_{GS} = 0$ V, $f = 1$ MHz	-	3770	-	pF	
Output capacitance	C_{oss}		-	1370	-		
Reverse transfer capacitance	C_{rss}		-	40	-		
Total gate charge	Q_g	$V_{DS} = 30$ V, $V_{GS} = 10$ V, $I_D = 20$ A	-	55	83	nC	
Gate-source charge	Q_{gs}	$V_{DS} = 30$ V, $V_{GS} = 7.5$ V, $I_D = 20$ A	-	42.5	64		
Gate-drain charge	Q_{gd}		-	16.7	-		
Output charge	Q_{oss}		$V_{DS} = 30$ V, $V_{GS} = 0$ V	-	88.5		-
Gate resistance	R_g		$f = 1$ MHz	0.3	0.9		1.6
Turn-on delay time	$t_{d(on)}$	$V_{DD} = 30$ V, $R_L = 1.5$ Ω , $I_D \cong 20$ A, $V_{GEN} = 10$ V, $R_g = 1$ Ω	-	16	32	ns	
Rise time	t_r		-	10	20		
Turn-off delay time	$t_{d(off)}$		-	30	60		
Fall time	t_f		-	10	20		
Turn-on delay time	$t_{d(on)}$	$V_{DD} = 30$ V, $R_L = 1.5$ Ω , $I_D \cong 20$ A, $V_{GEN} = 7.5$ V, $R_g = 1$ Ω	-	20	40		
Rise time	t_r		-	20	40		
Turn-off delay time	$t_{d(off)}$		-	27	54		
Fall time	t_f		-	12	24		
Drain-Source Body Diode Characteristics							
Continuous source-drain diode current	I_S	$T_C = 25$ °C	-	-	100	A	
Pulse diode forward current	I_{SM}		-	-	300		
Body diode voltage	V_{SD}	$I_S = 5$ A, $V_{GS} = 0$ V	-	0.7	1.1	V	
Body diode reverse recovery time	t_{rr}	$I_F = 20$ A, $di/dt = 100$ A/ μ s, $T_J = 25$ °C	-	52	104	ns	
Body diode reverse recovery charge	Q_{rr}		-	50	100	nC	
Reverse recovery fall time	t_a		-	25	-	ns	
Reverse recovery rise time	t_b		-	27	-		

Notes


- a. Pulse test; pulse width ≤ 300 μ s, duty cycle ≤ 2 %
b. Guaranteed by design, not subject to production testing

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current and Gate Voltage



Capacitance




Gate Charge




On-Resistance vs. Junction Temperature




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage




Threshold Voltage



On-Resistance vs. Gate-to-Source Voltage



Single Pulse Power, Junction-to-Ambient




Safe Operating Area, Junction-to-Ambient

Note


a. $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified




TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Current Derating ^a



Power, Junction-to-Case




Power, Junction-to-Ambient

Note


- a. The power dissipation P_D is based on T_J max. = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?77248.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.