

## R-C Thermal Model Parameters

### DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in PSpice, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the PSpice simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the PSpice Platform".

### R-C THERMAL MODEL FOR TANK CONFIGURATION



R-C VALUES FOR TANK CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RT1	2.9266	917.2687m	n/a
RT2	17.0404	387.4991m	n/a
RT3	9.2255	91.2298m	n/a
RT4	38.8075	804.0024m	n/a
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CT1	10.5538m	48.3596m	n/a
CT2	666.3130m	6.5279m	n/a
CT3	81.2192m	151.4566u	n/a
CT4	2.9412	48.2011m	n/a


#### Note

- n/a indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.



R-C THERMAL MODEL FOR FILTER CONFIGURATION



R-C VALUES FOR FILTER CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RF1	1.7089	337.0464m	n/a
RF2	11.1144	320.0625m	n/a
RF3	23.4081	592.4403m	n/a
RF4	31.7686	950.8471m	n/a
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CF1	2.6545m	2.4164m	n/a
CF2	41.4401m	3.9506m	n/a
CF3	448.4091m	17.7681m	n/a
CF4	3.0625	5.2287m	n/a

Note

- n/a indicates not applicable

