


Ultra Thin MiniQFN-10L-T0.35 Case Outline



DIM.	MILLIMETERS			INCHES		
	MIN.	NOM.	MAX.	MIN.	NOM.	MAX.
A	0.30	0.35	0.40	0.012	0.014	0.016
A1	0.00	0.02	0.05	0.0000	0.0008	0.0020
A3	0.127 REF			0.005 REF		
b	0.15	0.20	0.25	0.006	0.008	0.010
D	1.80 BSC			0.071 BSC		
e	0.40 BSC			0.016 BSC		
E	1.40 BSC			0.055 BSC		
L	0.35	0.40	0.45	0.014	0.016	0.018
L1	0.45	0.50	0.55	0.018	0.020	0.022
N ⁽³⁾	10			10		
Nd ⁽³⁾	2			2		
Ne ⁽³⁾	3			3		
ECN: T15-0603-Rev. A, 12-Oct-15 DWG: 6045						

Notes

- (1) Use millimeters as the primary measurement.
- (2) Dimensioning and tolerances conform to ASME Y14.5M. - 1994.
- (3) N is the number of terminals, Nd is the number of terminals in X-direction, and Ne is the number of terminals in Y-direction.
- (4) Dimension b applies to plated terminal and is measured between 0.15 mm and 0.30 mm from terminal tip.
- (5) The pin #1 identifier must be existed on the top surface of the package by using indentation mark or other feature of package body.
- (6) Package warpage max. 0.05 mm.