


## Multi SMD LED RGB



### DESCRIPTION

The VLMRGB1500... is a high brightness tricolor LED designed primarily for RGB displays and backlights. It is using the popular PCB based 0404 SMD package with 120° emission characteristic. The 4 pin package with common anode allows individual driving of each chip and thus a gapless coverage of a wide color space by additive color mixing. It provides high reliability in a temperature range from -40 °C to +85 °C, using highly suitable blue light stable package materials.

### PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: SMD 0404, 4 pin
- Product series: RGB
- Angle of half intensity:  $\pm 60^\circ$

### FEATURES

- Utilizing high brightness AlInGaP and InGaN chip technologies
- 4 pin RGB SMD LED package allows individual control the driving current of each chip
- Compact package outline dimensions (L x W x H in mm): 1.0 x 1.0 x 0.65
- Qualified according to JEDEC® moisture sensitivity level 3
- Compatible to IR reflow soldering
- Operation temperature range: -40 °C to +85 °C
- ESD-withstand voltage: up to 2 kV for red and 1 kV for blue and green according to JESD22-A114-B
- Luminous intensities and colors categorized per reel
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



### APPLICATIONS

- Telecommunication, office equipment, home appliances, industrial equipment, white goods
- Wide range of accent and decorative lighting
- Displays: full color message and displays video boards
- Keyboard backlighting
- Status indicator
- Signal and symbol illumination

### PARTS TABLE

PART	COLOR	LUMINOUS INTENSITY (mcd)			at I <sub>F</sub> (mA)	WAVELENGTH (nm)			at I <sub>F</sub> (mA)	FORWARD VOLTAGE (V)			at I <sub>F</sub> (mA)	TECHNOLOGY
		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		
		VLMRGB1500-GS08	Red	26		-	65	5		616	-	628		
	True green	122	-	303	5	519	-	537	5	2.0	-	3.2	5	InGaN
	Blue	22	-	66	5	464	-	479	5	2.0	-	3.2	5	InGaN

#### Note

- Measurement accuracy:  $\pm 11\%$  for luminous intensity,  $\pm 1$  nm for dominant wavelength,  $\pm 0.1$  V for forward voltage



<b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)				
<b>VLMRGB1500, RED</b>				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Forward current		$I_F$	25	mA
Power dissipation		$P_{tot}$	62	mW
Junction temperature		$T_j$	95	$^{\circ}\text{C}$
Peak forward current	$t_p < 100\text{ }\mu\text{s}$ , duty cycle = 0.1	$I_{FM}$	60	mA
Thermal resistance junction-to-solder point, 1 chip		$R_{thJP}$	300	K/W
Thermal resistance junction-to-ambient, 1 chip	Mounted on FR4 PC board ( $t = 1.6\text{ mm}$ ) with Cu pad size $> 16\text{ mm}^2$	$R_{thJA}$	500	K/W
Operating temperature		$T_{amb}$	-40 to +85	$^{\circ}\text{C}$
Storage temperature		$T_{stg}$	-40 to +90	$^{\circ}\text{C}$
ESD voltage	HBM	$V_{ESD}$	2000	V

<b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)				
<b>VLMRGB1500, TRUE GREEN, BLUE</b>				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Forward current		$I_F$	20	mA
Power dissipation		$P_{tot}$	76	mW
Junction temperature		$T_j$	95	$^{\circ}\text{C}$
Peak forward current	$t_p < 100\text{ }\mu\text{s}$ , duty cycle = 0.1	$I_{FM}$	100	mA
Thermal resistance junction-to-solder point, 1 chip		$R_{thJP}$	300	K/W
Thermal resistance junction-to-ambient, 1 chip	Mounted on FR4 PC board ( $t = 1.6\text{ mm}$ ) with Cu pad size $> 16\text{ mm}^2$	$R_{thJA}$	500	K/W
Operating temperature		$T_{amb}$	-40 to +85	$^{\circ}\text{C}$
Storage temperature		$T_{stg}$	-40 to +90	$^{\circ}\text{C}$
ESD voltage	HBM	$V_{ESD}$	1000	V

<b>OPTICAL AND ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)							
<b>VLMRGB1500, RED, TRUE GREEN, BLUE</b>							
PARAMETER	TEST CONDITION	COLOR	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity	$I_F = 5\text{ mA}$	Red	$I_v$	26	-	65	mcd
		True green		122	-	303	
		Blue		22	-	66	
Dominant wavelength		Red	$\lambda_d$	616	-	628	nm
		True green		519	-	537	
		Blue		464	-	479	
Peak wavelength		Red	$\lambda_p$	-	632	-	nm
		True green		-	518	-	
		Blue		-	468	-	
Spectral half width at 50 % $I_{rel}$ max.	Red	$\Delta\lambda_{0.5}$	-	12	-	nm	
	True green		-	27	-		
	Blue		-	20	-		
Angle of half intensity	Red	$\phi$	-	$\pm 60$	-	$^{\circ}$	
	True green		-	$\pm 60$	-		
	Blue		-	$\pm 60$	-		
Forward voltage	Red	$V_F$	1.5	-	2.15	V	
	True green		2.0	-	3.2		
	Blue		2.0	-	3.2		
Reverse current <sup>(1)</sup>	$V_R = 5\text{ V}$	Red	$I_R$	-	-	10	$\mu\text{A}$
		True green		-	-	10	
		Blue		-	-	10	

**Notes**

- Not designed for operating in reverse direction.  
Measurement accuracy:  $\pm 11\%$  for luminous intensity,  $\pm 1\text{ nm}$  for dominant wavelength,  $\pm 0.1\text{ V}$  for forward voltage
- (1) Not designed for operating in reverse direction; reverse voltage is only applied for testing purpose; only applied for testing purpose



<b>LUMINOUS INTENSITY</b> (in mcd at 5 mA)						
BIN CODE	RED		TRUE GREEN		BLUE	
	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.
A	26.0	31.0	122.0	146.0	22.0	26.5
B	31.0	37.0	146.0	175.0	26.5	32.0
C	37.0	45.0	175.0	210.0	32.0	38.0
D	45.0	54.0	210.0	252.0	38.0	46.0
E	54.0	65.0	252.0	303.0	46.0	55.0
F	-	-	-	-	55.0	66.0

**Note**

- Tolerance on each luminous intensity bin is  $\pm 11\%$ .  
The above classification represents the brightness range which includes only a few brightness groups.  
Only one luminous intensity group per color will be shipped on each reel (there will be no mixing of two groups on each reel).  
In order to ensure availability, single brightness groups will not be orderable.

<b>DOMINANT WAVELENGTH</b> (in nm at 5 mA)						
BIN CODE	RED		TRUE GREEN		BLUE	
	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.
1	616.0	619.0	519.0	522.0	464.0	467.0
2	619.0	622.0	522.0	525.0	467.0	470.0
3	622.0	625.0	525.0	528.0	470.0	473.0
4	625.0	628.0	528.0	531.0	473.0	476.0
5	-	-	531.0	534.0	476.0	479.0
6	-	-	534.0	537.0	-	-

**Note**

- Tolerance for each dominate wavelength bin is  $\pm 1\text{ nm}$ .  
The above classification represents the wavelength range which includes only a few brightness groups.  
Only one wavelength group per color will be shipped on each reel (there will be no mixing of two groups on each reel).  
In order to ensure availability, single wavelength groups will not be orderable.

**MARKING EXAMPLE FOR SELECTION CODE ON LABEL**

Selection code: BBC/232 (sequence: RGB for both IV and color groups)

- BBC:
  - I<sub>v</sub> group red: B (31 mcd to 37 mcd)
  - I<sub>v</sub> group true green: B (164 mcd to 175 mcd)
  - I<sub>v</sub> group blue: C (32 mcd to 38 mcd)
- 232:
  - LD group red: 2 (619 mcd to 622 nm)
  - LD group true green: 3 (525 mcd to 528 nm)
  - LD group blue: 2 (467 mcd to 470 nm)

**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 2 - Relative Luminous Intensity vs. Angular Displacement




Fig. 5 - Relative Luminous Intensity vs. Forward Current








Fig. 3 - Relative Intensity vs. Wavelength

## PACKAGE DIMENSIONS / SOLDERING PADS DIMENSIONS in millimeters




Not indicated tolerances  $\pm 0.1$

**TAPING DIMENSIONS** in millimeters



Drawing-No.: 9.800-5172.01  
Issue: VK; 18.04.24

QTY per reel: 4000 pcs  
MOQ: 20 000 pcs



REEL DIMENSIONS							
TAPING VERSION	REEL DIMENSIONS IN mm ACCORDING DRAWING REFERENCE						
	A	B	C	D	N	W1	W2
GS08	178 ± 1	2 ± 0.5	13 ± 0.5	4 ± 0.5	60 ± 0.2	9 ± 0.2	12 ± 1

**SOLDERING PROFILE**





Fig. 6 - Vishay Lead (Pb)-free Reflow Soldering Profile According to J-STD-020


**BAR CODE PRODUCT LABEL (example)**



- A. 2D bar code
- B. Vishay part number
- C. Quantity
- D. Selection code (bin): brightness and color groups
- E. Code of manufacturing plant
- F. Termination plating finish
- G. Batch = date code: year / week / plant code
- H. Region code
- I. Internal serial number
- J. Sales location
- K. ESD symbol
- L. Lead (Pb)-free symbol
- M. RoHS symbol, halogen-free symbol
- N. Internal lot numbers

**DRY PACKING**

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



**FINAL PACKING**

The sealed reel is packed into a cardboard box. A secondary cardboard box is used for shipping purposes.

**RECOMMENDED METHOD OF STORAGE**

Dry box storage is recommended as soon as the aluminum bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.


After more than 168 h under these conditions moisture content will be too high for reflow soldering.

In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:  
192 h at 40 °C + 5 °C / - 0 °C and < 5 % RH (dry air / nitrogen) or

96 h at 60 °C + 5 °C and < 5 % RH for all device containers or

24 h at 100 °C + 5 °C not suitable for reel or tubes.

An EIA JEDEC standard JESD22-A112 level 3 label is included on all aluminum dry bags.



Example of JESD22-A112 level 3 label



**ESD PRECAUTION**

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the antistatic shielding bag. Electrostatic sensitive devices warning labels are on the packaging.

**VISHAY SEMICONDUCTORS STANDARD BAR CODE LABELS**

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.