


Highbright 0201 ChipLED



DESCRIPTION

The 0201 ChipLED delivers brilliant illumination in one of the smallest surface-mount formats available. Measuring just 0.65 mm x 0.375 mm x 0.35 mm, it is perfectly suited for space-constrained applications in consumer electronics, wearables, industrial systems, and more. This RoHS-compliant component combines ultra compact dimensions, low power consumption, a wide viewing angle, and multiple color options engineered for seamless integration into automated SMT processes. Offering exceptional versatility and performance, the 0201 ChipLED empowers the next generation of compact, high efficiency electronic designs.

PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: SMD 0201 ChipLED
- Product series: standard
- Angle of half intensity: $\pm 60^\circ$

FEATURES

- Super small ChipLED with high brightness 0.65 x 0.375 x 0.35 (L x W x H in mm)
- High reliability PCB based
- Wavelength:
 - Yellow: 585.5 nm to 594.5 nm
 - Soft orange: 597.5 nm to 609.5 nm
 - Red: 617.5 nm to 633.5 nm
- AllnGaP technology
- Wide viewing angle: 120°
- Grouping parameter: luminous intensity, wavelength and forward voltage
- Available in 8 mm tape on 7" diameter reel
- HBM ESD-withstand voltage: up to 2 kV according to JESD22-A114
- Compatible to IR reflow soldering
- Preconditioning according to JEDEC® level 3
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



APPLICATIONS

- Backlighting for keypads, logos, and buttons in ultra thin devices
- Instrument illumination
- Indicators and backlight for telecommunication equipment, consumer electronics, and white goods
- Displays for industrial control systems
- Next-generation wearables and smart accessories
- General use

PARTS TABLE

PART	COLOR	LUMINOUS INTENSITY (mcd)			at I _F (mA)	WAVELENGTH (nm)			at I _F (mA)	FORWARD VOLTAGE (V)			at I _F (mA)	TECHNOLOGY
		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		
VLMY1700-GS08	Yellow	4.5	-	11.5	2	585.5	-	594.5	2	1.55	-	2.35	2	AllnGaP/GaAs
VLMO1700-GS08	Soft orange	7.2	-	18	2	597.5	-	609.5	2	1.5	-	2.2	2	AllnGaP/GaAs
VLMR1700-GS08	Red	7.2	-	18	2	617.5	-	633.5	2	1.55	-	2.35	2	AllnGaP/GaAs

**ABSOLUTE MAXIMUM RATINGS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)
VLMY170., VLMO170., VLMR170. (AlInGaP technology)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage ⁽¹⁾		V_R	5	V
DC forward current		I_F	25	mA
Surge forward current	1/10 duty cycle, 0.1 ms pulse width	I_{FSM}	50	mA
Power dissipation	$T_{amb} \leq 25\text{ }^{\circ}\text{C}$	P_V	60	mW
Operating temperature range		T_{amb}	-40 to +85	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	-40 to +90	$^{\circ}\text{C}$
ESD withstand voltage	HBM	V_{ESD}	2000	V
Reflow solder conditions	According Vishay specifications	T_{slid}	260	$^{\circ}\text{C}$

Note

⁽¹⁾ Reverse voltage is intended for test purposes only; do not operate the device under reverse bias

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)
VLMY170., YELLOW

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity	$I_F = 2\text{ mA}$	I_V	4.5	-	11.5	mcd
Dominant wavelength	$I_F = 2\text{ mA}$	λ_d	585.5	-	594.5	nm
Peak wavelength	$I_F = 2\text{ mA}$	λ_p	-	591	-	nm
Angle of half intensity	$I_F = 2\text{ mA}$	φ	-	± 60	-	$^{\circ}$
Spectral line half width	$I_F = 2\text{ mA}$	$\Delta\lambda$	-	20	-	nm
Forward voltage	$I_F = 2\text{ mA}$	V_F	1.55	-	2.35	V
Reverse current	$V_R = 5\text{ V}$	I_R	-	-	50	μA

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)
VLMO170., SOFT ORANGE

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity	$I_F = 2\text{ mA}$	I_V	7.2	-	18	mcd
Dominant wavelength	$I_F = 2\text{ mA}$	λ_d	597.5	-	609.5	nm
Peak wavelength	$I_F = 2\text{ mA}$	λ_p	-	610	-	nm
Angle of half intensity	$I_F = 2\text{ mA}$	φ	-	± 60	-	$^{\circ}$
Spectral line half width	$I_F = 2\text{ mA}$	$\Delta\lambda$	-	20	-	nm
Forward voltage	$I_F = 2\text{ mA}$	V_F	1.5	-	2.2	V
Reverse current	$V_R = 5\text{ V}$	I_R	-	-	50	μA

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)
VLMR170., RED

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity	$I_F = 2\text{ mA}$	I_V	7.2	-	18	mcd
Dominant wavelength	$I_F = 2\text{ mA}$	λ_d	617.5	-	633.5	nm
Peak wavelength	$I_F = 2\text{ mA}$	λ_p	-	632	-	nm
Angle of half intensity	$I_F = 2\text{ mA}$	φ	-	± 60	-	$^{\circ}$
Spectral line half width	$I_F = 2\text{ mA}$	$\Delta\lambda$	-	20	-	nm
Forward voltage	$I_F = 2\text{ mA}$	V_F	1.55	-	2.35	V
Reverse current	$V_R = 5\text{ V}$	I_R	-	-	50	μA



LUMINOUS INTENSITY CLASSIFICATION AT 2 mA					
GROUP	LUMINOUS INTENSITY (mcd)		ASSIGNMENT VLM...		
	MIN.	MAX.			
J1	4.5	5.6	Y1700	-	-
J2	5.6	7.2	Y1700	-	-
K1	7.2	9.0	Y1700	O1700	R1700
K2	9.0	11.5	Y1700	O1700	R1700
L1	11.5	14.5	-	O1700	R1700
L2	14.5	18.0	-	O1700	R1700

Note

- Tolerance of luminous intensity: ± 11 %

COLOR CLASSIFICATION AT 2 mA			
COLOR	GROUP	DOMINANT WAVELENGTH (nm)	
		MIN.	MAX.
Yellow	D3	585.5	588.5
	D4	588.5	591.5
	D5	591.5	594.5
Soft orange	D7	597.5	600.5
	D8	600.5	603.5
	D9	603.5	606.5
	D10	606.5	609.5
Red	E4	617.5	621.5
	E5	621.5	625.5
	E6	625.5	629.5
	E7	629.5	633.5

Note

- Tolerance of dominant wavelength: ± 1 nm

Notes

- In order to ensure availability, single groups for luminous intensity, dominant wavelength, and forward voltage will not be orderable
- Only one group for luminous intensity, dominant wavelength, and forward voltage will be shipped in any one reel

FORWARD VOLTAGE CLASSIFICATION AT 2 mA			
COLOR	GROUP	FORWARD VOLTAGE (V)	
		MIN.	MAX.
Yellow	00	1.55	1.75
	0	1.75	1.95
	1	1.95	2.15
	2	2.15	2.35
Soft orange	X	1.50	1.85
	Y	1.85	2.20
Red	1	1.55	1.95
	2	1.95	2.35

Note

- Tolerance of forward voltage: ± 0.05 V


TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 2 - Relative Luminous Intensity vs. Angular Displacement




Fig. 5 - Relative Luminous Intensity vs. Forward Current




Fig. 3 - Relative Intensity vs. Wavelength




Fig. 6 - Change of Dominant Wavelength vs. Forward Current




Fig. 7 - Relative Forward Voltage vs. Ambient Temperature




Fig. 8 - Relative Luminous Intensity vs. Ambient Temperature





Fig. 9 - Change of Dominant Wavelength vs. Ambient Temperature

REEL DIMENSIONS in millimeters



Drawing-No.: 9.800-5172.01

Issue: VK; 18.04.24


DIMENSIONS OF REEL in millimeters (according drawing reference)							
TAPING VERSION	A	B	C	D	N	W1	W2
GS08	$\varnothing 180 \pm 2$	2 ± 0.5	$\varnothing 13 \pm 0.2$	-	$\varnothing 60 + 0 / - 1$	$9 + 0.3 / - 0$	11.4 ± 1

Reels come in quantity of 3000 units.

TAPE DIMENSIONS in millimeters



PACKAGE DIMENSIONS in millimeters



Note

- Suggested pad dimensions for reference only; please modify the pad dimensions based on individual need

SOLDERING PROFILE





Fig. 10 - Vishay Lead (Pb)-free Reflow Soldering Profile (according to J-STD-020C)


BAR CODE PRODUCT LABEL (Example only)



- A. 2D barcode
- B. Part No: Vishay part number
- C. QTY: quantity
- D. SelCode: selection bin code
- E. Country of origin
- F. PTC: product plant code
- G. Termination finish
- H. Region code
- I. Serial#: serial number
- K. Batch Number: year, week, country code, plant code
- L. SL: storage location
- M. Environmental Symbols: RoHS, lead (Pb)-free, halogen-free
- N. Lot numbers

DRY PACKING

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



FINAL PACKING

The sealed reel is packed into a cardboard box. A secondary cardboard box is used for shipping purposes.

RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the aluminum bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.

After more than 168 h under these conditions moisture content will be too high for reflow soldering.

In case of moisture absorption, the devices will recover to the former condition by drying under the condition given in J-STD-033.

A JEDEC J-STD-033 level 3 label is included on all aluminum dry bags.

CAUTION
This bag contains
MOISTURE-SENSITIVE DEVICES

LEVEL (MSL)

3

1. Calculated shelf life in sealed bag: 12 months at < 40°C and < 90% relative humidity (RH)
2. Peak package body temperature: 260°C
3. After bag is opened, devices that will be subjected to reflow solder or other high temperature process must be
 - a) Mounted within **168 h** of factory conditions ≤ 30°C/60%RH, or
 - b) Stored per J-STD-033.
4. Devices require bake before mounting, if:
 - a) Humidity Indicator Card reads >10% for level 2a - 5a devices or > 60% for level 2 devices when read at 23°C ± 5°C
 - b) 3a or 3b are not met
5. If baking is required, refer to IPC/JEDEC J-STD-033 for bake procedure

Bag Seal Date: _____
If blank, see adjacent bar code label

Note: Level (MSL) and body temperature defined by IPC/JEDEC J-STD-020

Example of JEDEC J-STD-033 Level 3 Label



ESD PRECAUTION

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the antistatic shielding bag. Electrostatic sensitive devices warning labels are on the packaging.

**VISHAY SEMICONDUCTORS STANDARD
BAR CODE LABELS**

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.