

1 Form A Solid-State Relay



DESCRIPTION


The VOR1003M4 is an optically isolated 1 form A solid-state relay in a surface-mount 4 pin SOP package. This 1 form A opto-isolated relay comes in a low profile SOP-4 package, but still offers up to 5 A load current making it ideal for high current industrial applications.

FEATURES

- Load voltage 30 V
- Continuous load current = 5 A
- Isolation voltage 3750 V_{RMS}
- Low on resistance R_{ON} = 0.7 Ω (typ.)
- Fast switching:
t_{on} = 1.5 ms (typ.), t_{off} = 0.15 ms (typ.)
- Low leakage current I_{LEAK} < 1 μA (typ.)
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)



APPLICATIONS

- Security systems
- Instrumentation
- Industrial controls

AGENCY APPROVALS

- UL (pending)
- cUL (pending)
- DIN EN 60747-5-5 (VDE 0884-5) (pending)
- CQC (pending)

ORDERING INFORMATION

V	O	R	1	0	0	3	M	4	#
PART NUMBER									TAPE AND REEL



PACKAGE

SOP-4, tape and reel

UL, cUL, CQC, VDE, FIMKO

VOR1003M4T

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)				
PARAMETER	CONDITIONS	SYMBOL	VALUE	UNIT
INPUT				
LED continuous forward current		I_F	50	mA
LED reverse voltage		V_R	5	V
OUTPUT				
DC or peak AC load voltage		V_L	30	V
Continuous load current		I_L	5	A
SSR				
Total power dissipation		P_{diss}	800	mW
Ambient temperature range		T_{amb}	-40 to +85	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	-40 to +110	$^{\circ}\text{C}$
Soldering temperature	$t \leq 10\text{ s max.}$	T_{sld}	260	$^{\circ}\text{C}$

Note

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.

ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
INPUT						
LED forward current, switch turn-on	$I_L = 100\text{ mA}$	I_{Fon}	-	2	5	mA
LED forward current, switch turn-off	$I_L = 1\text{ }\mu\text{A}$	I_{Foff}	0.4	2	-	mA
LED reverse current	$V_R = 5\text{ V}$	I_R	-	-	1	μA
LED forward voltage	$I_F = 10\text{ mA}$	V_F	-	1.2	1.5	V
LED reverse voltage	$I_R = 10\text{ }\mu\text{A}$	V_R	-	5	-	V
OUTPUT						
On-resistance	$I_F = 10\text{ mA}$, $I_L = 2\text{ A}$	R_{ON}	-	0.6	2.6	Ω
Off-state leakage current	$I_F = 0\text{ mA}$, $V_L = 24\text{ V}$	I_{LEAK}	-	0.1	1	μA

Note

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.

SWITCHING CHARACTERISTICS						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Turn-on time	$I_F = 10\text{ mA}$, $R_L = 200\text{ }\Omega$, $V_L = 50\text{ mA}$	t_{on}	-	0.5	3	ms
Turn-off time	$I_F = 10\text{ mA}$, $R_L = 200\text{ }\Omega$, $V_L = 50\text{ mA}$	t_{off}	-	0.1	0.5	ms




Fig. 1 - Timing Schematic

SAFETY AND INSULATION RATINGS				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Climatic classification	According to IEC 68 part 1		40 / 85 / 21	
Pollution degree	According to DIN VDE 0109		2	
Comparative tracking index	Insulation group IIIa	CTI	175	
Maximum rated withstanding isolation voltage	According to UL1577, t = 1 min	V_{ISO}	3750	V_{RMS}
Maximum transient isolation voltage	According to DIN EN 60747-5-5	V_{IOTM}	4800	V_{peak}
Maximum repetitive peak isolation voltage	According to DIN EN 60747-5-5	V_{IORM}	707	V_{peak}
Insulation resistance	$T_{amb} = 25\text{ }^{\circ}\text{C}$, $V_{IO} = 500\text{ V}$	R_{IO}	$\geq 10^{12}$	Ω
	$T_{amb} = 100\text{ }^{\circ}\text{C}$, $V_{IO} = 500\text{ V}$	R_{IO}	$\geq 10^{11}$	Ω
Output safety power		P_{SO}	750	mW
Input safety current		I_{SI}	200	mA
Input safety temperature		T_S	150	$^{\circ}\text{C}$
Clearance distance			≥ 5.2	mm
Creepage distance			≥ 5.2	mm

Note

- This SSR is suitable for “safe electrical insulation” only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.




Fig. 2 - Safety Input Current vs. Ambient Temperature




Fig. 3 - Safety Power Dissipation vs. Ambient Temperature


TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Fig. 4 - Load Current vs. Ambient Temperature




Fig. 7 - Normalized On-Resistance vs. Ambient Temperature




Fig. 5 - Forward Current vs. Forward Voltage




Fig. 8 - Off-State Leakage Current vs. Ambient Temperature




Fig. 6 - Normalized Forward Current for Switch Turn-On vs. Ambient Temperature




Fig. 9 - Turn-On Time vs. Ambient Temperature




Fig. 10 - Turn-On Time vs. Forward Current




Fig. 12 - Turn-Off Time vs. Forward Current




Fig. 11 - Turn-Off Time vs. Ambient Temperature




Fig. 13 - Load Current vs. Load Voltage


PACKAGE DIMENSIONS (in millimeters)


Fig. 14 - Package Drawings



PACKAGE MARKING


Fig. 15 - VOR1003M4


Notes

- YWW = date code
- Tape and reel suffix (T) is not part of the package marking

TAPE AND REEL INFORMATION (in millimeters)

Note:

- Cumulative tolerance of 10 spocket holes is 0.20

Fig. 16 - VOR1003M4T (3000 pieces on reel)

SOLDER PROFILES

Fig. 17 - Lead (Pb)-free Reflow Solder Profile
According to J-STD-020 for SMD Devices

HANDLING AND STORAGE CONDITIONS

ESD level: HBM class 2

Floor life: 168 h

Conditions: $T_{amb} < 30\text{ °C}$, RH < 60 %

Moisture sensitivity level 3, according to J-STD-020



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.