


Side View SMD LED



DESCRIPTION

The VLMB14SV460-01UL is a blue, 457 nm, side looking emitting diode based on InGaN emitter chip technology with extremely high radiant intensities and high optical power, molded in a clear, untinted PCB based package with lens for surface mounting (SMD). It is certified according to UL 268 standard for smoke detectors.

PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: SMD side view
- Product series: standard
- Angle of half intensity: $\pm 12^\circ$

FEATURES

- Package type: surface-mount
- Package form: side view
- Small dimensions (L x W x H in mm): 3.0 x 2.61 x 1.2
- Peak wavelength: $\lambda_p = 452$ nm (typical)
- High radiant intensity
- Angle of half intensity: $\phi = \pm 12^\circ$ (typical)
- Compatible with automatic placement equipment
- Available in 8 mm tape on 7" diameter reels
- Soldering terminal with tin plating
- MSL 3 according to J-STD-020
- UL 268 certification
- ESD-withstand voltage: up to 2 kV HBM according to JESD22-A114-B
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Smoke detectors
- General use

PARTS TABLE

PART	COLOR	RADIANT INTENSITY (mW/sr)			at I _F (mA)	PEAK WAVELENGTH (nm)			at I _F (mA)	FORWARD VOLTAGE (V)			at I _F (mA)	TECHNOLOGY
		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		MIN.	TYP.	MAX.		
VLMB14SV460-01UL	Blue	26	38	52	20	445	452	465	20	2.6	2.9	3.4	20	InGaN / sapphire

ABSOLUTE MAXIMUM RATINGS (T_{amb} = 25 °C, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage ⁽¹⁾		V _R	5	V
DC forward current		I _F	50	mA
Maximum pulse forward current	t _p = 100 μs, t _p /T = 1 %, T _{amb} = 70 °C	I _{FP}	0.15	A
Power dissipation		P _V	170	mW
Junction temperature		T _j	115	°C
Operating temperature range		T _{amb}	-40 to +85	°C
Storage temperature range		T _{stg}	-55 to +100	°C
Soldering temperature	According to Fig. 10, J-STD-020	T _{sd}	260	°C
Thermal resistance junction to ambient	J-STD-051, soldered on PCB	R _{thJA}	450	K/W
ESD-withstand voltage	HBM	V _{ESD}	2	kV

Note

⁽¹⁾ Driving the LED in reverse direction is suitable for short term application only

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)
VLMB14SV460-01UL, BLUE

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Radiant intensity ⁽¹⁾	$I_F = 20\text{ mA}$	I_e	26	38	52	mW/sr
Radiant flux	$I_F = 20\text{ mA}$	ϕ_e	-	21	-	mW
Luminous flux	$I_F = 20\text{ mA}$	PHI_V	-	860	-	mlm
Peak wavelength ⁽¹⁾	$I_F = 20\text{ mA}$	λ_p	445	452	465	nm
Dominant wavelength	$I_F = 20\text{ mA}$	λ_d	-	457	-	nm
Spectral bandwidth at 50% $I_{rel. max.}$	$I_F = 20\text{ mA}$	$\Delta\lambda_{0.5}$	-	16	-	nm
Angle of half intensity	$I_F = 20\text{ mA}$	ϕ	-	± 12	-	$^{\circ}$
Forward voltage ⁽¹⁾	$I_F = 20\text{ mA}$	V_F	2.6	2.9	3.4	V
Reverse current	$V_R = 5\text{ V}$	I_R	-	0.1	10	μA

Note

(1) Tolerances: $\pm 15\%$ for I_e , $\pm 0.1\text{ V}$ for V_F , $\pm 1\text{ nm}$ for λ_p


TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Fig. 1 - Maximum Permissible Forward Current vs. Ambient Temperature




Fig. 3 - Relative Intensity vs. Wavelength




Fig. 2 - Relative Luminous Intensity vs. Angular Displacement




Fig. 4 - Forward Current vs. Forward Voltage




Fig. 5 - Relative Luminous Intensity vs. Forward Current




Fig. 8 - Change of Peak Wavelength vs. Forward Current




Fig. 6 - Relative Radiant Intensity vs. Forward Current




Fig. 9 - Relative Forward Voltage vs. Ambient Temperature




Fig. 7 - Change of Dominant Wavelength vs. Forward Current




Fig. 10 - Relative Luminous Intensity vs. Ambient Temperature




Fig. 11 - Relative Radiant Intensity vs. Ambient Temperature




Fig. 12 - Change of Dominant Wavelength vs. Ambient Temperature






Fig. 13 - Change of Peak Wavelength vs. Ambient Temperature



PACKAGE DIMENSIONS in millimeters




Recommended Solder Pad







REEL DIMENSIONS in millimeters



TAPE DIMENSIONS in millimeters



LEADER AND TRAILER DIMENSIONS in millimeters



COVER TAPE PEEL STRENGTH

According to DIN EN 60286-3
 0.1 N to 1.3 N
 300 mm/min ± 10 mm/min
 165° to 180° peel angle

LABEL

Standard bar code labels for finished goods

The standard bar code labels are product labels and used for identification of goods. The finished goods are packed in final packing area. The standard packing units are labeled with standard bar code labels before transported as finished goods to warehouses. The labels are on each packing unit and contain Vishay Semiconductor GmbH specific data.

SOLDERING PROFILE





Fig. 14 - Lead (Pb)-free Reflow Soldering Profile (according to J-STD-020)


BAR CODE PRODUCT LABEL (example)



- A. 2D barcode
- B. Part No: Vishay part number
- C. QTY: quantity
- D. SelCode: selection bin code
- E. Country of origin
- F. PTC: production plant code
- G. Termination finish
- H. Region code
- I. Serial#: serial number
- K. Batch Number: year, week, country code, plant code
- L. SL: sales location
- M. Environmental Symbols: RoHS, lead (Pb)-free, halogen-free
- N. Lot numbers

DRY PACKING

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



FINAL PACKING

The sealed reel is packed into a cardboard box. A secondary cardboard box is used for shipping purposes.



RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the aluminum bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.

After more than 168 h under these conditions moisture content will be too high for reflow soldering.

In case of moisture absorption, the devices will recover to the former condition by drying under the condition given in J-STD-033.


An EIA JEDEC standard J-STD-033 level 3 label is included on all dry bags.

ESD PRECAUTION

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the antistatic shielding bag. Electrostatic sensitive devices warning labels are on the packaging.

VISHAY SEMICONDUCTORS STANDARD BAR CODE LABELS

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.



Example of MSL Label



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.