


High Sensitivity, I²C Ambient Light Sensor



DESCRIPTION

Designed using CMOS process technology, the VEML3235P is an advanced ambient light sensor featuring an I²C protocol interface. It is easy to operate via simple I²C commands.

Incorporating a photodiode, amplifiers, and analog circuits all within a single chip, it achieves spectral sensitivity optimized to closely match the response of the human eye.

Offering excellent temperature compensation, the VEML3235P also features a robust refresh rate setting that eliminates the need for an external RC low pass filter. A software shutdown mode reduces power consumption to less than 1 μ A.

FEATURES

- Package type: surface-mount
- Dimensions (L x W x H in mm): 2.0 x 1.25 x 1.0
- Integrated modules: ambient light sensor (ALS)
- Supply voltage range V_{DD} : 2.6 V to 3.6 V
- Communication via I²C interface
- Floor life: 168 h, MSL 3, according to J-STD-020
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



APPLICATIONS

- Handheld device
- Notebook
- Consumer device
- Industrial and medical application
- Computing, industrial devices, and displays

AMBIENT LIGHT FUNCTION

- High ALS sensitivity with minimum detectable intensity of 0.002 lx/cnt supports low transmittance lens design
- Excellent temperature compensation
- High dynamic detection resolution
- Software shutdown mode control

PRODUCT SUMMARY

PART NUMBER	OPERATING VOLTAGE RANGE (V)	I ² C BUS VOLTAGE RANGE (V)	PEAK SENSITIVITY (nm)	AMBIENT LIGHT RANGE (lx)	AMBIENT LIGHT RESOLUTION (lx)	OUTPUT CODE	ADC RESOLUTION PROXIMITY / AMBIENT LIGHT
VEML3235P	2.6 to 3.6	1.7 to 3.6	550, 700 (ALS, W)	0 to 17 000	0.034	16 bit, I ² C	0.002

ORDERING INFORMATION

ORDERING CODE	PACKAGING	VOLUME ⁽¹⁾	REMARKS
VEML3235P	Tape and reel	MOQ: 2500	2.0 mm x 1.25 mm x 1.0 mm

Note

⁽¹⁾ MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	MIN.	MAX.	UNIT
Supply voltage		V_{DD}	0	4	V
Operation temperature range		T_{amb}	-40	+85	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	-40	+85	$^{\circ}\text{C}$

RECOMMENDED OPERATING CONDITION ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	MIN.	MAX.	UNIT
Supply voltage		V _{DD}	2.6	3.6	V
Operation temperature range		T _{amb}	-40	+85	°C
I ² C bus operating frequency		f _(I²C clk)	10	400	kHz

CIRCUIT BLOCK DIAGRAM




Fig. 1 - Block Diagram

PIN DESCRIPTIONS




Fig. 2 - Pin Descriptions (top view)

PIN DESCRIPTIONS

PIN ASSIGNMENT	SYMBOL	TYPE	FUNTION
1	GND	-	Power supply ground; all voltages are referenced to GND
2	SDA	I / O (open drain)	I ² C digital bus data input / output
3	SCL	I	I ² C digital clock input
4	V _{DD}	I	Supply voltage

BASIC CHARACTERISTICS ($T_{\text{amb}} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Supply voltage		V _{DD}	2.6	3.3	3.6	V
Supply current ⁽¹⁾	Active state	I _{DD}	150	250	400	μA
Shut down current ⁽¹⁾⁽²⁾	Idle state	I _{sd}	0	1	2	μA
I ² C clock rate range ⁽¹⁾		f _{SCL}	10	-	400	kHz
I ² C signal input, logic high ⁽¹⁾		V _{IH}	1.2	-	-	V
I ² C signal input, logic low ⁽¹⁾		V _{IL}	-	-	0.4	V
Output low voltage SDA ⁽¹⁾	3 mA sink current	V _{OL}	0	-	0.4	V
Detectable minimum illuminance ⁽¹⁾⁽³⁾	ALS_IT = 800 ms, Gain 1 = x 2, Gain2 = x 4		-	0.002	-	lx
Detectable illuminance ⁽¹⁾⁽³⁾	ALS_IT = 100 ms, Gain 1 = x 2, Gain2 = x 2		-	0.034	-	lx
Detectable maximum illuminance ⁽¹⁾⁽³⁾	ALS_IT = 50 ms, Gain 1 = x 1, Gain2 = x 1		-	17 000	-	lx
Dark offset ⁽¹⁾⁽²⁾	ALS_IT = 100 ms, Gain 1 = x 2, Gain2 = x 2		0	0	2	code

Notes

(1) Test condition: $V_{DD} = 3.3 \text{ V}$, temperature: 25°C

(2) Light conditions: dark



(3) Light conditions: 5000K white LED

**I²C TIMING CHARACTERISTICS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	SYMBOL	STANDARD MODE ⁽¹⁾		FAST MODE ⁽¹⁾		UNIT
		MIN.	MAX.	MIN.	MAX.	
Clock frequency	$f_{(SMBCLK)}$	10	100	10	400	kHz
Bus free time between start and stop condition	$t_{(BUF)}$	4.7	-	1.3	-	μs
Hold time after (repeated) start condition; after this period, the first clock is generated	$t_{(HDSTA)}$	4.0	-	0.6	-	μs
Repeated start condition setup time	$t_{(SUSTA)}$	4.7	-	0.6	-	μs
Stop condition setup time	$t_{(SUSTO)}$	4.0	-	0.6	-	μs
Data hold time	$t_{(HDDAT)}$	-	3450	-	900	ns
Data setup time	$t_{(SUDAT)}$	250	-	100	-	ns
I ² C clock (SCL) low period	$t_{(LOW)}$	4.7	-	1.3	-	μs
I ² C clock (SCL) high period	$t_{(HIGH)}$	4.0	-	0.6	-	μs
Clock / data fall time	$t_{(F)}$	-	300	-	300	ns
Clock / data rise time	$t_{(R)}$	-	1000	-	300	ns



Note

⁽¹⁾ Data based on standard I²C protocol requirement, not tested in production

Fig. 3 - I²C Timing Diagram



PARAMETER TIMING INFORMATION

Fig. 4 - I²C Bus Timing for Sending Word Command FormatFig. 5 - I²C Bus Timing for Receive Word Command Format



BASIC CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Fig. 6 - Relative Spectral Sensitivity vs. Wavelength




Fig. 7 - Relative Sensitivity vs. Angular Displacement

APPLICATION INFORMATION
1. Pin Connection With the Host

Known for being a cost-effective solution, the VEML3235P is an ambient light sensor featuring an I²C interface. You can easily access “light intensity” readings through its standard serial digital interface without complex calculations or external controller programming.

Locating a 0.1 μF capacitor near the V_{DD} pin in the circuit is recommended for power supply noise rejection. Ensuring proper I²C communication, the design suggests using 2.2 k Ω pull-up resistors on the bus lines.




Fig. 8 - Hardware Pin Connection Diagram

APPLICATION CIRCUIT PARAMETERS		
METER	VALUE	DESCRIPTION
V_{DD}	2.6 V to 3.6 V	A staple power supply such as a low dropout regulator or a switching regulator is required; the power supply isolation can be further improved with a decoupling capacitor C_1
$V_{pull\ up}$	1.7 V to 3.6 V	A staple power supply such as a low dropout regulator or a switching regulator is required; a voltage level shifter is required if the I ² C bus voltage from the microcontroller is higher than 2 V
C_1	100 nF	Decoupling capacitors are recommended to reduce the noise in the supply voltage
R_1 to R_2	2.2 k Ω to 4.7 k Ω	Pull-up resistors within the range of 2.2 k Ω to 4.7 k Ω are recommended; any increase in bus capacitance or resistance will increase the logic high transition time



Digital Interface

Programmed via the I²C bus, the VEML3235P contains a command register that controls all sensor operations.

Allowing users to set operation parameters and latch light data, this simple command structure easily programs operations.


Utilizing Fig. 9, users can view both read and write I²C command formats between the VEML3235P and the host.

Linked to host activity are the white blocks in the figure, while gray blocks indicate the VEML3235P's acknowledgement of access.


Interactions between the host and sensor follow this command protocol to ensure accurate data exchange.

Every transfer cycle corresponds to host commands and sensor responses, allowing reliable communication over I²C.

Send byte → write command to VEML3235P



Receive byte → read data from VEML3235P



S = start condition

P = stop condition

A = acknowledge

N = not acknowledge

☐ Host action

☒ Sensor acknowledge

Fig. 9 - Command Protocol Format

Command Register Format

The VEML3235P has a 16-bit resolution per G and W channel, the VEML3235P communicates via a 7-bit I²C protocol assigned to the 0x10 slave address.

COMMAND CODE DESCRIPTION					
COMMAND CODE	REGISTER NAME	DATE BYTE LOW / HIGH	BIT	FUNCTION DESCRIPTION	R / W
0x00	Reserved	L	7	Set 0	R / W
	ALS/W_IT		6 : 4	ALS / W integration time setting (0 : 0 : 0) = 50 ms (0 : 0 : 1) = 100 ms (0 : 1 : 0) = 200 ms (0 : 1 : 1) = 400 ms (1 : 0 : 0) = 800 ms	
	Reserved		3 : 1	Set 0	
	SD	H	0	00 = power on 01 = initialized 11 = shut down	
	Reserved		7		
	Gain1		6	Set 0	
	Gain2		5	0 = x1, 1 = x2	
	Reserved		4 : 3	(0 : 0) = x1 (0 : 1) = x2 (1 : 0) = reserved (1 : 1) = x4	
	INIT		2 : 1	Set 0	
0x04	W_LSB	L	7 : 0	W LSB data	R
	W_MSB	H	7 : 0	W MSB data	
0x05	ALS_LSB	L	7 : 0	ALS LSB data	
	ALS_MSB	H	7 : 0	ALS MSB data	
0x09	ID_L	L	7 : 0	ID part number: 3235 = 0011 0101	
	Reserved	H	7 : 0	Reserved	



Data Access

Starting with 16-bit high resolution sensitivity, VEML3235P measures each channel accurately.

To represent this 16-bit data, two bytes are used: one for the least significant byte (LSB) and another for the most significant byte (MSB). Ensure the host follows the read word protocol to correctly retrieve this data. VEML3235P data format is shown below. Each detail of the data format is illustrated as follows.

16-BIT DATA FORMAT																
VEML3235P 16-BIT DATA FORMAT																
Data bit	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Data byte low																
Data byte high																

Note

S	Slave address	Wr	A	Command code	A	S	Slave address	Rd	A	Data byte low	A	Data byte high	N	P
---	---------------	----	---	--------------	---	---	---------------	----	---	---------------	---	----------------	---	---

- Data byte low represents LSB and data byte high represents MSB


PACKAGE INFORMATION in millimeters


Fig. 10 - Package Dimensions




Fig. 11 - PCB Layout Footprint

RECOMMENDED STORAGE AND REBAKING CONDITIONS				
PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
Storage temperature		5	50	°C
Relative humidity		-	60	%
Open time		-	168	h
Total time	From the date code on the aluminized envelope (unopened)	-	12	months
Rebaking	Tape and reel: 60 °C	-	22	h
	Tube: 60 °C	-	22	h



RECOMMENDED INFRARED REFLOW

Soldering conditions which are based on J-STD-020 C

IR REFLOW PROFILE CONDITION			
PARAMETER	CONDITIONS	TEMPERATURE	TIME
Peak temperature		255 °C + 0 °C / - 5 °C (max.: 260 °C)	10 s
Preheat temperature range and timing		150 °C to 200 °C	60 s to 120 s
Timing within 5 °C to peak temperature		-	10 s to 30 s
Timing maintained above temperature / time		217 °C	60 s to 150 s
Timing from 25 °C to peak temperature		-	8 min (max.)
Ramp-up rate		3 °C/s (max.)	-
Ramp-down rate		6 °C/s (max.)	-

Recommend Normal Solder Reflow is 235 °C to 255 °C




Fig. 12 - OPLGA Solder Reflow Profile Chart

RECOMMENDED IRON TIP SOLDERING CONDITION AND WARNING HANDLING

- Solder the device with the following conditions:
 - Soldering temperature: 400 °C (max.)
 - Soldering time: 3 s (max.)
- If the temperature of the method portion rises in addition to the residual stress between the leads, the possibility that an open or short circuit occurs due to the deformation or destruction of the resin increases
- The following methods: VPS and wave soldering, have not been suggested for the component assembly
- Cleaning method conditions:
 - Solvent: methyl alcohol, ethyl alcohol, isopropyl alcohol
 - Solvent temperature < 45 °C (max.)
 - Time: 3 min (min.)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.