


RF PIN Diodes - Dual, Common Cathode in SOT-323



DESIGN SUPPORT TOOLS click logo to get started



DESCRIPTION

Characterized by low reverse capacitance the PIN diodes BAR64V-05W was designed for RF signal switching and tuning. As a function of the forward bias current the forward resistance (RF) can be adjusted over a wide range. A long carrier life time offers low signal distortion for signals over 10 MHz up to 3 GHz. Typical applications for these PIN diodes are switches and attenuators in wireless, mobile, and TV-systems.

FEATURES

- High voltage current controlled RF resistor
- Small diode capacitance
- Low series inductance
- Low forward resistance
- Improved performance due to two separate dice
- Base P/N-E3 - RoHS-compliant, commercial grade
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

APPLICATIONS

- For frequencies up to 3 GHz
- RF-signal tuning
- Signal attenuator and switches
- Mobile, wireless, and TV-applications

MECHANICAL DATA

Case: SOT-323

Weight: approx. 5.7 mg

Packaging codes/options:

18/10K per 13" reel (8 mm tape), 10K/box

08/3K per 7" reel (8 mm tape), 15K/box

PARTS TABLE

PART	ORDERING CODE	TYPE MARKING	CIRCUIT CONFIGURATION	REMARKS
BAR64V-05W	BAR64V-05W-E3-08 or BAR64V-05W-E3-18	DW5	Common cathode	Tape and reel

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PART	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage		V_R	100	V
Forward continuous current		I_F	100	mA


THERMAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Junction temperature		T_j	150	$^{\circ}\text{C}$
Storage temperature range		T_{stg}	-55 to +150	$^{\circ}\text{C}$
Operating temperature range		T_{op}	-55 to +125	$^{\circ}\text{C}$




ELECTRICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	$I_F = 50\text{ mA}$		V_F			1.1	V
Reverse voltage	$I_F = 10\text{ }\mu\text{A}$		V_R	100			V
Reverse current	$V_R = 50\text{ V}$		I_R			0.05	μA
Diode capacitance	$f = 1\text{ MHz}, V_R = 0\text{ V}$		C_D		0.5		pF
	$f = 1\text{ MHz}, V_R = 1\text{ V}$		C_D		0.37	0.5	pF
	$f = 1\text{ MHz}, V_R = 20\text{ V}$		C_D		0.23	0.35	pF
Differential forward resistance	$f = 100\text{ MHz}, I_F = 1\text{ mA}$		r_f		10	20	Ω
	$f = 100\text{ MHz}, I_F = 10\text{ mA}$		r_f		2	3.8	Ω
	$f = 100\text{ MHz}, I_F = 100\text{ mA}$		r_f		0.8	1.35	Ω
Charge carrier lifetime	$I_F = 10\text{ mA}, I_R = 6\text{ mA}, i_R = 3\text{ mA}$		t_{rr}		1.8		μs
Series inductance			L_S		1		nH


TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)




18342 Fig. 1 - Forward Resistance vs. Forward Current



18326 Fig. 3 - Forward Current vs. Forward Voltage



18334 Fig. 2 - Diode Capacitance vs. Reverse Voltage



18338 Fig. 4 - Typical Charge Recovery Curve




Fig. 5 - Insertion Loss of One Diode Inserted in Series with 50 Ω Strip Line




Fig. 6 - Isolation of One Diode Inserted in Series with 50 Ω Strip Line








Fig. 7 - Second Order Intercept Point for One Diode Inserted in 50 Ω Strip Line



PACKAGE DIMENSIONS in millimeters (inches): SOT-323



foot print recommendation:



Document no.: 6.541-5040.02-4
Rev. 1 - Date: 06. April 2010
21113



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.