



Optocoupler

UL Product iQ®



Note: We are enhancing our systems and you may notice duplicate entries/missing/outdated data. During this interim period, please contact our Customer Service at <https://www.ul.com/about/locations>.

Optical Isolators Certified for Canada - Component

COMPANY

VISHAY INFRARED COMPONENTS INC
2201 LAURELWOOD RD
SANTA CLARA, CA 95054-1516 United States

E52744

Marking: Company name or tradename "E52744", or trademark , model designation, and the Recognized Component Mark

for Canada 

Note: For additional marking information, refer to the [Guide Information Page](#).

Double Protected optical isolators having an isolation voltage of 5300 Vac, Model(s): VO3020, VO3021, VO3022, VO3023, VOT8024A, VOT8025, VOT8026, VOT8121A

Double protection optical isolator having an isolation voltage of 5300Vrms, Model(s): VOW135*, VOW136*, VOW137*, VOW138*, VOW139*, VOW22XX@, VOW2601*, VOW2611*, VOW312X@

Double protection Optical isolator, insulation, provides 3750 Vac isolation, Model(s): SFH1690*, SFH690*, SFH691*, SFH6916*, VO160*, VOM160*, VOM305*, VOM45*, VOM618*, VOMA618*, VOMD110*, VOMH60A*, VOMHM60LA

Double protection optical isolator, provides 3125 Vac isolation, Model(s): SFH692*

Double protection optical isolators at 3750 Vac isolation voltage, Model(s): VOMDA1271 may be followed by additional alphanumeric characters.

Double protection optical isolators at 5300 Vac isolation voltage, Model(s): VOR1121(A6) may be followed by additional alphanumeric characters.

Double protection optical isolators having an isolation voltage of 2500Vrms, Model(s): LH1529FG, LH1529GP, LH1532FP

Double protection optical isolators having an isolation voltage of 3750 V ac, Model(s): VOM617A, VOM618A, VOS615A, VOS617A, VOS618A, VOS625A, VOS627A, VOS628A, VOT8024AM, VOT8121AM

Double protection optical isolators having an isolation voltage of 3750 Vrms, Model(s): LH1546AEF*, VO1400*, VOIH060A, VOIH063A, VOM1271*, VOMA617*, VOMH60A, VOR1142(M4)#

Double protection optical isolators having an isolation voltage of 3750 Vrms, Model(s): VO0600T All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 3750 Vrms, Model(s): VO0601T All models may be followed by additional alphanumeric characters



Double protection optical isolators having an isolation voltage of 3750 Vrms, Model(s): VO0611T All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 3750 Vrms, Model(s): VO0630T All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 3750 Vrms, Model(s): VO0631T All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 3750 Vrms, Model(s): VO0661T All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 4420Vrms, Model(s): BRT1x*, BRT2x*, CNY1*, CNY74*, H11Ax*, H11Bx*, H11Dx*, IL1*, IL2*, IL250*, IL251*, IL252*, IL255*, IL30*, IL300*, IL410* / IL4108*, IL4116*, IL4117*, IL4118*, IL420* / IL4208*, IL4216*, IL4217*, IL4218*, IL5*, IL66*, IL66B*, IL755*, IL755B*, IL766*, IL766B*, ILD1*, ILD1615*, ILD2*, ILD250*, ILD251*, ILD252*, ILD30*, ILD31*, ILD32*, ILD5*, ILD55*, ILD610*, ILD615*, ILD620*, ILD621*, ILD66*, ILD74*, ILD755*, ILD766*, ILQ1*, ILQ1615*, ILQ2*, ILQ30*, ILQ31*, ILQ32*, ILQ5*, ILQ55*, ILQ615*, ILQ620*, ILQ621*, ILQ66*, ILQ74*, K814*, K815*, K824*, K825*, K827*, K844*, K845*, K847*, LH1544*, MCA230*, MCA231*, MCA255*, MCT5210*, MCT5211*, MCT6*, MCT62H*, MCT6H*, MOC810*, SFH1617A*, SFH600*, SFH601*, SFH608*, SFH6106*, SFH610A*, SFH6156*, SFH615A*, SFH6176*, SFH617A*, SFH6186*, SFH618A*, SFH619A*, SFH6206*, SFH620A*, SFH6286*, SFH628A*, SFH636*, SFH640*, SFH655A*, TCED1100*, TCED2100*, TCED4100*, TCET1600*, TCET2100*, TCET2200*, TCET2600*, TCET4100*, TCET4600*, VO3052*, VO3053*, VO3062*, VO3063*, VO4154*, VO4156*, VO4157*, VO4158*, VO4254*, VO4256*, VO4257*, VO4258*

Double protection optical isolators having an isolation voltage of 5000 Vrms, Model(s): 4N25, 4N26, 4N27, 4N28, 4N35, 4N36, 4N37, 4N38, 6N137A, CNY117, CNY117F, CNY17 [+], CNY17F, SFH601, SFH619A, SFH640, H11D1, VOH1016, VOH260A, VOH263A, VOT8123, VOT8125

Double protection optical isolators having an isolation voltage of 5000 Vrms, Model(s): 6N137 All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 5000 Vrms, Model(s): VO2601 All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 5000 Vrms, Model(s): VO2611 All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 5000 Vrms, Model(s): VO2630 All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 5000 Vrms, Model(s): VO2631 All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 5000 Vrms, Model(s): VO4661 All models may be followed by additional alphanumeric characters

Double protection optical isolators having an isolation voltage of 5300 V ac, Model(s): VOD3120, VOFH260A, VOFH260A

Double protection optical isolators having an isolation voltage of 5300 Vrms, Model(s): SFH1617A, SFH615A, SFH617A, VO615C, VO617A, VO617B, VO617C, VO618A, VO618C, VOWH260A

Double protection optical isolators having an isolation voltage of 5300 Vrms, Model(s): VOA300 May be followed by alphanumeric characters.

Double protection optical isolators having an isolation voltage of 5300Vrms, Model(s): 6N1135*, 6N1136*, 6N135*, 6N136*, 6N137*, 6N138*, 6N139*, LH1500A*, LH1505A*, LH1510A*, LH1518A*, LH1520A*, LH1522A*, LH1525A*, LH1526A*, LH1532A*, LH1540A*, LH1546AA*, LH1546AD*, LH1546AT*, LH1550A1*, SFH6135*, SFH6136*, SFH6138*, SFH6139*, SFH632x@, SFH6345*, SFH670x@, SFH671x@, SFH673x@, SFH674x@, SFH675x@, VO14642A*, VO2601*, VO2611*, VO263x@, VO4661*, VOR1121(B6)#, VOR1142(A4)#, VOR1142(A6)#, VOR1142(B4)#, VOR1142(B6)#, VOR2121(A8)#, VOR2121(B8)#, VOR2142(A8)#, VOR2142(B8)#



Double protection optical isolators, providing 5000 vac isolation, Model(s): 4N, CNY17, CNY75, CQY80, HS817, K233, K817P, TCDT110, TCDT111, TCDT112, TCET110, TCET111, TCET120, VO610A, VO615A

Double protection optical isolators, providing 5300 Vac isolation, Model(s): LH1262*, VO1263*

Optical isolators, single protection type, providing 3333 Vac isolation, System Y, Model(s): IL12*, IL20*, IL21*, IL22*, IL256*, ILD12*, ILD20*, ILD21*, ILD22*, ILD256*, ILD28*, SFH63*, SFH672*, SFH674*, SFH675*, VO06*, VO20*

Optical isolators, single protection type, providing 3333 Vac isolation, System Y, Model(s): VO21*, VO22*, VOD20*, VOD22*

Single protection optical isolator, providing 4420 Vac isolation, System H, Model(s): VO2223, VO2223*, VO31x0@

Single protection optical isolator, providing 4420 Vac isolation, System H, Model(s): VO31x0, where x may be any number, may be followed by additional letters.

Single protection optical isolators, providing 4420 Vac isolation., Model(s): 4N3*, K30*

- May be followed by additional alphanumeric characters, the VOR prefix shown and the suffixes in parentheses are optional.

% - May be followed by additional suffixes.

(\$) - These models may be followed by additional letters and numbers

(&) - where "X" can be any number between 0-9.

* - May be followed by alphanumeric characters.

@ - Where X is any number, may be followed by additional alphanumeric characters.

Note - In addition to trademark/ tradename - system, model or catalog designation on the device itself or on the smallest shipping container. System designation may be preceded by an maximum 4 digit date code, and may be followed by the factory identification code, with or without spaces due to space constraints.

Last Updated on 2024-01-11

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."