


## Specification of GaAlAs IR Emitting Diode Chip



### FEATURES

- Package type: chip
- Package form: single chip
- Technology: multi quantum well (MQW)
- Dimensions chip (L x W x H in mm): 0.2 x 0.2 x 0.19
- Peak wavelength:  $\lambda = 940$  nm
- Material categorization:  
for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



### DESCRIPTION

TB9408VA is an infrared, 940 nm emitting diode in GaAlAs multi quantum well technology with high radiant power and high speed. Anode is the bond pad on top.

### GENERAL INFORMATION

The datasheet is based on Vishay optoelectronics sample testing under certain predetermined and assumed conditions, and is provided for illustration purpose only. Customers are encouraged to perform testing in actual proposed packaged and used conditions. Vishay optoelectronics die products are tested using Vishay optoelectronics based quality assurance procedures and are manufactured using Vishay optoelectronics established processes. Estimates such as those described and set forth in this datasheet for semiconductor die will vary depending on a number of packaging, handling, use, and other factors. Therefore sold die may not perform on an equivalent basis to standard package products.

### PRODUCT SUMMARY

COMPONENT	$\phi_e$ (mW)	$I_e$ (mW/sr)	$\phi$ (deg)	$\lambda_p$ (nm)	$t_r$ (ns)
TB9408VA	3.5	4.0	$\pm 80$	940	15

#### Note

- Test condition see table "Basic Characteristics"

### ORDERING INFORMATION

ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM
TB9408VA-SF-F	wafer sawn on foil	MOQ: 100 000 pcs	chip

#### Note

- MOQ: minimum order quantity



### ABSOLUTE MAXIMUM RATINGS ( $T_{amb} = 25$ °C, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Forward current		$I_F$	75	mA
Reverse voltage		$V_R$	5	V
Surge forward current	$t_p = 100$ $\mu$ s	$I_{FSM}$	500	mA
Junction temperature		$T_j$	100	°C
Operating temperature range		$T_{amb}$	-40 to +85	°C
Storage temperature range chip		$T_{stg1}$	-40 to +100	°C
Storage temperature range on foil		$T_{stg2}$	-40 to +50	°C


<b>BASIC CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Forward voltage	$I_F = 5\text{ mA}$	$V_F$	1.1	1.18	1.25	V
	$I_F = 20\text{ mA}$	$V_F$	1.13	1.26	1.4	V
	$I_F = 100\text{ mA}$	$V_F$		1.45		V
	$I_F = 500\text{ mA}, t_p = 100\text{ }\mu\text{s}$	$V_F$		2.0		V
Radiant power <sup>(1)</sup>	$I_F = 100\text{ mA}$	$\phi_e$		22		mW
Radiant intensity <sup>(2)</sup>	$I_F = 100\text{ mA}$	$I_e$		4.0		mW/sr
Radiant power (epoxy encapsulated)	$I_F = 100\text{ mA}$	$\phi_e$		40		mW
Radiant power chip <sup>(3)</sup>	$I_F = 50\text{ mA}$	$\phi_e$	2.5	3.5	5.0	mW
Temperature coefficient of radiant power	$I_F = 1\text{ mA}$	$TK_{\phi_e}$		-1.1		%/K
Reverse voltage	$I_R = 10\text{ }\mu\text{A}$	$V_R$	7	18		V
Temperature coefficient of forward voltage	$I_F = 1\text{ mA}$	$TK_{V_F}$		-1.5		mV/K
Angle of half intensity	$I_F = 100\text{ mA}$	$\phi$		$> \pm 80$		deg
Peak wavelength	$I_F = 30\text{ mA}$	$\lambda_p$	920	945	960	nm
Spectral bandwidth	$I_F = 30\text{ mA}$	$\lambda_{0.5}$		25		nm
Rise time / fall time	$I_F = 100\text{ mA}$	$t_r, t_f$		15		ns

**Notes**

- (1) The measurements are based on samples of die which are mounted on a TO-18 gold header without resin coating
- (2) The radiant intensity,  $I_e$ , is measured on the geometric axis of the TO-18 header
- (3) The radiant power,  $\phi_e$ , is measured with chip on bare plate and aperture angle about  $30^{\circ}$ , as indicated on the label of each wafer

**BASIC CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)

 Fig. 1 - Relative Spectral Emission  
 $\phi_{e\text{ rel}} = f(\lambda)$ 

 Fig. 2 - Radiant Characteristics  
 $I_{rel} = f(\phi)$ 
**DIMENSIONS**

Electrode pattern:



Sectional view (schematic):




Fig. 3



MECHANICAL DIMENSIONS					
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT
Length of chip edge (x-direction)	L <sub>x</sub>	0.185	0.200	0.215	mm
Length of chip edge (y-direction)	L <sub>y</sub>	0.185	0.200	0.215	mm
Emission area	A <sub>E</sub>	0.18 x 0.18			mm <sup>2</sup>
Die height	H	0.175	0.190	0.205	mm
Diameter of bondpad	d		0.110		mm

ADDITIONAL INFORMATION	
Frontside metallization, anode	gold
Backside metallization, cathode	gold alloy
Dicing	sawing
Die bonding technology	epoxy bonding

**Note**

- All chips are checked in accordance with the Vishay Semiconductor, specification of visual inspection FVOV6870. The visual inspection shall be made in accordance with the "specification of visual inspection as referenced". The visual inspection of chip backside is performed with stereo microscope with incident light and 40x to 80x magnification. The quality inspection (final visual inspection) is performed by production. An additional visual inspection step as special release procedure by QM is not installed.

**HANDLING AND STORAGE CONDITIONS**

- The hermetically sealed shipment lots shall be opened in temperature and moisture controlled cleanroom environment only. It is mandatory to follow the rules for disposition of material that can be hazardous for humans and environment.
- Product must be handled only at ESD safe workstations. Standard ESD precautions and safe work environments are as defined in MIL-HDBK-263.
- Singulated die are not to be handled with tweezers. A vacuum wand with non metallic ESD protected tip should be used.

**PACKING**

Chips are fixed on adhesive foil. Upon request the foils can be mounted on plastic frame or disco frame. For shipment, the wafers are arranged to stacks and hermetically sealed in plastic bags to ensure protection against environmental influence (humidity and contamination).

Use for recycling reliable operators only. We can help getting in touch with your nearest sales office. By agreement we will take back packing material, if it is sorted. You will have to bear the costs of transport. We will invoice you for any costs incurred for packing material that is returned unsorted or which we are not obliged to accept.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.