

Optocoupler



PRODUCT CERTIFICATE

No.: CQC09001037308

NAME AND ADDRESS OF THE APPLICANT

Vishay Semiconductor Malaysia Sdn Bhd
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

NAME AND ADDRESS OF THE MANUFACTURER

Vishay Semiconductor Malaysia Sdn Bhd
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

NAME AND ADDRESS OF THE FACTORY

Vishay Semiconductor Malaysia Sdn Bhd (V002589)
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

NAME, MODEL AND SPECIFICATION

Opto Couplers

K3010P-XXXX, K3010P-XXXXT, K3010PG-XXXX, K3010PG-XXXXT, K3011P-XXXX, K3011P-XXXXT, K3011PG-XXXX, K3011PG-XXXXT, K3012P-XXXX, K3012P-XXXXT, K3012PG-XXXX, K3012PG-XXXXT, K3020P-XXXX, K3020P-XXXXT, K3020PG-XXXX, K3020PG-XXXXT, K3021P-XXXX, K3021P-XXXXT, K3021PG-XXXX, K3021PG-XXXXT, K3022P-XXXX, K3022P-XXXXT, K3022PG-XXXX, K3022PG-XXXXT, K3023P-XXXX, K3023P-XXXXT, K3023PG-XXXX, K3023PG-XXXXT, K3036P-XXXX, K3036P-XXXXT, K3036PG-XXXX, K3036PG-XXXXT (注: 型号中的变量 "X" 仅代表封装形式和VDE局部放电的代号, 可以是空白, 字母A-Z或者数字1-9的组合) 外部爬电距离>8.5mm, 绝缘穿透距离≥0.4mm, 通过热循环测试, 适用于海拔5000米及以

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB8898-2011

CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471543-2015.

Date of issue: May.20,2016

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Nov.25,2009

President:

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nanshuan Xilu, Beijing 100070 P.R.China
<http://www.cqc.com.cn>

C 0082672



产品认证证书

证书编号: CQC09001037308

申请人名称及地址

威旭半导体马来西亚有限公司
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

制造商名称及地址

威旭半导体马来西亚有限公司
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

生产企业名称及地址

威旭半导体马来西亚有限公司 (V002589)
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

产品名称和系列、规格、型号

光电藕合器

K3010P-XXXX, K3010P-XXXXT, K3010PG-XXXX, K3010PG-XXXXT, K3011P-XXXX, K3011P-XXXXT, K3011PG-XXXX, K3011PG-XXXXT, K3012P-XXXX, K3012P-XXXXT, K3012PG-XXXX, K3012PG-XXXXT, K3020P-XXXX, K3020P-XXXXT, K3020PG-XXXX, K3020PG-XXXXT, K3021P-XXXX, K3021P-XXXXT, K3021PG-XXXX, K3021PG-XXXXT, K3022P-XXXX, K3022P-XXXXT, K3022PG-XXXX, K3022PG-XXXXT, K3023P-XXXX, K3023P-XXXXT, K3023PG-XXXX, K3023PG-XXXXT, K3036P-XXXX, K3036P-XXXXT, K3036PG-XXXX, K3036PG-XXXXT (注: 型号中的变量“X”仅代表封装形式和VDE局部放电的代号, 可以是空白, 字母A-Z或者数字1-9的组合) 外部爬电距离 >8.5mm, 绝缘穿透距离 ≥ 0.4mm, 通过热循环测试, 适用于海拔5000米及以下

产品标准和技术要求

GB8898-2011

认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-471543-2015 认证规则的要求, 特发此证。

发证日期: 2016年05月20日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持
本证书为变更证书, 证书首次颁发日期: 2009年11月25日

主任:



中国质量认证中心

中国·北京·南四环西路188号9区100070

http://www.cqc.com.cn

C 0082672