



## Small Signal Schottky Diodes



**DESIGN SUPPORT TOOLS** click logo to get started



### MECHANICAL DATA

**Case:** DO-35 (DO-204AH)

**Weight:** approx. 125 mg

**Cathode band color:** black

**Packaging codes/options:**

TR/10K per 13" reel (52 mm tape), 50K/box

TAP/10K per ammpack (52 mm tape), 50K/box

### FEATURES

- The SD103 series is a metal-on-silicon Schottky barrier device which is protected by a PN junction guarding
- The low forward voltage drop and fast switching make it ideal for protection of MOS devices, steering, biasing and coupling diodes for fast switching and low logic level applications
- Other applications are click suppression, efficient full wave bridges in telephone subsets, and blocking diodes in rechargeable low voltage battery systems
- These diodes are also available in the SOD-123 and SOD-323 case with type designations SD103AW(S) to SD103CW(S), and in the MiniMELF case with type designations LL103A thru LL103C
- For general purpose applications
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS COMPLIANT**  
**HALOGEN FREE**

### APPLICATIONS

- HF-detector
- Protection circuit
- Small battery charger
- AC/DC, DC/DC converters

| PARTS TABLE |                      |                         |              |                       |                        |
|-------------|----------------------|-------------------------|--------------|-----------------------|------------------------|
| PART        | TYPE DIFFERENTIATION | ORDERING CODE           | TYPE MARKING | CIRCUIT CONFIGURATION | REMARKS                |
| SD103A      | $V_R = 40\text{ V}$  | SD103A-TR or SD103A-TAP | SD103A       | Single                | Tape and reel/ammopack |
| SD103B      | $V_R = 30\text{ V}$  | SD103B-TR or SD103B-TAP | SD103B       | Single                | Tape and reel/ammopack |
| SD103C      | $V_R = 20\text{ V}$  | SD103C-TR or SD103C-TAP | SD103C       | Single                | Tape and reel/ammopack |

| ABSOLUTE MAXIMUM RATINGS ( $T_{amb} = 25\text{ }^\circ\text{C}$ , unless otherwise specified) |   |        |           |       |      |
|---|---|--------|-----------|-------|------|
| PARAMETER   | TEST CONDITION                              | PART   | SYMBOL    | VALUE | UNIT |
| Peak inverse voltage  |   | SD103A | $V_R$     | 40    | V    |
|   |   | SD103B | $V_R$     | 30    | V    |
|   |   | SD103C | $V_R$     | 20    | V    |
| Power dissipation (infinite heat sink) <sup>(1)</sup>   |   |        | $P_{tot}$ | 400   | mW   |
| Peak forward surge current  | $t_p = 300\text{ }\mu\text{s}$ square pulse |        | $I_{FSM}$ | 15    | A    |

**Note**

<sup>(1)</sup> Valid provided that leads at a distance of 4 mm from case are kept at ambient temperature

| THERMAL CHARACTERISTICS ( $T_{amb} = 25\text{ }^\circ\text{C}$ , unless otherwise specified) |                |            |             |                  |
|--|----------------|------------|-------------|------------------|
| PARAMETER  | TEST CONDITION | SYMBOL     | VALUE       | UNIT             |
| Thermal resistance junction to ambient air <sup>(1)</sup>                                    |                | $R_{thJA}$ | 310         | K/W              |
| Junction temperature   |                | $T_j$      | 125         | $^\circ\text{C}$ |
| Storage temperature range  |                | $T_{stg}$  | -55 to +150 | $^\circ\text{C}$ |

**Note**

<sup>(1)</sup> Valid provided that leads at a distance of 4 mm from case are kept at ambient temperature



| ELECTRICAL CHARACTERISTICS (T <sub>amb</sub> = 25 °C, unless otherwise specified) |  |        |                   |      |      |      |      |
|---|--|--------|-------------------|------|------|------|------|
| PARAMETER   | TEST CONDITION   | PART   | SYMBOL            | MIN. | TYP. | MAX. | UNIT |
| Reverse breakdown voltage   | I <sub>R</sub> = 50 μA   | SD103A | V <sub>(BR)</sub> | 40   |      |      | V    |
|   |  | SD103B | V <sub>(BR)</sub> | 30   |      |      | V    |
|   |  | SD103C | V <sub>(BR)</sub> | 20   |      |      | V    |
| Leakage current   | V <sub>R</sub> = 30 V  | SD103A | I <sub>R</sub>    |      |      | 5    | μA   |
|   | V <sub>R</sub> = 20 V  | SD103B | I <sub>R</sub>    |      |      | 5    | μA   |
|   | V <sub>R</sub> = 10 V  | SD103C | I <sub>R</sub>    |      |      | 5    | μA   |
| Forward voltage drop  | I <sub>F</sub> = 20 mA   |        | V <sub>F</sub>    |      |      | 370  | mV   |
|   | I <sub>F</sub> = 200 mA  |        | V <sub>F</sub>    |      |      | 600  | mV   |
| Diode capacitance   | V <sub>R</sub> = 0 V, f = 1 MHz  |        | C <sub>D</sub>    |      | 50   |      | pF   |
| Reverse recovery time   | I <sub>F</sub> = I <sub>R</sub> = 50 mA to 200 mA, recover to 0.1 I <sub>R</sub> |        | t <sub>rr</sub>   |      | 10   |      | ns   |

**TYPICAL CHARACTERISTICS** (T<sub>amb</sub> = 25 °C, unless otherwise specified)




Fig. 1 - Forward Current vs. Forward Voltage




Fig. 3 - Reverse Current vs. Junction Temperature




Fig. 2 - Forward Current vs. Forward Voltage




Fig. 4 - Diode Capacitance vs. Reverse Voltage





Fig. 5 - Typical Non-Repetitive Forward Surge Current vs. Pulse Width

**PACKAGE DIMENSIONS** in millimeters (inches): **DO-35 (DO-204AH)**



Rev. 6 - Date: 19. December 2011  
 Document no.: SB-V-3906.04-031(4)  
 94 9366



## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.