

Surface Mount Fast Avalanche Rectifiers

eSMP® Series


SMP (DO-220AA)

 Cathode  —  Anode

ADDITIONAL RESOURCES


[3D Models](#)

| PRIMARY CHARACTERISTICS | |
|-------------------------|------------------------------------|
| $I_{F(AV)}$ | 1.0 A |
| V_{RRM} | 200 V, 400 V, 600 V, 800 V, 1000 V |
| I_{FSM} | 30 A, 25 A |
| t_{tr} | 140 ns, 120 ns |
| V_F | 1.15 V, 1.4 V |
| I_R | 1 μ A |
| E_{AS} | 20 mJ |
| T_J max. | 175 °C |
| Package | SMP (DO-220AA) |
| Circuit configuration | Single |

FEATURES

- Very low profile - typical height of 1.0 mm
- Ideal for automated placement
- Glass passivated pellet chip junction
- Fast switching for high efficiency
- Low reverse current
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

 AUTOMOTIVE
GRADE
Available

RoHS
COMPLIANT
HALOGEN
FREE

TYPICAL APPLICATIONS

For use in fast switching rectification of power supply, inverters, converters, and freewheeling diodes for consumer, automotive, and telecommunication.

MECHANICAL DATA

Case: SMP (DO-220AA)

Molding compound meets UL 94 V-0 flammability rating
Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3 - halogen-free, RoHS-compliant, and automotive grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 2 whisker test, HM3 suffix meets JESD 201 class 2 whisker test

| MAXIMUM RATINGS ($T_A = 25\text{ °C}$ unless otherwise noted) | | | | | | | |
|---|----------------|-------------|-------|-------|-------|-------|------|
| PARAMETER | SYMBOL | AR1PD | AR1PG | AR1PJ | AR1PK | AR1PM | UNIT |
| Device marking code | | ARD | ARG | ARJ | ARK | ARM | |
| Maximum repetitive peak reverse voltage | V_{RRM} | 200 | 400 | 600 | 800 | 1000 | V |
| Average forward current | $I_{F(AV)}$ | 1.0 | | | | | A |
| Peak forward surge current 10 ms single half sine-wave superimposed on rated load | I_{FSM} | 30 | | | 25 | | A |
| Non-repetitive avalanche energy at $I_{AS} = 1.0\text{ A}$, $T_A = 25\text{ °C}$ | E_{AS} | 20 | | | | | mJ |
| Operating junction and storage temperature range | T_J, T_{STG} | -55 to +175 | | | | | °C |



| ELECTRICAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted) | | | | | | | | | |
|--|--|-------------------------|-------------------------------|-------|-------|-------|-------|-------|------|
| PARAMETER | TEST CONDITIONS | | SYMBOL | AR1PD | AR1PG | AR1PJ | AR1PK | AR1PM | UNIT |
| Maximum instantaneous forward voltage | I _F = 1.0 A | T _A = 25 °C | V _F ⁽¹⁾ | 1.25 | | | 1.6 | | V |
| | | T _A = 125 °C | | 1.15 | | | 1.4 | | |
| Maximum reverse current | Rated V _R | T _A = 25 °C | I _R ⁽²⁾ | 1.0 | | | | | μA |
| | | T _A = 125 °C | | 100 | | | | | |
| Maximum reverse recovery time | I _F = 0.5 A, I _R = 1.0 A, I _{rr} = 0.25 A | | t _{rr} | 140 | | | 120 | | ns |
| Typical junction capacitance | 4.0 V, 1 MHz | | C _J | 12.5 | | | 8.5 | | pF |

Notes

- (1) Pulse test: 300 μs pulse width, 1 % duty cycle
- (2) Pulse test: Pulse width ≤ 40 ms

| THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted) | | | | | | | | |
|---|---------------------------------|-------|-------|-------|-------|-------|------|--|
| PARAMETER | SYMBOL | AR1PD | AR1PG | AR1PJ | AR1PK | AR1PM | UNIT | |
| Typical thermal resistance | R _{θJA} ⁽¹⁾ | 132 | | | | | °C/W | |
| | R _{θJM} ⁽¹⁾ | 15 | | | | | | |

Note

- (1) Free air, mounted on recommended copper pad area. Thermal resistance R_{θJA} - junction to ambient, R_{θJM} - junction to mount at the terminal cathode band

| ORDERING INFORMATION (Example) | | | | |
|--------------------------------|-----------------|------------------------|---------------|------------------------------------|
| PREFERRED P/N | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE |
| AR1PJ-M3/84A | 0.024 | 84A | 3000 | 7" diameter plastic tape and reel |
| AR1PJ-M3/85A | 0.024 | 85A | 10 000 | 13" diameter plastic tape and reel |
| AR1PJHM3/84A ⁽¹⁾ | 0.024 | 84A | 3000 | 7" diameter plastic tape and reel |
| AR1PJHM3/85A ⁽¹⁾ | 0.024 | 85A | 10 000 | 13" diameter plastic tape and reel |

Note

- (1) Automotive grade

RATINGS AND CHARACTERISTICS CURVES (T_A = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 6 - Typical Reverse Characteristics




Fig. 4 - Typical Instantaneous Forward Characteristics




Fig. 7 - Typical Reverse Characteristics




Fig. 5 - Typical Instantaneous Forward Characteristics




Fig. 8 - Typical Junction Capacitance








Fig. 9 - Typical Transient Thermal Impedance

PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

SMP (DO-220AA)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.