

SMD Aluminum Solid Capacitors with Conductive Polymer



FEATURES

- New OS-CON 94SVPD series provides improved characteristics with up to 125 °C temperature capability and 35 V maximum voltage rating in a SMD package
- Improved damp heat (steady state) 85 °C x 85 % RH performance
- Suitable for use in smoothing circuits of vehicle-mounted equipment, industrial equipment, etc.
- This product can support lead (Pb)-free reflow ⁽²⁾
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

| QUICK REFERENCE DATA | | | |
|--|--|--|--|
| DESCRIPTION | CONDITIONS | VALUE | |
| Operating temperature range | - | - 55 °C to + 125 °C | |
| Capacitance tolerance | 120 Hz | M: ± 20 % | |
| Tangent of loss angle (tan δ) | 120 Hz | ≤ values in Electrical Data and Ordering Information table | |
| Leakage current (µA/2 min) (or less) ⁽¹⁾ | After 2 min | ≤ values in Electrical Data and Ordering Information table | |
| ESR | - | ≤ values in Electrical Data and Ordering Information table | |
| Characteristics of impedance ratio at high and low temperature | 100 kHz, + 20 °C | - 55 °C | Z/Z _{20 °C} 0.75 to 1.25 |
| | | + 125 °C | Z/Z _{20 °C} 0.75 to 1.0 |
| Endurance | + 125 °C, 2000 h rated voltage applied | ΔC/C | Within ± 20 % |
| | | tan δ | 2 x or < than an initial standard |
| | | ESR | 2 x or < than an initial standard |
| | | Leakage current | Below an initial standard |
| Damp heat (steady state) | + 85 °C, 85 % to 90 % RH, 1000 h rated voltage applied | ΔC/C | Within ± 20 % |
| | | tan δ | 2 x or < than an initial standard |
| | | ESR | 2 x or < than an initial standard |
| | | Leakage current | Below an initial standard |
| Solder heat resistance ⁽²⁾ | (VPS) (230 °C x 75 s) | ΔC/C | Within ± 10 % |
| | | tan δ | 1.3 x or < than an initial standard |
| | | ESR | 1.3 x or < than an initial standard |
| | | Leakage current | Below an initial standard (after voltage processing) |

Notes

- ⁽¹⁾ If any doubt arises, measure the current after applying voltage (voltage treatment). Voltage treatment: The rated voltage is applied (10 V to 35 V) for 120 min at 125 °C.
- ⁽²⁾ Refer to "Recommended Reflow Profile" for maximum temperatures.

| DIMENSIONS in millimeters | | | | | | | |
|---------------------------|-----------|---------------|---------|---------|---------|------------|---------|
| | | | | | | | |
| SIZE CODE | Ø D ± 0.5 | L + 0.1/- 0.4 | W ± 0.2 | H ± 0.2 | C ± 0.2 | R | P ± 0.2 |
| C6 | 6.3 | 5.9 | 6.6 | 6.6 | 7.3 | 0.6 to 0.8 | 2.1 |
| E7 | 8.0 | 6.9 | 8.3 | 8.3 | 9.0 | 0.6 to 0.8 | 3.2 |
| F8 | 10.0 | 7.9 | 10.3 | 10.3 | 11.0 | 0.6 to 0.8 | 4.6 |
| E12 | 8.0 | 11.9 | 8.3 | 8.3 | 9.0 | 0.8 to 1.1 | 3.2 |
| F12 | 10.0 | 12.6 | 10.3 | 10.3 | 11.0 | 0.8 to 1.1 | 4.6 |

| CASE CODE LIST | | | | |
|----------------------------------|---------------------------------|----------------|----------------|----------------|
| CAPACITANCE (μF) | RATED VOLTAGE (SURGE AT 125 °C) | | | |
| | 10.0 (11.5) | 16.0 (18.4) | 25.0 (29.0) | 35.0 (40.0) |
| 8.2 | | | | E7 |
| 10 | | | C6 | |
| 18 | | | | F8 |
| 22 | | | E7 | E12 |
| 39 | | | F8 | |
| 47 | | | E12 | F12 |
| 56 | C6 | | | |
| 82 | | E7 | F12 | |

| RECOMMENDED LAND PATTERN DIMENSIONS (in millimeters) | | | | |
|--|-----------|-----|------|-----|
| | SIZE CODE | a | b | c |
| | C6 | 2.1 | 9.1 | 1.6 |
| | E7 | 2.8 | 11.1 | 1.9 |
| | F8 | 4.3 | 13.1 | 1.9 |
| | E12 | 2.8 | 11.1 | 1.9 |
| | F12 | 4.3 | 13.1 | 1.9 |

| FREQUENCY COEFFICIENT FOR RIPPLE CURRENT | | | | |
|--|-------------------------|-------------------------|---------------------------|----------------------------|
| FREQUENCY | 120 Hz \leq f < 1 kHz | 1 kHz \leq f < 10 kHz | 10 kHz \leq f < 100 kHz | 100 kHz \leq f < 500 kHz |
| COEFFICIENT | 0.05 | 0.3 | 0.7 | 1 |


| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | |
|--|----------------------------|-----------|--|-----------------------------|--------------------------|----------------------------|---|----------------------------|
| U_R (V) | C_R (μF) | CASE CODE | MAX. ESR (100 kHz TO 300 kHz) (m Ω) | RATED RIPPLE CURRENT | ALLOWABLE RIPPLE CURRENT | MAX. TANGENT OF LOSS ANGLE | MAX. LEAKAGE CURRENT (μA) ⁽²⁾ | PART NUMBER ⁽¹⁾ |
| | | | | 100 kHz (mA) ⁽³⁾ | | | | |
| | | | | 105 °C < Tx \leq 125 °C | Tx \leq 105 °C | | | |
| 10 | 56 | C6 | 45 | 538 | 1700 | 0.12 | 112 | 94SVPD566X0010C6 |
| 16 | 82 | E7 | 40 | 670 | 2120 | 0.12 | 262 | 94SVPD826X0016E7 |
| 25 | 10 | C6 | 65 | 474 | 1500 | 0.10 | 50 | 94SVPD106X0025C6 |
| | 22 | E7 | 48 | 580 | 1835 | 0.10 | 110 | 94SVPD226X0025E7 |
| | 39 | F8 | 45 | 664 | 2100 | 0.10 | 195 | 94SVPD396X0025F8 |
| | 47 | E12 | 30 | 943 | 2980 | 0.12 | 235 | 94SVPD476X0025E12 |
| | 82 | F12 | 28 | 1202 | 3800 | 0.12 | 410 | 94SVPD826X0025F12 |
| 35 | 8.2 | E7 | 70 | 400 | 1300 | 0.10 | 57 | 94SVPD825X0035E7 |
| | 18 | F8 | 60 | 550 | 1800 | 0.10 | 126 | 94SVPD186X0035F8 |
| | 22 | E12 | 50 | 700 | 2300 | 0.12 | 154 | 94SVPD226X0035E12 |
| | 47 | F12 | 30 | 1150 | 3650 | 0.12 | 329 | 94SVPD476X0035F12 |

Notes


- (1) Capacitance tolerance: M \pm 20 %
 (2) After 2 min
 (3) Tx: Ambient temperature



FREQUENCY CHARACTERISTICS



| FREQUENCY (kHz) | 0.12 | 0.5 | 1 | 10 | 100 | 500 | 1000 | 5000 | 10 000 |
|---------------------------------|---------|--------|--------|-------|-------|-------|-------|-------|--------|
| 94SVPD106X0025C6 IMPEDANCE (Ω) | 127.769 | 31.001 | 15.608 | 1.612 | 0.176 | 0.046 | 0.032 | 0.093 | 0.179 |
| 94SVPD106X0025C6 ESR (Ω) | 1.303 | 0.482 | 0.306 | 0.081 | 0.044 | 0.035 | 0.032 | 0.033 | 0.040 |
| 94SVPD186X0035F8 IMPEDANCE (Ω) | 72.87 | 17.781 | 8.955 | 0.918 | 0.096 | 0.023 | 0.037 | 0.200 | 0.397 |
| 94SVPD186X0035F8 ESR (Ω) | 1.681 | 0.333 | 0.179 | 0.043 | 0.027 | 0.023 | 0.023 | 0.026 | 0.034 |
| 94SVPD476X0035F12 IMPEDANCE (Ω) | 30.178 | 7.389 | 3.725 | 0.392 | 0.05 | 0.016 | 0.025 | 0.134 | 0.266 |
| 94SVPD476X0035F12 ESR (Ω) | 0.852 | 0.206 | 0.121 | 0.045 | 0.023 | 0.016 | 0.014 | 0.017 | 0.023 |
| 94SVPD826X0025F12 IMPEDANCE (Ω) | 16.736 | 4.096 | 2.074 | 0.229 | 0.029 | 0.014 | 0.028 | 0.144 | 0.285 |
| 94SVPD826X0025F12 ESR (Ω) | 0.339 | 0.135 | 0.094 | 0.033 | 0.015 | 0.011 | 0.011 | 0.014 | 0.019 |







Notes

- n = 30 pieces
- V.P.S. test conditions: 230 °C x 75 s x 2 (V.P.S. = Vapor Phase Soldering method)



TYPICAL PARAMETERS

| MODEL | TEST ITEM | TEST TEMPERATURE | APPLIED VOLTAGE | LOT. NUMBER |
|------------------|----------------------------------|------------------|-----------------|-------------|
| 94SVPD186X0035F8 | Endurance (after V.P.S. test) | 125 °C | 35 V | 6517A3254 |







Notes

- n = 30 pieces
- V.P.S. test conditions: 230 °C x 75 s x 2 (V.P.S. = Vapor Phase Soldering method)



TYPICAL PARAMETERS

| MODEL | TEST ITEM | TEST TEMPERATURE | APPLIED VOLTAGE | LOT. NUMBER |
|-------------------|----------------------------------|------------------|-----------------|-------------|
| 94SVPD476X0035F12 | Endurance (after V.P.S. test) | 125 °C | 35 V | 7209A6544 |







Notes

- n = 30 pieces
- V.P.S. test conditions: 230 °C x 75 s x 2 (V.P.S. = Vapor Phase Soldering method)




TYPICAL PARAMETERS

| MODEL | TEST ITEM | TEST TEMPERATURE | APPLIED VOLTAGE | LOT. NUMBER |
|-------------------|----------------------------------|------------------|-----------------|-------------|
| 94SVPD826X0025F12 | Endurance (after V.P.S. test) | 125 °C | 25 V | 7527A6544 |



Notes

- n = 30 pieces
- V.P.S. test conditions: 230 °C x 75 s x 2 (V.P.S. = Vapor Phase Soldering method)







Notes

- n = 30 pieces
- V.P.S. test conditions: 230 °C x 75 s x 2 (V.P.S. = Vapor Phase Soldering method)




TYPICAL PARAMETERS

| MODEL | TEST ITEM | TEST TEMPERATURE | APPLIED VOLTAGE | TEST HUMIDITY | LOT. NUMBER |
|------------------|---|------------------|-----------------|---------------|-------------|
| 94SVPD186X0035F8 | Damp heat (steady state) (after V.P.S. test) | 85 °C | 35 V | 85 % | 6517A3254 |



Notes

- n = 30 pieces
- V.P.S. test conditions: 230 °C x 75 s x 2 (V.P.S. = Vapor Phase Soldering method)







Notes

- n = 30 pieces
- V.P.S. test conditions: 230 °C x 75 s x 2 (V.P.S. = Vapor Phase Soldering method)



TYPICAL PARAMETERS


| MODEL | TEST ITEM | TEST TEMPERATURE | APPLIED VOLTAGE | TEST HUMIDITY | LOT. NUMBER |
|-------------------|---|------------------|-----------------|---------------|-------------|
| 94SVDP826X0025F12 | Damp heat (steady state) (after V.P.S. test) | 85 °C | 25 V | 85 % | 6806A6724 |



Notes

- n = 30 pieces
- V.P.S. test conditions: 230 °C x 75 s x 2 (V.P.S. = Vapor Phase Soldering method)

RECOMMENDED REFLOW PROFILE



Vishay OS-CON has different characteristics against soldering heat from conventional aluminum electrolytic capacitors or tantalum capacitors because of its unique materials and structure.

Please note the following points on soldering of Vishay OS-CON 94SVPD series to draw out the best performance.

| ITEM | 94SVPD SERIES | |
|-------------------------|----------------------------|-------------|
| | Peak temperature (max.) | 250 °C |
| Preheat | 150 °C to 180 °C 90 ± 30 s | |
| 200 °C over time (max.) | 60 s | 60 s |
| 220 °C over time (max.) | 50 s | 50 s |
| 230 °C over time (max.) | 40 s | 40 s |
| Reflow number | Twice or less | Only 1 time |

Note

- All temperatures are measured on the topside of the Al-can and terminal surface.

Attention:

Reflow soldering may reduce the capacitance of products before or after soldering even if soldering conditions stipulated in Recommended Reflow Condition are met. Though the actual reflow conditions are subject to change depending on the kind of reflow soldering method, please be aware that the peak temperature at the top of Al-case and electrode terminals should not exceed peak temperature. Particular notice should be given to the time that Vishay OS-CON is heated at 200 °C or higher during reflow. Be aware that soldering considerably deviating from these conditions will cause problems such as a 50 % reduction in capacitance, and a considerable increase in leakage current.

The leakage current value may increase (from a few μ A to a few mA) even within the above conditions. When the Vishay OS-CON is used in a DC circuit, the leakage current will decrease gradually through self-recovery after voltage is applied. If your reflow profile (reflow temperature, number of reflows, etc.) deviates from the above conditions for mounting the 94SVPD series, please consult with Vishay OS-CON.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.