



Type 94SVP/SVPD Solid Aluminum Capacitors with Organic Semiconductor

TAPING SPECIFICATIONS FOR AUTOMATIC INSERTING MACHINES



DIMENSIONS in millimeters								
SIZE CODE	A	B	W	F	E	P	t	T
A5	4.7 ± 0.2	4.7 ± 0.2	12.0 ± 0.3	5.5 ± 0.1	1.75 ± 0.1	8.0 ± 0.1	0.4 ± 0.1	5.8 ± 0.2
B6	5.6 ± 0.2	5.6 ± 0.2	16.0 ± 0.3	7.5 ± 0.1	1.75 ± 0.1	8.0 ± 0.1	0.4 ± 0.1	6.2 ± 0.2
C6	6.9 ± 0.2	6.9 ± 0.2	16.0 ± 0.3	7.5 ± 0.1	1.75 ± 0.1	12.0 ± 0.1	0.4 ± 0.1	6.2 ± 0.2
E7	8.6 ± 0.2	8.6 ± 0.2	24.0 ± 0.3	11.5 ± 0.1	1.75 ± 0.1	12.0 ± 0.1	0.4 ± 0.1	7.2 ± 0.2
F8	10.7 ± 0.2	10.7 ± 0.2	24.0 ± 0.3	11.5 ± 0.1	1.75 ± 0.1	16.0 ± 0.1	0.4 ± 0.1	8.2 ± 0.2
E12	8.6 ± 0.2	8.6 ± 0.2	24.0 ± 0.3	11.5 ± 0.1	1.75 ± 0.1	16.0 ± 0.1	0.4 ± 0.1	12.3 ± 0.2
F12	10.7 ± 0.2	10.7 ± 0.2	24.0 ± 0.3	11.5 ± 0.1	1.75 ± 0.1	16.0 ± 0.1	0.4 ± 0.1	13.0 ± 0.2



DIMENSIONS in millimeters		
SIZE CODE	W1	W2
A5	13.0 ± 0.5	17.5 ± 1.0
B6, C6	17.0 ± 0.5	21.5 ± 1.0
E7, F8, E12, F12	25.0 ± 0.5	29.5 ± 1.0



Reel Specifications

Type 94SVP/SVPD
Solid Aluminum Capacitors with Organic Semiconductor
Electrolyte Surface Mount Chip

Vishay OS-CON

MINIMUM PACKING QUANTITY	
SIZE CODE	PCS/REEL (Ø 380)
A5	2000
B6	1500
C6	1000
E7	1000
F8	500
E12	400
F12	400