



R-C Thermal Model Parameters

DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in PSpice, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the PSpice simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the PSpice Platform".

R-C THERMAL MODEL FOR TANK CONFIGURATION




R-C VALUES FOR TANK CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RT1	n/a	67.6124m	n/a
RT2	n/a	64.9846m	n/a
RT3	n/a	88.6132m	n/a
RT4	n/a	378.9024m	n/a
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CT1	n/a	45.8152m	n/a
CT2	n/a	26.7314m	n/a
CT3	n/a	4.8770m	n/a
CT4	n/a	150.7120m	n/a

- Note**
- n/a indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.



R-C THERMAL MODEL FOR FILTER CONFIGURATION



R-C VALUES FOR FILTER CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RF1	n/a	126.0545m	n/a
RF2	n/a	74.8495m	n/a
RF3	n/a	35.3084m	n/a
RF4	n/a	363.7369m	n/a
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CF1	n/a	5.0522m	n/a
CF2	n/a	538.5542u	n/a
CF3	n/a	8.7935m	n/a
CF4	n/a	139.5273m	n/a

Note

- n/a indicates not applicable

