



## HEXFRED® Ultrafast Diodes, 30 A (Single Phase Bridge MTP Power Modules)



MTP

### FEATURES

- Low profile package
- Low  $t_{rr}$  and  $Q_{rr}$
- Soft reverse recovery
- Direct mounting to heatsink
- Round pin with PCB solderable terminals
- UL approved file E78996 
- Low junction to case thermal resistance
- 3500  $V_{RMS}$  insulation voltage
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)


**RoHS  
COMPLIANT**

### PRIMARY CHARACTERISTICS

$V_R$	1200 V
$V_F$ (typical) at $I_F = 30$ A	2.46 V
$I_O$ at 88 °C	30 A
$Q_{rr}$ (typical)	720 nC
$I_{RRM}$ (typical)	12 A
$t_{rr}$ (typical)	121 ns
$di_{(rec)M}/dt$ (typical)	300 A/ $\mu$ s
Package	MTP
Circuit configuration	Single phase bridge

### DESCRIPTION

A range of extremely compact single-phase rectifier bridges offering efficient and reliable operation.

The low profile package has been specifically conceived to maximize space saving and optimize the electrical layout of the application specific power supplies.

### ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Cathode to anode voltage	$V_R$		1200	V
Continuous forward current per diode	$I_F$	$T_C = 88$ °C	30	A
Single pulse forward current per diode	$I_{FSM}$	10 ms sine or 6 ms rectangular pulse, $T_J = 25$ °C	300	
Maximum repetitive forward current per diode	$I_{FRM}$		200	
Maximum power dissipation per diode	$P_D$	$T_C = 88$ °C	85	W
Operating junction temperature range	$T_J$		-40 to +150	°C

### ELECTRICAL SPECIFICATIONS ( $T_J = 25$ °C unless otherwise specified)


PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Cathode to anode breakdown voltage	$V_{BR}$	$I_R = 100$ $\mu$ A	1200	-	-	V
Forward voltage	$V_F$	$I_F = 30$ A	-	2.46	3.34	V
		$I_F = 60$ A	-	3.11	4.45	
		$I_F = 30$ A, $T_J = 125$ °C	-	2.32	2.96	
		$I_F = 60$ A, $T_J = 125$ °C	-	3.07	3.96	
Reverse leakage current	$I_R$	$V_R = 1200$ V	-	2.8	50	$\mu$ A
		$V_R = 1200$ V, $T_J = 125$ °C	-	2	10	mA
Junction capacitance	$C_T$	$V_R = 200$ V	-	50	75	pF



<b>DYNAMIC RECOVERY CHARACTERISTICS</b> ( $T_J = 25\text{ }^\circ\text{C}$ unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNITS
Reverse recovery time	$t_{rr}$	$T_J = 25\text{ }^\circ\text{C}$	$I_F = 30\text{ A}$ $dI_F/dt = 200\text{ A}/\mu\text{s}$ $V_R = 200\text{ V}$	-	121	170	ns
		$T_J = 125\text{ }^\circ\text{C}$		-	180	260	
Peak recovery current	$I_{RR}$	$T_J = 25\text{ }^\circ\text{C}$		-	12	16	A
		$T_J = 125\text{ }^\circ\text{C}$		-	17	24	
Reverse recovery charge	$Q_{rr}$	$T_J = 25\text{ }^\circ\text{C}$		-	720	1350	nC
		$T_J = 125\text{ }^\circ\text{C}$		-	1540	2310	
Peak rate of fall of recovery current during $t_b$	$dl_{(rec)M}/dt$	$T_J = 25\text{ }^\circ\text{C}$		-	300	-	A/ $\mu\text{s}$
		$T_J = 125\text{ }^\circ\text{C}$		-	265	-	


<b>INSULATION TABLE</b>				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
RMS insulation voltage	$V_{INS}$	$T_J = 25\text{ }^\circ\text{C}$ , all terminals shorted, $f = 50\text{ Hz}$ , $t = 1\text{ s}$	3500	V

<b>THERMAL - MECHANICAL SPECIFICATIONS</b>				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range	$T_J, T_{Stg}$		-40 to +150	$^\circ\text{C}$
Maximum thermal resistance, $\frac{\text{per module}}{\text{junction to case}}$ $\frac{\text{per junction}}$	$R_{thJC}$	DC operation	0.18	$^\circ\text{C}/\text{W}$
			0.73	
Typical thermal resistance, case to heatsink	$R_{thCS}$	Mounting surface, smooth and greased	0.06	
Approximate weight			65	g
Mounting torque, $\pm 10\%$ to heatsink		A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound. Lubricated threads.	4	Nm




93161\_01

Fig. 1 - Output Current Ratings Characteristics




93161\_04

Fig. 4 - Typical Values of Reverse Current vs. Reverse Voltage (Per Diode)




93161\_02

Fig. 2 - On-State Power Loss Characteristics




93161\_05

Fig. 5 - Maximum Surge Forward Current (Per Diode)




93161\_03

Fig. 3 - Typical Forward Voltage Drop Characteristics (Per Diode)




93161\_06

Fig. 6 - Typical Reverse Time vs.  $di_F/dt$  (Per Diode)




93161\_07

Fig. 7 - Typical Stored Charge vs.  $di/dt$  (Per Diode)



93161\_08

Fig. 8 - Typical Recovery Current vs.  $di/dt$  (Per Diode)



93161\_09

Fig. 9 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics (Per Diode)


**ORDERING INFORMATION TABLE**

Device code	<b>VS-</b>	<b>3</b>	<b>5</b>	<b>MT</b>	<b>120</b>	<b>P</b>	<b>B</b>
	①	②	③	④	⑤		⑥

- 1** - Vishay Semiconductors product
- 2** - Current rating (3 = 30 A)
- 3** - Circuit configuration code: 5 = single phase bridge
- 4** - Package indicator: MT = MTP
- 5** - Voltage code: code x 10 (120 = 1200 V)
- 6** - Pinout code: B = round pins



**CIRCUIT CONFIGURATION**




**LINKS TO RELATED DOCUMENTS**

<b>LINKS TO RELATED DOCUMENTS</b>	
Dimensions	<a href="http://www.vishay.com/doc?95383">www.vishay.com/doc?95383</a>



### MTP - Full Pin

**DIMENSIONS** in millimeters



Use Self Tapping Screw  
or M2.5 x X.  
e.g. M2.5 x 6 or M2.5 x 8  
according to PCB  
thickness used

PINS POSITION  
WITH TOLERANCE  $\text{Ø } 0.6$



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.