



Standard Recovery Diodes, (Stud Version), 40 A



DO-5 (DO-203AB)

FEATURES

- High surge current capability
- Stud cathode and stud anode version
- Leaded version available
- Types up to 1600 V V_{RRM}
- Designed and qualified for multiple level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

TYPICAL APPLICATIONS

- Battery charges
- Converters
- Power supplies
- Machine tool controls
- Welding

| PRIMARY CHARACTERISTICS | |
|-------------------------|-----------------|
| $I_{F(AV)}$ | 40 A |
| Package | DO-5 (DO-203AB) |
| Circuit configuration | Single |

| MAJOR RATINGS AND CHARACTERISTICS | | | | |
|-----------------------------------|-----------------|-------------|--------------|------------------|
| PARAMETER | TEST CONDITIONS | 40HF(R) | | UNITS |
| | | 10 TO 120 | 140/160 | |
| $I_{F(AV)}$ | | 40 | 40 | A |
| | T_C | 140 | 110 | °C |
| $I_{F(RMS)}$ | | 62 | 62 | A |
| I_{FSM} | 50 Hz | 570 | 570 | A |
| | 60 Hz | 595 | 595 | |
| I^2t | 50 Hz | 1600 | 1600 | A ² s |
| | 60 Hz | 1450 | 1450 | |
| V_{RRM} | Range | 100 to 1200 | 1400 to 1600 | V |
| T_J | | -65 to 190 | -65 to 160 | °C |

ELECTRICAL SPECIFICATIONS

| VOLTAGE RATINGS | | | | |
|-----------------|--------------|--|--|--|
| TYPE NUMBER | VOLTAGE CODE | V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V | V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V | I_{RRM} MAXIMUM AT $T_J = T_J$ MAXIMUM mA |
| VS-40HF(R) | 10 | 100 | 200 | 9 |
| | 20 | 200 | 300 | |
| | 40 | 400 | 500 | |
| | 60 | 600 | 700 | |
| | 80 | 800 | 900 | |
| | 100 | 1000 | 1100 | |
| | 120 | 1200 | 1300 | |
| | 140 | 1400 | 1500 | 4.5 |
| 160 | 1600 | 1700 | | |



| FORWARD CONDUCTION | | | | | | |
|---|---------------|--|---------------------------|-----------|---------|-------------------|
| PARAMETER | SYMBOL | TEST CONDITIONS | | 40HF(R) | | UNITS |
| | | | | 10 TO 120 | 140/160 | |
| Maximum average forward current at case temperature | $I_{F(AV)}$ | 180° conduction, half sine wave | | 40 | 40 | A |
| Maximum RMS forward current | $I_{F(RMS)}$ | | | 140 | 110 | °C |
| Maximum peak, one-cycle forward, non-repetitive surge current | I_{FSM} | t = 10 ms t = 8.3 ms | No voltage reapplied | 62 | | A |
| | | t = 10 ms t = 8.3 ms | 100 % V_{RRM} reapplied | 570 | | A |
| | | | | 595 | | |
| | | | | 480 | | |
| | | | | 500 | | |
| Maximum I^2t for fusing | I^2t | t = 10 ms t = 8.3 ms | No voltage reapplied | 1600 | | A ² s |
| | | t = 10 ms t = 8.3 ms | 100 % V_{RRM} reapplied | 1450 | | |
| | | | | 1150 | | |
| | | | | 1050 | | |
| Maximum $I^2\sqrt{t}$ for fusing | $I^2\sqrt{t}$ | t = 0.1 ms to 10 ms, no voltage reapplied | | 16 000 | | A ² √s |
| Value of threshold voltage (up to 1200 V) | $V_{F(TO)}$ | $T_J = T_J$ maximum | | 0.65 | | V |
| Value of threshold voltage (for 1400 V/1600 V) | $V_{F(TO)}$ | | | 0.76 | | |
| Value of forward slope resistance (up to 1200 V) | r_f | $T_J = T_J$ maximum | | 4.29 | | mΩ |
| Value of forward slope resistance (for 1400 V/1600 V) | r_f | | | 3.8 | | |
| Maximum forward voltage drop | V_{FM} | $I_{pk} = 125$ A, $T_J = 25$ °C, $t_p = 400$ μs rectangular wave | | 1.30 | 1.50 | V |

| THERMAL AND MECHANICAL SPECIFICATIONS | | | | | | |
|--|----------------|---|--|-----------------|------------|---------------------|
| PARAMETER | SYMBOL | TEST CONDITIONS | | 40HF(R) | | UNITS |
| | | | | 10 to 120 | 140 to 160 | |
| Maximum junction operating and storage temperature range | T_J, T_{Stg} | | | -65 to 190 | -65 to 160 | °C |
| Maximum thermal resistance, junction to case | R_{thJC} | DC operation | | 0.95 | | K/W |
| Maximum thermal resistance, case to heatsink | R_{thCS} | Mounting surface, smooth, flat and greased | | 0.25 | | |
| Maximum allowable mounting torque (+0 %, -10 %) | | Not lubricated thread, tightening on nut ⁽¹⁾ | | 3.4 (30) | | N · m (lbf · in) |
| | | Lubricated thread, tightening on nut ⁽¹⁾ | | 2.3 (20) | | |
| | | Not lubricated thread, tightening on hexagon ⁽²⁾ | | 4.2 (37) | | |
| | | Lubricated thread, tightening on hexagon ⁽²⁾ | | 3.2 (28) | | |
| Approximate weight | | | | 17 | | g |
| | | | | 0.6 | | oz. |
| Case style | | See dimensions - link at the end of datasheet | | DO-5 (DO-203AB) | | |

Notes

- (1) Recommended for pass-through holes
- (2) Recommended for holed threaded heatsinks

| ΔR_{thJC} CONDUCTION | | | | |
|------------------------------|-----------------------|------------------------|---------------------|-------|
| CONDUCTION ANGLE | SINUSOIDAL CONDUCTION | RECTANGULAR CONDUCTION | TEST CONDITIONS | UNITS |
| 180° | 0.14 | 0.10 | $T_J = T_J$ maximum | K/W |
| 120° | 0.16 | 0.17 | | |
| 90° | 0.21 | 0.22 | | |
| 60° | 0.30 | 0.31 | | |
| 30° | 0.50 | 0.50 | | |

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 3 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 4 - Current Ratings Characteristics




Fig. 5 - Forward Power Loss Characteristics



Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Forward Power Loss Characteristics




Fig. 8 - Forward Power Loss Characteristics




Fig. 9 - Maximum Non-Repetitive Surge Current




Fig. 11 - Forward Voltage Drop Characteristics (Up To 1200 V)




Fig. 10 - Maximum Non-Repetitive Surge Current




Fig. 12 - Forward Voltage Drop Characteristics (For 1400 V/1600 V)





Fig. 13 - Thermal Impedance Z_{thJC} Characteristics



ORDERING INFORMATION TABLE



- 1** - Vishay Semiconductors product
- 2** -
 - 40 = standard device
 - 41 = not isolated lead
 - 42 = isolated lead with silicone sleeve
(red = reverse polarity)
(blue = normal polarity)
- 3** - HF = standard diode
- 4** -
 - None = stud normal polarity (cathode to stud)
 - R = stud reverse polarity (anode to stud)
- 5** - Voltage code x 10 = V_{RRM} (see Voltage Ratings table)
- 6** -
 - None = stud base DO-5 (DO-203AB) 1/4" 28UNF-2A
 - M = stud base DO-5 (DO-203AB) M6 x 1

| LINKS TO RELATED DOCUMENTS | |
|----------------------------|--|
| Dimensions | www.vishay.com/doc?95344 |

DO-203AB (DO-5) for 40HF(R) and 41HF(R) Series

DIMENSIONS FOR 40HF(R) SERIES in millimeters (inches)



Outline Dimensions

Vishay Semiconductors

DO-203AB (DO-5) for 40HF(R)
and 41HF(R) Series



DIMENSIONS FOR 41HF(R) SERIES in millimeters (inches)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.