




R-C Thermal Model Parameters

DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in PSpice, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the PSpice simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the PSpice Platform".

R-C THERMAL MODEL FOR TANK CONFIGURATION



| R-C VALUES FOR TANK CONFIGURATION | | | |
|-----------------------------------|---------|-----------|------|
| THERMAL RESISTANCE (°C/W) | | | |
| Junction to | Ambient | Case | Foot |
| RT1 | n/a | 55.4253m | n/a |
| RT2 | n/a | 163.2351m | n/a |
| RT3 | n/a | 150.4245m | n/a |
| RT4 | n/a | 27.7668m | n/a |
| THERMAL CAPACITANCE (Joules/°C) | | | |
| Junction to | Ambient | Case | Foot |
| CT1 | n/a | 17.1145m | n/a |
| CT2 | n/a | 154.7747u | n/a |
| CT3 | n/a | 81.0340m | n/a |
| CT4 | n/a | 157.0013u | n/a |


Note

- n/a indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.



R-C THERMAL MODEL FOR FILTER CONFIGURATION




| R-C VALUES FOR FILTER CONFIGURATION | | | |
|-------------------------------------|---------|-----------|------|
| THERMAL RESISTANCE (°C/W) | | | |
| Junction to | Ambient | Case | Foot |
| RF1 | n/a | 209.4074m | n/a |
| RF2 | n/a | 1.6963m | n/a |
| RF3 | n/a | 76.3896m | n/a |
| RF4 | n/a | 110.9684m | n/a |
| THERMAL CAPACITANCE (Joules/°C) | | | |
| Junction to | Ambient | Case | Foot |
| CF1 | n/a | 209.8096u | n/a |
| CF2 | n/a | 20.4429m | n/a |
| CF3 | n/a | 4.2279m | n/a |
| CF4 | n/a | 89.2495m | n/a |

Note

- n/a indicates not applicable




SiHP110N65SF Tank j-c Temperature: 27.0



Date: January 30, 2026 Page 1 Time: 18:31:43

SiHP110N65SF Filter j-c Temperature: 27.0



Date: January 30, 2026 Page 1 Time: 18:41:10