


MaxSiC® 1200 V N-Channel SiC MOSFET


Marking Code: Q120A045SL

PRODUCT SUMMARY		
V_{DS} (V) at T_J max.	1200	
$R_{DS(on)}$ typ. (mΩ) at 25 °C	$V_{GS} = 18$ V	45
Q_g typ. (nC)	83	
I_D (A)	51	
C_{oss} typ. (pF)	96	
P_D (W)	254	
Configuration	Single	

FEATURES

- AEC-Q101 qualified
- Fast switching speed
- Short circuit withstand time 3 μs
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Automotive on board charger
- Automotive DC/DC converter for EV/HEV
- Auxiliary drives
- EV Charging


RoHS
COMPLIANT
HALOGEN
FREE

ORDERING INFORMATION	
Package	TO-247AD 4L
Lead (Pb)-free and halogen-free	MXPQ120A045SL-GE3

ABSOLUTE MAXIMUM RATINGS ($T_C = 25$ °C, unless otherwise noted)				
PARAMETER	SYMBOL	LIMIT	UNIT	
Drain-source voltage	V_{DS}	1200	V	
Gate-source voltage	V_{GS}	-10 / +22		
Recommended operation voltage of gate-source	V_{GSOP}	-5 to -3 / +18		
Continuous drain current	$T_C = 25$ °C	I_D	51	A
Pulsed drain current ^a		I_{DM}	102	
Short-circuit withstand time ^b		T_{SC}	3	μs
Maximum power dissipation	$T_C = 25$ °C	P_D	254	W
Operating junction and storage temperature range		T_J, T_{stg}	-55 to +175	°C
Soldering recommendations (peak temperature)	For 10 s		260	°C
Single pulse avalanche energy ^c		E_{AS}	200	mJ

Notes







- a. Repetitive rating; pulse width limited by maximum junction temperature
b. $V_{GS} = 18$ V, $V_{DS} = 800$ V, $R_{g(ext)} = 20$ Ω, verified by the design / characterization
c. $T_J = 25$ °C, $V_{DD} = 120$ V, $L = 1$ mH, $V_{GS} = 18$ V, $I_{AS} = 20$ A







**THERMAL RESISTANCE RATINGS**






PARAMETER	SYMBOL	TYP.	MAX.	UNIT
Maximum junction-to-ambient	R_{thJA}	-	40	°C/W
Maximum junction-to-case (drain)	R_{thJC}	-	0.59	







SPECIFICATIONS ($T_J = 25\text{ °C}$, unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT	
Static							
Drain-source breakdown voltage	V _{DS}	V _{GS} = 0 V, I _D = 1 mA	1200	-	-	V	
Gate-source threshold voltage (N)	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 5 mA	-	2.8	-	V	
		V _{DS} = V _{GS} , I _D = 5 mA, T _J = 175 °C	-	1.9	-	V	
Gate-source leakage	I _{GSS}	V _{GS} = 22 V, V _{DS} = 0 V	-	-	100	nA	
		V _{GS} = -10 V, V _{DS} = 0 V	-	-	-100		
Zero gate voltage drain current	I _{DSS}	V _{DS} = 1200 V, V _{GS} = 0 V	-	-	10	μA	
Drain-source on-state resistance	R _{DS(on)}	V _{GS} = 15 V, I _D = 26 A	-	60	75	mΩ	
		V _{GS} = 18 V, I _D = 26 A	-	45	56		
		V _{GS} = 18 V, I _D = 26 A, T _J = 175 °C	-	82	-		
Transconductance	g _{fs}	V _{DS} = 10 V, I _D = 26 A	-	11	-	S	
Dynamic							
Input capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = 800 V, f = 100 KHz	-	2523	-	pF	
Output capacitance	C _{oss}		-	96	-		
Reverse transfer capacitance	C _{rss}		-	3	-		
Total gate charge	Q _g	V _{GS} = -5 V ~ 18 V, I _D = 26 A, V _{DS} = 800 V	-	83	-	nC	
Gate-source charge	Q _{gs}		-	24	-		
Gate-drain charge	Q _{gd}		-	23	-		
Gate Resistance	R _g	V _{DS} = 0 V, f = 1 MHz	-	3	-	Ω	
Switching Characteristics							
Turn-on delay time	t _{d(on)}	V _{GS} = -5 V ~ 18 V, I _D = 26 A, V _{DS} = 800 V, R _{g(ext)} = 4.4 Ω	T _J = 25 °C	-	20	-	ns
Rise time	t _r		T _J = 175 °C	-	18	-	
			T _J = 25 °C	-	17	-	
			T _J = 175 °C	-	16	-	
			T _J = 25 °C	-	26	-	
Turn-off delay time	t _{d(off)}		T _J = 175 °C	-	29	-	
			T _J = 25 °C	-	10	-	
Fall time	t _f		T _J = 175 °C	-	10	-	μJ
			T _J = 25 °C	-	285	-	
Turn-on switching energy	E _{on}		T _J = 175 °C	-	252	-	
Turn-off switching energy	E _{off}		T _J = 25 °C	-	86	-	
			T _J = 175 °C	-	85	-	
Body Diode Ratings and Characteristic							
Forward diode voltage	V _{SD}	V _{GS} = -5 V, I _{SD} = 13 A, T _J = 25 °C	-	4.9	-	V	
Continuous diode forward current	I _{SD}	V _{GS} = -5 V, T _J = 25 °C	-	-	37	A	
Pulsed diode forward current	I _{SDM}		-	-	102		
Reverse recovery time	t _{rr}	V _{GS} = -5 V, I _{SD} = 26 A, V _R = 800 V, di/dt = 1000 A/μs	-	19	-	ns	
Reverse recovery charge	Q _{rr}		-	83	-	nC	
Reverse recovery current	I _{RRM}		-	7	-	A	

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)

Fig. 1 - Typical Output Characteristics

Fig. 4 - Typical Transfer Characteristics

Fig. 2 - Typical Output Characteristics

Fig. 5 - Normalized On-Resistance vs. Drain Current

Fig. 3 - Typical Output Characteristics

Fig. 6 - Typical Capacitance vs. Drain-to-Source Voltage


Fig. 7 - Typical Gate Charge vs. Gate-to-Source Voltage

Fig. 10 - Typical Source-Drain Diode Forward Voltage

Fig. 8 - Normalized On-Resistance vs. Temperature

Fig. 11 - On-Resistance vs. Gate-to-Source Voltage

Fig. 9 - Drain-to-Source Voltage vs. Temperature

Fig. 12 - Threshold Voltage vs. Case Temperature


Fig. 13 - Drain Current vs. Case Temperature

Fig. 15 - Power, Dissipated P_D vs. Case Temperature

Fig. 14 - Output Capacitance and its Stored Energy vs. Drain-to-Source Voltage

Fig. 16 - Safe Operating Area

Fig. 17 - Transient Thermal Impedance


Fig. 18 - Waveforms of Switching Time

Fig. 21 - Waveforms for Gate Charge

Fig. 19 - Waveforms for Switching Energy

Fig. 22 - Waveforms for Reverse Recovery

Fig. 20 - Switching and Reverse Diode Characteristics Measurement Circuit

Fig. 23 - Thermal Equivalent Circuit

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?292860.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.