

Fast Recovery Diodes (Stud Version), 6 A, 12 A



DO-4 (DO-203AA)

FEATURES

- Short reverse recovery time
- Low stored charge
- Wide current range
- Excellent surge capabilities
- Standard JEDEC® types
- Stud cathode and stud anode versions
- Fully characterized reverse recovery conditions
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

TYPICAL APPLICATIONS

- DC power supplies
- Inverters
- Converters
- Choppers
- Ultrasonic systems
- Freewheeling diodes

| PRIMARY CHARACTERISTICS | |
|-------------------------|-----------------|
| $I_{F(AV)}$ | 6 A, 12 A |
| Package | DO-4 (DO-203AA) |
| Circuit configuration | Single |

| MAJOR RATINGS AND CHARACTERISTICS | | | | |
|-----------------------------------|-----------------|------------------------------------|------------------------------------|------------------|
| SYMBOL | TEST CONDITIONS | 1N3879(R) TO 1N3883(R) | 1N3889(R) TO 1N3893(R) | UNITS |
| $I_{F(AV)}$ | | 6 ⁽¹⁾ | 12 ⁽¹⁾ | A |
| | T_C maximum | 100 | 100 | °C |
| $I_{F(RMS)}$ | | 9.5 | 19 | A |
| I_{FSM} | 50 Hz | 72 | 145 | A |
| | 60 Hz | 75 ⁽¹⁾ | 150 ⁽¹⁾ | |
| I^2t | 50 Hz | 26 | 103 | A ² s |
| | 60 Hz | 23 | 94 | |
| $I^2\sqrt{t}$ | | 363 | 856 | $I^2\sqrt{s}$ |
| V_{RRM} | Range | 50 to 400 ⁽¹⁾ | 50 to 400 ⁽¹⁾ | V |
| t_{rr} | | See Recovery Characteristics table | See Recovery Characteristics table | ns |
| T_J | Range | -65 to +150 | -65 to +150 | °C |

Note
⁽¹⁾ JEDEC® registered values



ELECTRICAL SPECIFICATIONS

| VOLTAGE RATINGS | | | | | | |
|-----------------|--------------|---|---|--|---|---|
| TYPE NUMBER | VOLTAGE CODE | V _{RRM} , MAXIMUM REPETITIVE PEAK AND OFF-STATE VOLTAGE V | V _{RSM} , MAXIMUM NON-REPETITIVE PEAK VOLTAGE V | I _{RRM} MAXIMUM AT T _J = 25 °C µA | I _{RRM} MAXIMUM AT T _J = 100 °C mA | I _{RRM} MAXIMUM AT T _J = 150 °C mA |
| 1N3879(R) | - | 50 | 75 | 15 ⁽¹⁾ | 1.0 ⁽¹⁾ | 3.0 ⁽¹⁾ |
| 1N3880(R) | | 100 | 150 | | | |
| 1N3881(R) | | 200 | 250 | | | |
| 1N3882(R) | | 300 | 350 | | | |
| 1N3883(R) | | 400 | 450 | | | |
| 1N3889(R) | - | 50 | 75 | 25 ⁽¹⁾ | 3.0 ⁽¹⁾ | 5.0 ⁽¹⁾ |
| 1N3890(R) | | 100 | 150 | | | |
| 1N3891(R) | | 200 | 250 | | | |
| 1N3892(R) | | 300 | 350 | | | |
| 1N3893(R) | | 400 | 450 | | | |

Note

(1) JEDEC® registered values

| FORWARD CONDUCTION | | | | | | | |
|--|---------------------|---|----------------------------------|---|------------------------|------------------------|-------------------|
| PARAMETER | SYMBOL | TEST CONDITIONS | | | 1N3879(R) TO 1N3883(R) | 1N3889(R) TO 1N3893(R) | UNITS |
| Maximum average forward current at case temperature | I _{F(AV)} | 180° conduction, half sine wave DC | | | 6 ⁽¹⁾ | 12 ⁽¹⁾ | A |
| | | | | | 100 | 100 | °C |
| Maximum RMS current | I _{F(RMS)} | | | | 9.5 | 19 | |
| Maximum peak, one-cycle non-repetitive forward current | I _{FSM} | t = 10 ms | No voltage reapplied | Sinusoidal half wave, initial T _J = 150 °C | 85 | 170 | A |
| | | t = 8.3 ms | | | 90 | 180 | |
| | | t = 10 ms | 100 % V _{RRM} reapplied | | 72 | 145 | |
| | | t = 8.3 ms | | | 75 ⁽¹⁾ | 150 ⁽¹⁾ | |
| Maximum I ² t for fusing | I ² t | t = 10 ms | No voltage reapplied | | 36 | 145 | A ² s |
| | | t = 8.3 ms | | | 33 | 130 | |
| | | t = 10 ms | 100 % V _{RRM} reapplied | | 26 | 103 | |
| | | t = 8.3 ms | | | 23 | 94 | |
| Maximum I ² √t for fusing | I ² √t | t = 0.1 ms to 10 ms, no voltage reapplied | | | 363 | 1452 | A ² √s |
| Maximum forward voltage drop | V _{FM} | T _J = 25 °C; I _F = Rated I _{F(AV)} (DC) | | | 1.4 ⁽¹⁾ | 1.4 ⁽¹⁾ | V |
| | | T _C = 100 °C; I _{FM} = π x rated I _{F(AV)} | | | 1.5 ⁽¹⁾ | 1.5 ⁽¹⁾ | |

Note

(1) JEDEC® registered values

| RECOVERY CHARACTERISTICS | | | | | | |
|---------------------------------|----------------------|---|------------------------|------------------------|-------|--|
| PARAMETER | SYMBOL | TEST CONDITIONS | 1N3879(R) TO 1N3883(R) | 1N3889(R) TO 1N3893(R) | UNITS | |
| Maximum reverse recovery time | t _{rr} | T _J = 25 °C, I _F = 1 A to V _R = 30 V, di _F /dt = 100 A/µs | 150 | 150 | ns | |
| | | T _J = 25 °C, di _F /dt = 25 A/µs, I _{FM} = π x rated I _{F(AV)} | 300 ⁽¹⁾ | 300 ⁽¹⁾ | | |
| Maximum peak recovery current | I _{RM(REC)} | I _{FM} = π x rated I _{F(AV)} | 4 ⁽¹⁾ | 5 ⁽¹⁾ | - | |
| Maximum reverse recovery charge | Q _{rr} | T _J = 25 °C, I _F = 1 A to V _R = 30 V, di _F /dt = 100 A/µs | 400 | 350 | nC | |
| | | T _J = 25 °C, di _F /dt = 25 A/µs, I _{FM} = π x rated I _{F(AV)} | 400 | 400 | | |

Note

(1) JEDEC® registered values



| THERMAL AND MECHANICAL SPECIFICATIONS | | | | | |
|--|------------|--|---------------------------|---------------------------|---------------------|
| PARAMETER | SYMBOL | TEST CONDITIONS | 1N3879(R) TO 1N3883(R) | 1N3889(R) TO 1N3893(R) | UNITS |
| Maximum junction operating temperature range | T_J | | -65 to +150 | | °C |
| Maximum storage temperature range | T_{Stg} | | -65 to +175 | | |
| Maximum thermal resistance, junction to case | R_{thJC} | DC operation | 2.5 | 2.0 | °C/W |
| Maximum thermal resistance, case to heatsink | R_{thCS} | Mounting surface, smooth, flat and greased | 0.5 | | |
| Allowable mounting torque | | Not lubricated threads | 1.5 +0 - 10 % (13) | | N · m (lbf · in) |
| | | Lubricated threads | 1.2 +0 - 10 % (10) | | |
| Approximate weight | | | 7 | | g |
| | | | 0.25 | | oz. |
| Case style | | JEDEC® | DO-4 (DO-203AA) | | |

| ΔR_{thJC} CONDUCTION | | | | | | |
|------------------------------|---------------------------|---------------------------|---------------------------|---------------------------|-----------------------|-------|
| CONDUCTION ANGLE | 1N3879(R) TO 1N3883(R) | 1N3889(R) TO 1N3893(R) | 1N3879(R) TO 1N3883(R) | 1N3889(R) TO 1N3893(R) | TEST CONDITIONS | UNITS |
| | SINUSOIDAL CONDUCTION | | RECTANGULAR CONDUCTION | | | |
| 180° | 0.58 | 0.46 | 0.33 | 0.26 | $T_J = 150\text{ °C}$ | K/W |
| 120° | 0.60 | 0.48 | 0.58 | 0.46 | | |
| 60° | 1.28 | 1.02 | 1.28 | 1.02 | | |
| 30° | 2.20 | 1.76 | 2.20 | 1.76 | | |

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Average Forward Current vs. Maximum Allowable Case Temperature, 1N3879 Series






Fig. 2 - Average Forward Current vs. Maximum Allowable Case Temperature, 1N3889 Series




I_F , I_{FM} - Peak forward current prior to commutation
 $-di_F/dt$ - Rate of fall of forward current
 $I_{RM(REC)}$ - Peak reverse recovery current
 t_{rr} - Reverse recovery time
 Q_{rr} - Reverse recovered charge

Fig. 3 - Reverse Recovery Time Test Waveform




| Conduction angle - ϕ | ΔR - K/W |
|---------------------------|------------------|
| 180° | 0.58 |
| 120° | 0.60 |
| 60° | 1.28 |
| 30° | 2.20 |

Fig. 4 - Current Rating Nomogram (Sinusoidal Waveforms), 1N3879 Series




| Conduction angle - ϕ | ΔR - K/W |
|---------------------------|------------------|
| DC | 0 |
| 180° | 0.33 |
| 120° | 0.58 |
| 60° | 1.28 |
| 30° | 2.20 |

Fig. 5 - Current Rating Nomogram (Rectangular Waveforms), 1N3879 Series



| Conduction angle - ϕ | ΔR - KW |
|---------------------------|-----------------|
| 180° | 0.46 |
| 120° | 0.48 |
| 60° | 1.02 |
| 30° | 1.76 |

Fig. 6 - Current Rating Nomogram (Sinusoidal Waveforms), 1N3889 Series



| Conduction angle - ϕ | ΔR - KW |
|---------------------------|-----------------|
| DC | 0 |
| 180° | 0.26 |
| 120° | 0.46 |
| 60° | 1.02 |
| 30° | 1.76 |

Fig. 7 - Current Rating Nomogram (Rectangular Waveforms), 1N3889 Series




Fig. 8 - Maximum Forward Voltage vs. Forward Current, 1N3879 Series




Fig. 9 - Maximum High Level Forward Power Loss vs. Average Forward Current, 1N3879 Series




Fig. 10 - Maximum Forward Voltage vs. Forward Current, 1N3889 Series




Fig. 12 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 1N3879 Series




Fig. 11 - Maximum High Level Forward Power Loss vs. Average Forward Current, 1N3889 Series




Fig. 13 - Maximum Non-Repetitive Surge Current vs. Number of Current Pulses, 1N3889 Series





Fig. 14 - Maximum Transient Thermal Impedance, Junction to Case vs. Pulse Duration, All Series

LINKS TO RELATED DOCUMENTS

| | |
|------------|--|
| Dimensions | www.vishay.com/doc?95311 |
|------------|--|

DO-203AA (DO-4)

DIMENSIONS in millimeters (inches)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.