


# Ultrafast Rectifier, 2 x 30 A FRED Pt®



## FEATURES

- Low forward voltage drop
- 175 °C operating junction temperature
- Ultrafast recovery time
- Low leakage current
- Designed and qualified according to JEDEC®-JESD 47
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

## DESCRIPTION / APPLICATIONS

VS-60CPU04... series are the state of the art ultrafast recovery rectifiers designed with optimized performance of forward voltage drop and ultrafast recovery time.

The planar structure and the platinum doped life time control guarantee the best overall performance, ruggedness and reliability characteristics.

These devices are intended for use in the output rectification stage of SMPS, welding, UPS, DC/DC converters as well as freewheeling diodes in low voltage inverters, and chopper motor drives.

Their extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

## PRIMARY CHARACTERISTICS

|                       |                |
|-----------------------|----------------|
| $I_{F(AV)}$           | 2 x 30 A       |
| $V_R$                 | 400 V          |
| $V_F$ at $I_F$        | 0.92 V         |
| $t_{rr}$ typ.         | 37 ns          |
| $T_J$ max.            | 175 °C         |
| Package               | TO-247AC 3L    |
| Circuit configuration | Common cathode |

## ABSOLUTE MAXIMUM RATINGS

| PARAMETER  | SYMBOL         | TEST CONDITIONS                                   | VALUES      | UNITS |
|--|----------------|---|-------------|-------|
| Peak repetitive reverse voltage                            | $V_{RRM}$      |   | 400         | V     |
| Average rectified forward current<br>per leg<br>per device | $I_{F(AV)}$    | Rated $V_R$ , $T_C = 134$ °C                      | 30<br>60    | A     |
| Non-repetitive peak surge current per leg                  | $I_{FSM}$      | $T_J = 25$ °C, $t_p = 10$ ms                      | 300         |       |
| Peak repetitive forward current per leg                    | $I_{FM}$       | Rated $V_R$ , square wave, 20 kHz, $T_C = 134$ °C | 60          |       |
| Operating junction and storage temperatures                | $T_J, T_{Stg}$ |   | -65 to +175 | °C    |

## ELECTRICAL SPECIFICATIONS ( $T_J = 25$ °C unless otherwise specified)

| PARAMETER                              | SYMBOL        | TEST CONDITIONS                              | MIN. | TYP. | MAX. | UNITS   |
|--|---------------|--|------|------|------|---------|
| Breakdown voltage,<br>blocking voltage | $V_{BR}, V_R$ | $I_R = 100$ $\mu$ A                          | 400  | -    | -    | V       |
| Forward voltage                        | $V_F$         | $I_F = 30$ A                                 | -    | 1.10 | 1.30 |         |
|  |               | $I_F = 30$ A, $T_J = 150$ °C                 | -    | 0.92 | 1.10 |         |
|  |               | $I_F = 60$ A                                 | -    | 1.25 | 1.6  |         |
|  |               | $I_F = 60$ A, $T_J = 150$ °C                 | -    | 1.10 | 1.4  |         |
| Reverse leakage current                | $I_R$         | $V_R = V_R$ rated                            | -    | -    | 10   | $\mu$ A |
|  |               | $T_J = 150$ °C, $V_R = V_R$ rated            | -    | -    | 100  |         |
| Junction capacitance                   | $C_T$         | $V_R = 400$ V                                | -    | 40   | -    | pF      |
| Series inductance                      | $L_S$         | Measured lead to lead 5 mm from package body | -    | 12   | -    | nH      |



| DYNAMIC RECOVERY CHARACTERISTICS ( $T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified) |           |   |      |      |      |       |
|---|-----------|---|------|------|------|-------|
| PARAMETER   | SYMBOL    | TEST CONDITIONS   | MIN. | TYP. | MAX. | UNITS |
| Reverse recovery time   | $t_{rr}$  | $I_F = 1.0\text{ A}$ , $di_F/dt = 100\text{ A}/\mu\text{s}$ , $V_R = 30\text{ V}$ | -    | 37   | 40   | ns    |
|   |           | $I_F = 1.0\text{ A}$ , $di_F/dt = 50\text{ A}/\mu\text{s}$ , $V_R = 30\text{ V}$  | -    | 46   | -    |       |
|   |           | $T_J = 25\text{ }^{\circ}\text{C}$  | -    | 65   | -    |       |
|   |           | $T_J = 125\text{ }^{\circ}\text{C}$   | -    | 119  | -    |       |
| Peak recovery current   | $I_{RRM}$ | $T_J = 25\text{ }^{\circ}\text{C}$  | -    | 6.4  | -    | A     |
|   |           | $T_J = 125\text{ }^{\circ}\text{C}$   | -    | 14.7 | -    |       |
| Reverse recovery charge   | $Q_{rr}$  | $T_J = 25\text{ }^{\circ}\text{C}$  | -    | 206  | -    | nC    |
|   |           | $T_J = 125\text{ }^{\circ}\text{C}$   | -    | 874  | -    |       |

| THERMAL - MECHANICAL SPECIFICATIONS             |                   |   |              |      |            |                             |
|---|-------------------|---|--------------|------|------------|-----------------------------|
| PARAMETER                                       | SYMBOL            | TEST CONDITIONS                             | MIN.         | TYP. | MAX.       | UNITS                       |
| Maximum junction and storage temperature range  | $T_J$ , $T_{Stg}$ |   | -65          | -    | +175       | $^{\circ}\text{C}$          |
| Thermal resistance, junction to case per leg    | $R_{thJC}$        |   | -            | 0.6  | 1.0        | $^{\circ}\text{C}/\text{W}$ |
| Thermal resistance, junction to ambient per leg | $R_{thJA}$        | Typical socket mount                        | -            | -    | 40         |                             |
| Thermal resistance, case to heatsink            | $R_{thCS}$        | Mounting surface, flat, smooth, and greased | -            | 0.5  | -          |                             |
| Weight  |                   |   | -            | 6    | -          | g                           |
|   |                   |   | -            | 0.21 | -          | oz.                         |
| Mounting torque                                 |                   |   | 6.0<br>(5.0) | -    | 12<br>(10) | kgf · cm<br>(lbf · in)      |
| Marking device                                  |                   | Case style TO-247AC 3L                      | 60CPU04      |      |            |                             |




Fig. 1 - Typical Forward Voltage Drop Characteristics






Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




93189\_03

Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




93189\_04

Fig. 4 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics



93189\_05

Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current




93189\_06

Fig. 6 - Forward Power Loss Characteristics



93189\_07

Fig. 7 - Typical Reverse Recovery Time vs.  $di_F/dt$ 


93189\_08

Fig. 8 - Typical Stored Charge vs.  $di_F/dt$ 

### Note

- (1) Formula used:  $T_C = T_J - (P_d + P_{dREV}) \times R_{thJC}$ ;  
 $P_d$  = forward power loss =  $I_{F(AV)} \times V_{FM}$  at  $(I_{F(AV)}/D)$  (see fig. 6);  
 $P_{dREV}$  = inverse power loss =  $V_{R1} \times I_R (1 - D)$ ;  $I_R$  at  $V_{R1}$  = rated  $V_R$




Fig. 9 - Reverse Recovery Waveform and Definitions



**ORDERING INFORMATION TABLE**

|             |     |    |   |   |   |    |     |
|-------------|-----|----|---|---|---|----|-----|
| Device code | VS- | 60 | C | P | U | 04 | -N3 |
|             | 1   | 2  | 3 | 4 | 5 | 6  | 7   |

- |   |   |   |
|---|---|---|
| 1 | - | Vishay Semiconductors product             |
| 2 | - | Current rating (60 = 60 A)                |
| 3 | - | Circuit configuration: C = common cathode |
| 4 | - | P = TO-247AC                              |
| 5 | - | U = ultrafast rectifier                   |
| 6 | - | Voltage rating (04 = 400 V)               |
| 7 | - | Environmental digit:                      |
- N3 = halogen-free, RoHS-compliant and totally lead (Pb)-free

| ORDERING INFORMATION (Example) |                   |                        |                         |
|--------------------------------|-------------------|------------------------|-------------------------|
| PREFERRED P/N                  | QUANTITY PER TUBE | MINIMUM ORDER QUANTITY | PACKAGING DESCRIPTION   |
| VS-60CPU04-N3                  | 25                | 500                    | Antistatic plastic tube |

| LINKS TO RELATED DOCUMENTS |  |
|----------------------------|--|
| Dimensions                 | <a href="http://www.vishay.com/doc?96138">www.vishay.com/doc?96138</a> |
| Part marking information   | <a href="http://www.vishay.com/doc?95007">www.vishay.com/doc?95007</a> |
| SPIICE model               | <a href="http://www.vishay.com/doc?95398">www.vishay.com/doc?95398</a> |



## TO-247AC 3L

DIMENSIONS in millimeters and inches



| SYMBOL | MILLIMETERS |       | INCHES |       | NOTES |
|--------|-------------|-------|--------|-------|-------|
|        | MIN.        | MAX.  | MIN.   | MAX.  |       |
| A      | 4.65        | 5.31  | 0.183  | 0.209 |       |
| A1     | 2.21        | 2.59  | 0.087  | 0.102 |       |
| A2     | 1.17        | 1.37  | 0.046  | 0.054 |       |
| b      | 0.99        | 1.40  | 0.039  | 0.055 |       |
| b1     | 0.99        | 1.35  | 0.039  | 0.053 |       |
| b2     | 1.65        | 2.39  | 0.065  | 0.094 |       |
| b3     | 1.65        | 2.34  | 0.065  | 0.092 |       |
| b4     | 2.59        | 3.43  | 0.102  | 0.135 |       |
| b5     | 2.59        | 3.38  | 0.102  | 0.133 |       |
| c      | 0.38        | 0.89  | 0.015  | 0.035 |       |
| c1     | 0.38        | 0.84  | 0.015  | 0.033 |       |
| D      | 19.71       | 20.70 | 0.776  | 0.815 | 3     |
| D1     | 13.08       | -     | 0.515  | -     | 4     |

| SYMBOL | MILLIMETERS |       | INCHES    |       | NOTES |
|--------|-------------|-------|-----------|-------|-------|
|        | MIN.        | MAX.  | MIN.      | MAX.  |       |
| D2     | 0.51        | 1.35  | 0.020     | 0.053 |       |
| E      | 15.29       | 15.87 | 0.602     | 0.625 | 3     |
| E1     | 13.46       | -     | 0.53      | -     |       |
| e      | 5.46 BSC    |       | 0.215 BSC |       |       |
| Ø K    | 0.254       |       | 0.010     |       |       |
| L      | 14.20       | 16.10 | 0.559     | 0.634 |       |
| L1     | 3.71        | 4.29  | 0.146     | 0.169 |       |
| Ø P    | 3.56        | 3.66  | 0.14      | 0.144 |       |
| Ø P1   | -           | 7.39  | -         | 0.291 |       |
| Q      | 5.31        | 5.69  | 0.209     | 0.224 |       |
| R      | 4.52        | 5.49  | 0.178     | 0.216 |       |
| S      | 5.51 BSC    |       | 0.217 BSC |       |       |

## Notes

- (1) Dimensioning and tolerancing per ASME Y14.5M-1994
- (2) Contour of slot optional
- (3) Dimension D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- (5) Lead finish uncontrolled in L1
- (6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- (7) Outline conforms to JEDEC® outline TO-247 with exception of dimension Q



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.