
### Vishay Semiconductors

www.vishay.com

# Ultra fast Rectifier, 2 x 3 A FRED Pt<sup>®</sup>



PRIMARY CHARACTERISTICS					
I <sub>F(AV)</sub>	2 x 3 A				
V <sub>R</sub>	200 V				
V <sub>F</sub> at I <sub>F</sub>	0.9 V				
t <sub>rr</sub> typ.	See Recovery table				
T <sub>J</sub> max.	175 °C				
Package	DPAK (TO-252AA)				
Circuit configuration	Common cathode				

#### FEATURES

- Ultra fast recovery time
- Low forward voltage drop
- Low leakage current
- 175 °C operating junction temperature
- AEC-Q101 qualified
- Meets JESD 201 class 2 whisker test



- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

#### **DESCRIPTION / APPLICATIONS**

Vishay Semiconductors' 200 V series are the state of the art hyper fast recovery rectifiers specifically designed with optimized performance of forward voltage drop and hyper fast recovery time.

The planar structure and the platinum doped life time control, guarantee the best overall performance, ruggedness and reliability characteristics.

These devices are intended for use in the output rectification stage of SMPS, UPS, DC/DC converters as well as freewheeling diode in low voltage inverters and chopper motor drives.

Their extremely optimized stored charge and low recovery current minimize the switching losses and reduce over dissipation in the switching element and snubbers.

ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Peak repetitive reverse voltage	V <sub>RRM</sub>		200	V
Average rectified forward current per device	I <sub>F(AV)</sub>	Total device, rated V <sub>R</sub> , T <sub>C</sub> = 159 °C	6	
Non-repetitive peak surge current	I <sub>FSM</sub>		50	А
Peak repetitive forward current per diode	I <sub>FM</sub>	Rated V <sub>R</sub> , square wave, 20 kHz, T <sub>C</sub> = 159 °C	6	
Operating junction and storage temperatures	T <sub>J</sub> , T <sub>Stg</sub>		-65 to +175	°C

<b>ELECTRICAL SPECIFICATIONS</b> ( $T_J = 25 \text{ °C}$ unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS	
Breakdown voltage, blocking voltage	$V_{BR}, V_{R}$	I <sub>R</sub> = 100 μA	200	-	-		
		I <sub>F</sub> = 3 A	-	0.9	1	v	
Forward voltage	V <sub>F</sub>	I <sub>F</sub> = 3 A, T <sub>J</sub> = 125 °C	-	0.78	0.9		
		I <sub>F</sub> = 6 A	-	1	1.2		
		I <sub>F</sub> = 6 A, T <sub>J</sub> = 125 °C	-	0.89	1.08		
Deveree leekere eurrent	1	$V_{R} = V_{R}$ rated	-	-	5		
Reverse leakage current	I <sub>R</sub>	$T_J = 125 \text{ °C}, V_R = V_R \text{ rated}$	-	-	100	μA	
Junction capacitance	CT	V <sub>R</sub> = 200 V	-	12	-	pF	
Series inductance	Ls	Measured lead to lead 5 mm from package body	-	8.0	-	nH	

 Revision: 09-Dec-2019
 1
 Document Number: 94743

 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



www.vishay.com

## Vishay Semiconductors

<b>DYNAMIC RECOVERY CHARACTERISTICS</b> (T <sub>J</sub> = 25 $^{\circ}$ C unless otherwise specified)										
PARAMETER	SYMBOL	TEST	TEST CONDITIONS			MAX.	UNITS			
		I <sub>F</sub> = 1.0 A, dI <sub>F</sub>	$dt = 50 \text{ A/}\mu\text{s}, \text{V}_{\text{R}} = 30 \text{ V}$	-	20	35				
Reverse recovery time	t <sub>rr</sub>	T <sub>J</sub> = 25 °C		-	19	-	ns			
		T <sub>J</sub> = 125 °C	l <sub>F</sub> = 3 A V <sub>R</sub> = 160 V	-	26	-				
Deals receivers ourrent		T <sub>J</sub> = 25 °C		-	3.1	-	•			
Peak recovery current	I <sub>RRM</sub>	IRRM	IRRM	IRRM	T <sub>J</sub> = 125 °C	v <sub>R</sub> = 160 v dI <sub>F</sub> /dt = 200 A/µs	-	4.6	-	A
	0	T <sub>J</sub> = 25 °C		-	30	-	20			
Reverse recovery charge	Q <sub>rr</sub>	T <sub>J</sub> = 125 °C		-	60	-	nC			

THERMAL - MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNITS	
Maximum junction and storage temperature range	T <sub>J</sub> , T <sub>Stg</sub>	-65	-	175	°C	
Thermal resistance, junction to case per leg	R <sub>thJC</sub>	-	-	5	°C/W	
M. 5.14		-	0.3	-	g	
Weight		-	0.01	-	oz.	
Mounting torque		6.0 (5.0)	-	12 (10)	kgf · cm (lbf · in)	
Marking device		Case style DP	AK (TO-252AA)	6CWH	02FNH	




Fig. 1 - Maximum Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage

## VS-6CWH02FNHM3

**Vishay Semiconductors** 






Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage





Fig. 4 - Maximum Thermal Impedance ZthJC Characteristics




Revision: 09-Dec-2019

3

Document Number: 94743

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>







#### Note

- <sup>(1)</sup> Formula used:  $T_C = T_J (Pd + Pd_{REV}) \times R_{thJC}$ ;
  - Pd = forward power loss =  $I_{F(AV)} \times V_{FM}$  at ( $I_{F(AV)}/D$ ) (see fig. 6); Pd<sub>REV</sub> = inverse power loss =  $V_{R1} \times I_R$  (1 - D);  $I_R$  at  $V_{R1}$  = rated  $V_R$

## VS-6CWH02FNHM3

## **Vishay Semiconductors**




Fig. 8 - Typical Stored Charge vs. dl<sub>F</sub>/dt




Fig. 9 - Reverse Recovery Parameter Test Circuit




Fig. 10 - Reverse Recovery Waveform and Definitions

 Revision: 09-Dec-2019
 4
 Document Number: 94743

 For technical questions within your region: DiodesAmericas@vishay.com, DiodesAsia@vishay.com, DiodesEurope@vishay.com
 THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

## Vishay Semiconductors

**ORDERING INFORMATION TABLE** 

www.vishay.com

SHAY

Device code	VS-	6	с	w	н	02	FN	TRL	н	М3
		2	3	4	5	6	7	8	9	10
	<ol> <li>Vishay Semiconductors product</li> <li>Current rating (6 = 6 A)</li> <li>Center tap configuration</li> <li>Package identifier: W = DPAK</li> <li>H = hyperfast recovery</li> </ol>									
		- FN - • No	Voltage rating (02 = 200 V) FN = TO-252AA • None = tube (50 pieces) • TR = tape and reel							
	9 - 10 -	• TF • TF • H = • Env	RL = tap RR = tap AEC-Q rironmer	e and re be and re 101 qua ntal digit	eel (left eel (righ lified :	t oriente	ed)	terminat	tions lea	ad (Pb)-fr

ORDERING INFORMATION (Example)						
PREFERRED P/N	QUANTITY PER T/R	MINIMUM ORDER QUANTITY	PACKAGING DESCRIPTION			
VS-6CWH02FNHM3	75	3000	Antistatic plastic tube			
VS-6CWH02FNTRHM3	2000	2000	13" diameter reel			
VS-6CWH02FNTRRHM3	3000	3000	13" diameter reel			
VS-6CWH02FNTRLHM3	3000	3000	13" diameter reel			


LINKS TO RELATED DOCUMENTS				
Dimensions www.vishay.com/doc?95519				
Part marking information	www.vishay.com/doc?95518			
Packaging information	www.vishay.com/doc?95033			

## **Outline Dimensions**



**Vishay Semiconductors** 

# DPAK (TO-252AA)



#### Notes

<sup>(1)</sup> Dimensioning and tolerancing as per ASME Y14.5M-1994

<sup>(2)</sup> Lead dimension uncontrolled in L5

<sup>(3)</sup> Dimension D1, E1, L3 and b3 establish a minimum mounting surface for thermal pad

(4) Dimensions D and E do not include mold flash. Mold flash shall not exceed 0.127 mm (0.005") per side. These dimensions are measured at the outermost extremes of the plastic body

<sup>(5)</sup> Outline conforms to JEDEC<sup>®</sup> outline TO-252AA, except for D1 dimension



Vishay

## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.