

Insulated Gate Bipolar Transistor (Trench IGBT), 600 V, 80 A


SOT-227
FEATURES

- High speed trench gate field-stop IGBT positive temperature coefficient
- T_J maximum = 175 °C
- FRED Pt® anti-parallel diodes with ultrasoft reverse recovery
- Fully isolated package
- Very low internal inductance (≤ 5 nH typical)
- Industry standard outline
- UL approved file E78996
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


**RoHS
COMPLIANT**

PRIMARY CHARACTERISTICS	
V_{CES}	600 V
I_C DC	80 A at $T_C = 97$ °C
$V_{CE(on)}$ typical at 80 A, 25 °C	1.83 V
I_F (DC)	56 A at $T_C = 100$ °C
Speed	8 kHz to 30 kHz
Package	SOT-227
Circuit configuration	Single switch with AP diode

BENEFITS

- Designed for increased operating efficiency in power conversion: UPS, SMPS, welding, induction heating
- Easy to assemble and safe paralleling
- Direct mounting to heatsink
- Plug-in compatible with other SOT-227 packages
- Lower conduction losses and switching losses
- Low EMI, requires less snubbing

ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Collector to emitter voltage	V_{CES}		600	V
Continuous collector current	I_C	$T_C = 25$ °C	123	A
		$T_C = 90$ °C	85	
Pulsed collector current	I_{CM}		315	
Diode continuous forward current	I_F	$T_C = 25$ °C	85	
		$T_C = 90$ °C	60	
Gate-to-emitter voltage	V_{GE}		± 20	V
Power dissipation, IGBT	P_D	$T_C = 25$ °C	454	W
		$T_C = 90$ °C	258	
Power dissipation, diode	P_D	$T_C = 25$ °C	238	
		$T_C = 90$ °C	135	
Isolation voltage	V_{ISOL}	Any terminal to case, $t = 1$ min	2500	V



ELECTRICAL SPECIFICATIONS (T _J = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Collector to emitter breakdown voltage	V _{BR(CES)}	V _{GE} = 0 V, I _C = 2.0 mA	600	-	-	V
Collector to emitter voltage	V _{CE(on)}	V _{GE} = 15 V, I _C = 80 A	-	1.83	2.45	
		V _{GE} = 15 V, I _C = 80 A, T _J = 125 °C	-	2.12	-	
		V _{GE} = 15 V, I _C = 80 A, T _J = 150 °C	-	2.2	-	
Gate threshold voltage	V _{GE(th)}	V _{CE} = V _{GE} , I _C = 1.0 mA	4.6	5.6	7.5	
Temperature coefficient of threshold voltage	ΔV _{GE(th)/ΔT_J}	V _{CE} = V _{GE} , I _C = 1.0 mA (25 °C to 150 °C)	-	-18.8	-	mV/°C
Collector to emitter leakage current	I _{CES}	V _{GE} = 0 V, V _{CE} = 600 V	-	0.2	100	μA
		V _{GE} = 0 V, V _{CE} = 600 V, T _J = 125 °C	-	51	-	
		V _{GE} = 0 V, V _{CE} = 600 V, T _J = 150 °C	-	259	-	
Forward voltage drop, diode	V _{FM}	I _F = 80 A, V _{GE} = 0 V	-	1.92	3.15	V
		I _F = 80 A, V _{GE} = 0 V, T _J = 125 °C	-	1.61	-	
		I _F = 80 A, V _{GE} = 0 V, T _J = 150 °C	-	1.54	-	
Gate to emitter leakage current	I _{GES}	V _{GE} = ± 20 V	-	-	± 250	nA

SWITCHING CHARACTERISTICS (T _J = 25 °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS	
Input capacitance	C _{iss}	V _{GE} = 0 V, V _{CE} = 25 V, f = 1.0 MHz	-	10 800	-	pF	
Output capacitance	C _{oss}		-	390	-		
Reverse transfer capacitance	C _{rss}		-	220	-		
Total gate charge (turn-on)	Q _g	I _C = 80 A, V _{CC} = 480 V, V _{GE} = 15 V	-	448	-	nC	
Gate to emitter charge (turn-on)	Q _{ge}		-	76	-		
Gate to collector charge (turn-on)	Q _{gc}		-	184	-		
Turn-on switching loss	E _{on}	I _C = 80 A, V _{CC} = 300 V, V _{GE} = 15 V, R _g = 27 Ω, L = 500 μH, T _J = 25 °C	-	1.95	-	mJ	
Turn-off switching loss	E _{off}		-	1.25	-		
Total switching loss	E _{tot}		-	3.2	-		
Turn-on delay time	t _{d(on)}		Energy losses include tail and diode recovery.	-	120	-	ns
Rise time	t _r			-	90	-	
Turn-off delay time	t _{d(off)}			-	442	-	
Fall time	t _f			-	35	-	
Turn-on switching loss	E _{on}		I _C = 80 A, V _{CC} = 300 V, V _{GE} = 15 V, R _g = 27 Ω, L = 500 μH, T _J = 125 °C	-	2.3	-	mJ
Turn-off switching loss	E _{off}			-	1.43	-	
Total switching loss	E _{tot}			-	3.73	-	
Turn-on delay time	t _{d(on)}	Energy losses include tail and diode recovery.		-	124	-	ns
Rise time	t _r			-	94	-	
Turn-off delay time	t _{d(off)}			-	455	-	
Fall time	t _f	-	43	-			
Diode reverse recovery time	t _{rr}	I _F = 50 A, dI _F /dt = 200 A/μs, V _R = 200 V	-	69	-	ns	
Diode peak reverse current	I _{rr}		-	4.9	-	A	
Diode recovery charge	Q _{rr}		-	169	-	nC	
Diode reverse recovery time	t _{rr}	I _F = 50 A, dI _F /dt = 200 A/μs, V _R = 200 V, T _J = 125 °C	-	139	-	ns	
Diode peak reverse current	I _{rr}		-	12.2	-	A	
Diode recovery charge	Q _{rr}		-	856	-	nC	



THERMAL AND MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Junction temperature range	T_J		-40	-	175	°C
Storage temperature range	T_{Stg}		-40	-	150	°C
Junction-to-case	IGBT	R_{thJC}	-	-	0.33	°C/W
	Diode		-	-	0.63	
Case-to-heatsink	R_{thCS}	Flat, greased surface	-	0.1	-	
Weight			-	30	-	g
Mounting torque		Torque to terminal	-	-	1.1 (9.7)	Nm (lbf. in)
		Torque to heatsink	-	-	1.3 (11.5)	Nm (lbf. in)
Case style	SOT-227					




Fig. 1 - Typical IGBT Output Characteristics, $V_{GE} = 15V$




Fig. 3 - Maximum IGBT Continuous Collector Current vs. Case Temperature




Fig. 2 - Typical IGBT Output Characteristics, $T_J = 125^\circ C$




Fig. 4 - Collector to Emitter Voltage vs. Junction Temperature




Fig. 5 - Typical IGBT Transfer Characteristics




Fig. 8 - Typical IGBT Zero Gate Voltage Collector Current




Fig. 6 - Typical IGBT Gate Threshold Voltage




Fig. 9 - Typical Diode Forward Characteristics




Fig. 7 - IGBT Safe Operating Area




Fig. 10 - Maximum Diode Continuous Forward Current vs. Case Temperature




Fig. 11 - Typical IGBT Energy Loss vs. I_C
 $T_J = 125\text{ }^\circ\text{C}$, $V_{CC} = 300\text{ V}$, $R_g = 27\text{ }\Omega$, $V_{GE} = 15\text{ V}$, $L = 500\text{ }\mu\text{H}$




Fig. 14 - Typical IGBT Switching Time vs. R_g
 $T_J = 125\text{ }^\circ\text{C}$, $V_{CC} = 300\text{ V}$, $I_C = 80\text{ A}$, $V_{GE} = 15\text{ V}$, $L = 500\text{ }\mu\text{H}$




Fig. 12 - Typical IGBT Switching Time vs. I_C
 $T_J = 125\text{ }^\circ\text{C}$, $V_{CC} = 300\text{ V}$, $R_g = 27\text{ }\Omega$, $V_{GE} = 15\text{ V}$, $L = 500\text{ }\mu\text{H}$




Fig. 15 - Typical t_{rr} Diode vs. di_F/dt
 $V_{rr} = 200\text{ V}$, $I_F = 50\text{ A}$




Fig. 13 - Typical IGBT Energy Loss vs. R_g
 $T_J = 125\text{ }^\circ\text{C}$, $V_{CC} = 300\text{ V}$, $I_C = 80\text{ A}$, $V_{GE} = 15\text{ V}$, $L = 500\text{ }\mu\text{H}$




Fig. 16 - Typical I_{rr} Diode vs. di_F/dt
 $V_{rr} = 200\text{ V}$, $I_F = 50\text{ A}$




Fig. 17 - Typical Diode Reverse Recovery Charge vs. di_F/dt
 $V_{rr} = 200\text{ V}$, $I_F = 50\text{ A}$




Fig. 18 - Maximum Thermal Impedance Z_{thJC} Characteristics, IGBT




Fig. 19 - Maximum Thermal Impedance Z_{thJC} Characteristics, Diode

ORDERING INFORMATION TABLE

Device code	VS-	G	T	80	D	A	60	U
	①	②	③	④	⑤	⑥	⑦	⑧

- 1** - Vishay Semiconductors product
- 2** - Insulated gate bipolar transistor (IGBT)
- 3** - T = trench IGBT
- 4** - Current rating (80 = 80 A)
- 5** - Circuit configuration (D = single switch with antiparallel diode)
- 6** - Package indicator (A = SOT-227)
- 7** - Voltage rating (60 = 600 V)
- 8** - Speed / type (U = ultrafast IGBT)

CIRCUIT CONFIGURATION		
CIRCUIT	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Single switch with AP diode	D	<div style="display: inline-block; vertical-align: top; margin-left: 20px;"> <p>Lead Assignment</p> </div>

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95423
Packaging information	www.vishay.com/doc?95425



SOT-227 Generation 2

DIMENSIONS in millimeters (inches)



Note

- Controlling dimension: millimeter



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.