



“Full Bridge” IGBT MTP (TrenchStop IGBT), 57 A



MTP
(Package example)

FEATURES

- Trench and Field Stop IGBT technology
- Positive $V_{CE(on)}$ temperature coefficient
- 10 μ s short circuit capability
- HEXFRED® antiparallel diodes with ultrasoft reverse recovery
- Low diode V_F
- Square RBSOA
- Aluminum nitride DBC
- Very low stray inductance design for high speed operation
- UL approved file E78996 
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

PRIMARY CHARACTERISTICS

V_{CES}	1200 V
I_C at $T_C = 25\text{ }^\circ\text{C}$	57 A
$V_{CE(on)}$	1.84 V
Speed	8 kHz to 30 kHz
Package	MTP
Circuit configuration	Full bridge

BENEFITS

- Optimized for welding, UPS and SMPS applications
- Rugged with ultrafast performance
- Outstanding ZVS and hard switching operation
- Low EMI, requires less snubbing
- Excellent current sharing in parallel operation
- Direct mounting to heatsink
- PCB solderable terminals
- Very low junction to case thermal resistance

ABSOLUTE MAXIMUM RATINGS

PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Collector to emitter breakdown voltage	V_{CES}		1200	V
Continuous collector current	I_C	$T_C = 25\text{ }^\circ\text{C}$	57	A
		$T_C = 80\text{ }^\circ\text{C}$	42	
Pulsed collector current	I_{CM}	$T_J = 150\text{ }^\circ\text{C}$, $t_p = 6\text{ ms}$, $V_{GE} = 15\text{ V}$	50	
Clamped inductive load current	I_{LM}		75	
Diode continuous forward current	I_F	$T_C = 106\text{ }^\circ\text{C}$	25	
Diode maximum forward current	I_{FM}		100	
Gate to emitter voltage	V_{GE}		± 20	V
RMS isolation voltage	V_{ISOL}	Any terminal to case, $t = 1\text{ min}$	2500	
Maximum power dissipation (only IGBT)	P_D	$T_C = 25\text{ }^\circ\text{C}$	240	W
		$T_C = 80\text{ }^\circ\text{C}$	134	



ELECTRICAL SPECIFICATIONS (T _J = 25 °C unless otherwise noted)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Collector to emitter breakdown voltage	V _{(BR)CES}	V _{GE} = 0 V, I _C = 850 μA	1200	-	-	V
Collector to emitter saturation voltage	V _{CE(on)}	V _{GE} = 15 V, I _C = 20 A	-	1.84	2.16	V
		V _{GE} = 15 V, I _C = 40 A	-	2.60	-	
		V _{GE} = 15 V, I _C = 20 A, T _J = 125 °C	-	2.06	-	
		V _{GE} = 15 V, I _C = 40 A, T _J = 125 °C	-	3.19	-	
		V _{GE} = 15 V, I _C = 20 A, T _J = 150 °C	-	2.12	-	
Gate threshold voltage	V _{GE(th)}	V _{CE} = V _{GE} , I _C = 850 μA	4.7	5.8	6.8	
Temperature coefficient of threshold voltage	V _{GE(th)} /ΔT _J	V _{CE} = V _{GE} , I _C = 0.85 mA (25 °C to 125 °C)	-	-12.1	-	mV/°C
Transconductance	g _{fe}	V _{CE} = 20 V, I _C = 20 A	-	13	-	S
Zero gate voltage collector current	I _{CES} ⁽¹⁾	V _{GE} = 0 V, V _{CE} = 1200 V, T _J = 25 °C	-	1.0	200	μA
		V _{GE} = 0 V, V _{CE} = 1200 V, T _J = 125 °C	-	0.52	-	mA
		V _{GE} = 0 V, V _{CE} = 1200 V, T _J = 150 °C	-	2.1	-	
Gate to emitter leakage current	I _{GES}	V _{GE} = ± 20 V	-	-	± 250	nA

Note

(1) I_{CES} includes also opposite leg overall leakage

SWITCHING CHARACTERISTICS (T _J = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Total gate charge (turn-on)	Q _g	I _C = 20 A	-	119	-	nC
Gate to emitter charge (turn-on)	Q _{ge}	V _{CC} = 960 V	-	20	-	
Gate to collector charge (turn-on)	Q _{gc}	V _{GE} = 15 V	-	57	-	
Turn-on switching loss	E _{on}	V _{CC} = 600 V, I _C = 20 A, V _{GE} = 15 V, R _g = 5 Ω, L = 1 mH, T _J = 25 °C, energy losses include tail and diode reverse recovery	-	0.75	-	mJ
Turn-off switching loss	E _{off}		-	0.66	-	
Total switching loss	E _{tot}		-	1.41	-	
Turn-on switching loss	E _{on}	V _{CC} = 600 V, I _C = 20 A, V _{GE} = 15 V, R _g = 5 Ω, L = 1 mH, T _J = 125 °C, energy losses include tail and diode reverse recovery	-	1.08	-	mJ
Turn-off switching loss	E _{off}		-	1.18	-	
Total switching loss	E _{tot}		-	2.26	-	
Input capacitance	C _{ies}	V _{GE} = 0 V	-	1430	-	pF
Output capacitance	C _{oes}	V _{CC} = 30 V	-	115	-	
Reverse transfer capacitance	C _{res}	f = 1.0 MHz	-	75	-	
Reverse bias safe operating area	RBSOA	T _J = 150 °C, I _C = 75 A, V _{CC} = 900 V, V _p = 1200 V, R _g = 4.7 Ω, V _{GE} = + 15 V to 0 V, L = 500 μH	Fullsquare			
Short circuit safe operating area	SCSOA	T _J = 150 °C, V _{CC} = 800 V, V _p = 1200 V, R _g = 5 Ω, V _{GE} = +15 V to 0 V	-	-	10	μs

DIODE SPECIFICATIONS (T _J = 25 °C unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Diode forward voltage drop	V _{FM}	I _C = 20 A	-	2.48	2.94	V
		I _C = 40 A	-	3.28	-	
		I _C = 20 A, T _J = 125 °C	-	2.44	-	
		I _C = 40 A, T _J = 125 °C	-	3.45	-	
		I _C = 20 A, T _J = 150 °C	-	2.21	-	
Reverse recovery energy of the diode	E _{rec}	V _{GE} = 15 V, R _g = 5 Ω, L = 200 μH	-	420	-	μJ
Diode reverse recovery time	t _{rr}	V _{CC} = 600 V, I _C = 20 A	-	98	-	ns
Peak reverse recovery current	I _{rr}	T _J = 125 °C	-	33	-	A



THERMAL AND MECHANICAL SPECIFICATIONS						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Junction and storage temperature range	T_J, T_{Stg}		-40	-	150	°C
Junction to case	IGBT	R_{thJC}	-	-	0.52	°C/W
	Diode		-	-	0.61	
Case to sink per module	R_{thCS}		-	0.06	-	
Clearance		External shortest distance in air between 2 terminals	5.5	-	-	mm
Creepage		Shortest distance along external surface of the insulating material between 2 terminals	8	-	-	
Mounting torque		A mounting compound is recommended and the torque should be checked after 3 hours to allow for the spread of the compound. Lubricated threads.	3 ± 10 %			Nm
Weight			66			g




Fig. 1 - Typical Trench IGBT Output Characteristics, $V_{GE} = 15\text{ V}$




Fig. 3 - Maximum Trench IGBT Continuous Collector Current vs. Case Temperature




Fig. 2 - Typical Trench IGBT Output Characteristics, $T_J = 125\text{ °C}$




Fig. 4 - Typical Trench IGBT Transfer Characteristics




Fig. 5 - Typical Trench IGBT Gate Threshold Voltage




Fig. 8 - Typical Trench IGBT Switching Time vs. I_C (with Antiparallel Diode)

$T_J = 125\text{ °C}$, $V_{CC} = 600\text{ V}$, $R_g = 4.7\ \Omega$, $V_{GE} = +15\text{V}/-15\text{V}$, $L = 500\ \mu\text{H}$




Fig. 6 - Typical Trench IGBT Zero Gate Voltage Collector Current




Fig. 9 - Typical Trench IGBT Energy Loss vs. R_g (with Antiparallel Diode)

$T_J = 125\text{ °C}$, $V_{CC} = 600\text{ V}$, $I_C = 20\text{ A}$, $V_{GE} = +15\text{V}/-15\text{V}$, $L = 500\ \mu\text{H}$




Fig. 7 - Typical Trench IGBT Energy Loss vs. I_C (with Antiparallel Diode)

$T_J = 125\text{ °C}$, $V_{CC} = 600\text{ V}$, $R_g = 4.7\ \Omega$, $V_{GE} = +15\text{V}/-15\text{V}$, $L = 500\ \mu\text{H}$




Fig. 10 - Typical Trench IGBT Switching Time vs. R_g (with Antiparallel Diode)

$T_J = 125\text{ °C}$, $V_{CC} = 600\text{ V}$, $I_C = 20\text{ A}$, $V_{GE} = +15\text{V}/-15\text{V}$, $L = 500\ \mu\text{H}$




Fig. 11 - Typical Trench IGBT Gate charge vs. Gate to Emitter Voltage




Fig. 14 - Typical Diode I_{rr} vs. R_g
 $T_J = 150\text{ }^\circ\text{C}$; $I_F = 5.0\text{ A}$




Fig. 12 - Typical Diode Forward Characteristics
 $t_p = 80\text{ }\mu\text{s}$




Fig. 15 - Typical Diode I_{rr} vs. di_F/dt
 $V_{CC} = 400\text{ V}$; $V_{GE} = 15\text{ V}$; $I_{CE} = 5.0\text{ A}$; $T_J = 150\text{ }^\circ\text{C}$




Fig. 13 - Typical Diode I_{rr} vs. I_F ,
 $T_J = 150\text{ }^\circ\text{C}$




Fig. 16 - Typical Diode Q_{rr} vs. di_F/dt
 $V_{CC} = 400\text{ V}$; $V_{GE} = 15\text{ V}$; $T_J = 150\text{ }^\circ\text{C}$




Fig. 17 - Trench IGBT Reverse BIAS SOA
 $T_J = 150\text{ }^\circ\text{C}$, $I_C = 75\text{ A}$, $R_g = 4.7\ \Omega$, $V_{GE} = +15\text{V}/0\text{ V}$, $V_{CC} = 700\text{ V}$,
 $V_p = 1200\text{ V}$




Fig. 18 - Trench IGBT Safe Operating Area




Fig. 19 - Maximum Trench IGBT Thermal Impedance Z_{thJC} Characteristics




Fig. 20 - Maximum Diode Thermal Impedance Z_{thJC} Characteristics




Fig. 21 - Gate Charge Circuit (Turn-Off)




Fig. 23 - S.C. SOA Circuit




Fig. 22 - RBSOA Circuit





Fig. 24 - Switching Loss Circuit

ORDERING INFORMATION TABLE

Device code	VS-	20	MT	120	P	F	P
	①	②	③	④	⑤	⑥	⑦
①	-	Vishay Semiconductors product					
②	-	Current rating (20 = 20 A)					
③	-	Essential part number					
④	-	Voltage code (120 = 1200 V)					
⑤	-	Speed / type (P = Trench IGBT)					
⑥	-	Circuit configuration (F = full bridge)					
⑦	-	P = lead (Pb)-free					



CIRCUIT CONFIGURATION




LINKS TO RELATED DOCUMENTS

Dimensions	www.vishay.com/doc?95245
------------	--



MTP MOSFET / IGBT Full-Bridge

DIMENSIONS in millimeters



Tolerance (unless other stated):

X = ± 0.3

X.X = ± 0.1

X.XX = ± 0.03



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.