



Thyristor High Voltage, Phase Control SCR, 100 A



TO-247AD 3L



FEATURES

- AEC-Q101 qualified, meets JESD 201 class 1A whisker test
- 150 °C maximum operating junction temperature
- Material categorization:
for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

Typical usage is in input rectification crowbar (soft start) and AC switch motor control, UPS, welding, and battery charge.

DESCRIPTION

The VS-100TPS12L high voltage series of silicon controlled rectifiers are specifically designed for medium power switching, and phase control applications. The glass passivation technology used, has reliable operation up to 150 °C junction temperature.

MECHANICAL DATA

Case: TO-247AD 3L

Molding compound meets UL 94 V-0 flammability rating

Terminals: matte tin plated leads, solderable per J-STD-002

LINKS TO ADDITIONAL RESOURCES



3D Models

| PRIMARY CHARACTERISTICS | |
|-------------------------|-------------------|
| $I_{T(AV)}$ | 100 A |
| V_{DRM}/V_{RRM} | 1200 V |
| V_{TM} (typ.) | 1.17 V |
| I_{GT} | 100 mA |
| T_J | -40 °C to +150 °C |
| Package | TO-247AD 3L |
| Circuit configuration | Single SCR |

| MAJOR RATINGS AND CHARACTERISTICS | | | | |
|--|-------------------|--------------------------------|-------------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | VALUES | UNITS |
| Peak repetitive reverse voltage | V_{RRM}/V_{DRM} | | 1200 | V |
| On-state voltage | V_T | 100 A, $T_J = 125$ °C, typical | 1.17 | |
| Average rectified forward current | $I_{T(AV)}$ | | 100 | A |
| Maximum continuous RMS on-state current | I_{RMS} | | 157 | |
| Non-repetitive peak surge current | I_{TSM} | $T_J = 150$ °C, 10 ms sine | 935 | |
| Maximum rate of rise | dV/dt | | 1000 | V/μs |
| Maximum operating junction and storage temperature range | T_J, T_{Stg} | | -40 to +150 | °C |

| VOLTAGE RATINGS | | | |
|-----------------|--|--|--|
| PART NUMBER | V_{RRM}/V_{DRM} , MAXIMUM REPETITIVE PEAK AND OFF-STATE VOLTAGE V | V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V | TYP. I_{RRM}/I_{DRM} AT 150 °C mA |
| VS-100TPS12L-M3 | 1200 | 1300 | 28 |



| ABSOLUTE MAXIMUM RATINGS | | | | | | |
|--|-------------------|--|--|------|--------|-------------------|
| PARAMETER | SYMBOL | TEST CONDITIONS | | TYP. | MAX. | UNITS |
| Maximum average on-state current | $I_{T(AV)}$ | $T_C = 103\text{ }^\circ\text{C}$, 180° conduction half sine wave | | - | 100 | A |
| Maximum continuous RMS on-state current as AC switch | $I_{T(RMS)}$ | | | - | 157 | |
| Peak, one-cycle non-repetitive surge current | I_{TSM} | 10 ms sine pulse, rated V_{RRM} applied | | - | 790 | A ² s |
| | | 10 ms sine pulse, no voltage reapplied | | - | 935 | |
| I^2t for fusing | I^2t | 10 ms sine pulse, rated V_{RRM} applied | | - | 3090 | |
| | | 10 ms sine pulse, no voltage reapplied | | - | 4370 | |
| $I^2\sqrt{t}$ for fusing | $I^2\sqrt{t}$ | $t = 0.1\text{ ms to }10\text{ ms}$, no voltage reapplied, $T_J = 150\text{ }^\circ\text{C}$ | | - | 43 700 | A ² √s |
| On-state voltage | V_T | 100 A, $T_J = 25\text{ }^\circ\text{C}$ | | 1.22 | 1.37 | V |
| | | 190 A, $T_J = 25\text{ }^\circ\text{C}$ | | 1.45 | 1.61 | |
| | | 100 A, $T_J = 125\text{ }^\circ\text{C}$ | | 1.17 | 1.26 | |
| | | 190 A, $T_J = 125\text{ }^\circ\text{C}$ | | 1.47 | 1.60 | |
| Low level value of threshold voltage | V_{T01} | $T_J = 150\text{ }^\circ\text{C}$ | | - | 0.82 | V |
| High level value of threshold voltage | V_{T02} | | | - | 0.93 | |
| Low level value of on-state slope resistance | r_{t1} | $T_J = 150\text{ }^\circ\text{C}$ | | - | 3.80 | mΩ |
| High level value of on-state slope resistance | r_{t2} | | | - | 3.50 | |
| Rate of rise of turned-on current | di/dt | $T_J = 150\text{ }^\circ\text{C}$, $V_R < 800\text{ V}$, $I_T = 100\text{ A}$, $I_{gt} = 200\text{ mA}$, $t_r < 100\text{ ns}$, repetitive | | - | 200 | A/μs |
| Rate of rise of turned-on current | di/dt | $T_J = 150\text{ }^\circ\text{C}$, $V_R < 1000\text{ V}$, $I_T = 100\text{ A}$, $I_{gt} = 200\text{ mA}$, $t_r < 100\text{ ns}$, non repetitive | | - | 500 | A/μs |
| Holding current | I_H | Anode supply = 6 V, resistive load, $T_J = 25\text{ }^\circ\text{C}$ | | - | 300 | mA |
| Latching current | I_L | | | - | 500 | |
| Reverse and direct leakage current | I_{RRM}/I_{DRM} | $T_J = 25\text{ }^\circ\text{C}$ | | 30 | 100 | μA |
| | | $T_J = 125\text{ }^\circ\text{C}$ | | 10 | 50 | mA |
| | | $T_J = 150\text{ }^\circ\text{C}$ | | 28 | 70 | |
| Rate of rise of off-state voltage | dV/dt | $T_J = T_J\text{ maximum}$, linear to 80 % V_{DRM} , $R_{g-k} = \text{open}$ | | - | 1000 | V/μs |

| TRIGGERING | | | | | | |
|-------------------------------------|-------------|---|-----------------------------------|------|------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | | TYP. | MAX. | UNITS |
| Peak gate power | P_{GM} | 10 ms sine pulse, no voltage reapplied | | - | 10 | W |
| Average gate power | $P_{G(AV)}$ | | | - | 2.5 | |
| Peak gate current | I_{GM} | | | - | 2.5 | A |
| Peak negative gate voltage | $-V_{GM}$ | | | - | 10 | V |
| Required DC gate voltage to trigger | V_{GT} | $T_J = -40\text{ }^\circ\text{C}$ | Anode supply = 6 V resistive load | 1.2 | 1.7 | |
| | | $T_J = 25\text{ }^\circ\text{C}$ | Anode supply = 6 V resistive load | 1.0 | 1.5 | |
| | | $T_J = 125\text{ }^\circ\text{C}$ | Anode supply = 6 V resistive load | 0.7 | 1.3 | |
| | | $T_J = 150\text{ }^\circ\text{C}$ | Anode supply = 6 V resistive load | 0.6 | 1.1 | |
| Required DC gate to trigger | I_{GT} | $T_J = -40\text{ }^\circ\text{C}$ | Anode supply = 6 V resistive load | 80 | 150 | mA |
| | | $T_J = 25\text{ }^\circ\text{C}$ | Anode supply = 6 V resistive load | 60 | 100 | |
| | | $T_J = 125\text{ }^\circ\text{C}$ | Anode supply = 6 V resistive load | 25 | 50 | |
| | | $T_J = 150\text{ }^\circ\text{C}$ | Anode supply = 6 V resistive load | 17 | 35 | |
| DC gate voltage not to trigger | V_{GD} | $T_J = 150\text{ }^\circ\text{C}$, $V_{DRM} = 80\text{ }^\circ\text{ rated value}$ | | - | 0.20 | V |
| DC gate current not to trigger | I_{GD} | | | - | 3.0 | mA |

| SWITCHING | | | | | | |
|---------------|----------|---|--|------|------|-------|
| PARAMETER | SYMBOL | TEST CONDITIONS | | TYP. | MAX. | UNITS |
| Turn-on time | t_{gt} | $I_T = 100\text{ A}$, $V_D = 50\text{ }^\circ\text{ }V_{DRM}$, $I_{gt} = 300\text{ mA}$, $T_J = 25\text{ }^\circ\text{C}$ | | 1.8 | - | μs |
| Turn-off time | t_q | $I_T = 100\text{ A}$, $V_D = 80\text{ }^\circ\text{ }V_{DRM}$, $dV/dt = 20\text{ V}/\mu\text{s}$, $t_p = 200\text{ }^\circ\text{ }μ\text{s}$, $I_{gt} = 100\text{ mA}$, $di/dt = 10\text{ A}/\mu\text{s}$, $V_R = 100\text{ V}$, $T_J = 150\text{ }^\circ\text{C}$ | | 135 | - | |



| ΔR_{thJ-HS} CONDUCTION PER JUNCTION | | | | | | | | | | | |
|---|---------------------------|-------|-------|-------|-------|-----------------------------|-------|-------|-------|-------|-------|
| DEVICE | SINE HALF-WAVE CONDUCTION | | | | | RECTANGULAR WAVE CONDUCTION | | | | | UNITS |
| | 180° | 120° | 90° | 60° | 30° | 180° | 120° | 90° | 60° | 30° | |
| VS-100TPS12L-M3 | 0.032 | 0.047 | 0.042 | 0.044 | 0.046 | 0.030 | 0.039 | 0.041 | 0.044 | 0.046 | °C/W |

| THERMAL AND MECHANICAL SPECIFICATIONS | | | | | |
|--|----------------|---------------------------------------|------------|------|------------------------|
| PARAMETER | SYMBOL | TEST CONDITIONS | MIN. | MAX. | UNITS |
| Maximum operating junction and storage temperature range | T_J, T_{Stg} | | -40 | 150 | °C |
| Maximum thermal resistance, junction to case | R_{thJC} | | - | 0.25 | °C/W |
| Maximum thermal resistance, junction to ambient | R_{thJA} | | - | 40 | |
| Typical thermal resistance, case to heatsink | R_{thCS} | Mounting surface, smooth, and greased | 0.20 | | |
| Approximate weight | | | 6 | | g |
| Mounting torque | minimum | | 6 (5) | | kgf · cm (lbf · in) |
| | maximum | | 12 (10) | | |
| Marking device | | Case style TO-247AD 3L | 100TPS12LH | | |




Fig. 1 - Current Rating Characteristics




Fig. 3 - On-State Power Loss Characteristics




Fig. 2 - Current Rating Characteristics




Fig. 4 - On-State Power Loss Characteristic




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - On-State Voltage Drop Characteristics





Fig. 8 - Thermal Impedance Z_{thJC} Characteristics



ORDERING INFORMATION TABLE



- 1** - Vishay Semiconductors product
- 2** - Current code (100 = 100 A)
- 3** - Circuit configuration:
T = thyristor
- 4** - P = TO-247 package
- 5** - Type of silicon:
S = standard recovery rectifier
- 6** - Voltage code (12 = 1200 V)
- 7** - Package L = long lead
- 8** - H = AEC-Q101 qualified
- 9** - M3 = halogen-free, RoHS-compliant, and terminations lead (Pb)-free

| ORDERING INFORMATION (example) | | | |
|--------------------------------|-------------------|------------------------|--------------------------|
| PREFERRED P/N | QUANTITY PER TUBE | MINIMUM ORDER QUANTITY | PACKAGING DESCRIPTION |
| VS-100TPS12LHM3 | 25 | 500 | Antistatic plastic tubes |

| LINKS TO RELATED DOCUMENTS | |
|----------------------------|--|
| Dimensions | www.vishay.com/doc?95626 |
| Part marking information | www.vishay.com/doc?95007 |

TO-247AD 3L

DIMENSIONS in millimeters and inches



| SYMBOL | MILLIMETERS | | INCHES | | NOTES | SYMBOL | MILLIMETERS | | INCHES | | NOTES |
|--------|-------------|-------|--------|-------|-------|--------|-------------|-------|-----------|-------|-------|
| | MIN. | MAX. | MIN. | MAX. | | | MIN. | MAX. | MIN. | MAX. | |
| A | 4.65 | 5.31 | 0.183 | 0.209 | | D2 | 0.51 | 1.30 | 0.020 | 0.051 | |
| A1 | 2.21 | 2.59 | 0.087 | 0.102 | | E | 15.29 | 15.87 | 0.602 | 0.625 | 3 |
| A2 | 1.50 | 2.49 | 0.059 | 0.098 | | E1 | 13.46 | - | 0.53 | - | |
| b | 0.99 | 1.40 | 0.039 | 0.055 | | e | 5.46 BSC | | 0.215 BSC | | |
| b1 | 0.99 | 1.35 | 0.039 | 0.053 | | Ø K | 0.254 | | 0.010 | | |
| b2 | 1.65 | 2.39 | 0.065 | 0.094 | | L | 19.81 | 20.32 | 0.780 | 0.800 | |
| b3 | 1.65 | 2.34 | 0.065 | 0.092 | | L1 | 3.71 | 4.29 | 0.146 | 0.169 | |
| b4 | 2.59 | 3.43 | 0.102 | 0.135 | | Ø P | 3.56 | 3.66 | 0.14 | 0.144 | |
| b5 | 2.59 | 3.38 | 0.102 | 0.133 | | Ø P1 | - | 6.98 | - | 0.275 | |
| c | 0.38 | 0.89 | 0.015 | 0.035 | | Q | 5.31 | 5.69 | 0.209 | 0.224 | |
| c1 | 0.38 | 0.84 | 0.015 | 0.033 | | R | 4.52 | 5.49 | 0.178 | 0.216 | |
| D | 19.71 | 20.70 | 0.776 | 0.815 | 3 | S | 5.51 BSC | | 0.217 BSC | | |
| D1 | 13.08 | - | 0.515 | - | 4 | | | | | | |

Notes

- (1) Dimensioning and tolerancing per ASME Y14.5M-1994
- (2) Contour of slot optional
- (3) Dimension D and E do not include mold flash. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- (5) Lead finish uncontrolled in L1
- (6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- (7) Outline conforms to JEDEC® outline TO-247 with exception of dimension A min., D, E min., Q min., S, and note 4



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.