

# SOT-227 Power Module Single Switch - Silicon Carbide Power MOSFET 100 A



SOT-227

## FEATURES

- High blocking voltage with low on-resistance
- High speed switching with low capacitance
- Soft body diode with low reverse recovery
- Maximum 175 °C junction temperature
- UL approved file E78996 
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT

## APPLICATIONS

- EV chargers
- Server and telecom PSU
- UPS
- Solar Inverters
- SMPS
- DC/DC converters

## PRIMARY CHARACTERISTICS

|                       |                    |
|-----------------------|--------------------|
| $V_{DSS}$             | 1200 V             |
| $R_{DS(on)}$ at 100 A | 23 mΩ              |
| $I_D$                 | 76 A at 90 °C      |
| Type                  | SiC MOSFET Modules |
| Package               | SOT-227            |

## DESCRIPTION

This is an high performance silicon carbide MOSFET. The high blocking voltage with low on-resistance, high speed switching with low capacitance make this MOSFET ideal for high frequency switching application including solar inverters and EV chargers.

## ABSOLUTE MAXIMUM RATINGS

| PARAMETER                                  | SYMBOL         | TEST CONDITIONS                          | MAX.        | UNITS |
|--------------------------------------------|----------------|------------------------------------------|-------------|-------|
| <b>MOSFET</b>                              |                |                                          |             |       |
| Drain to source voltage                    | $V_{DSS}$      |                                          | 1200        | V     |
| Continuous drain current, $V_{GS}$ at 15 V | $I_D$          | $T_C = 25\text{ °C}$                     | 98          | A     |
|                                            |                | $T_C = 90\text{ °C}$                     | 76          |       |
| Pulsed drain current                       | $I_{DM}^{(1)}$ |                                          | 200         |       |
| Power dissipation                          | $P_D$          | $T_C = 25\text{ °C}$                     | 468         | W     |
| Gate to source voltage                     | $V_{GS}$       |                                          | -8 / +19    | V     |
| <b>MODULE</b>                              |                |                                          |             |       |
| Operating junction temperature range       | $T_J$          |                                          | -55 to +175 | °C    |
| Operating storage temperature range        | $T_{Stg}$      |                                          | -40 to +150 |       |
| Insulation voltage (RMS)                   | $V_{ISOL}$     | any terminal to case, $t = 1\text{ min}$ | 2500        | V     |

### Note

<sup>(1)</sup> Limited at max. junction temperature

## RECOMMENDED OPERATING CONDITIONS

| PARAMETER                                   | SYMBOL       | RATING   | UNITS |
|---------------------------------------------|--------------|----------|-------|
| Recommended operating gate - source voltage | $V_{GS(op)}$ | -4 / +15 | V     |

**THERMAL AND MECHANICAL SPECIFICATIONS**

| PARAMETER                            | SYMBOL     | TEST CONDITIONS       | MIN.    | TYP. | MAX.       | UNITS        |
|--------------------------------------|------------|-----------------------|---------|------|------------|--------------|
| Operating junction temperature range | $T_J$      |                       | -55     | -    | 175        | °C           |
| Operating storage temperature range  | $T_{Stg}$  |                       | -40     | -    | 150        |              |
| Junction to case MOSFET              | $R_{thJC}$ |                       | -       | -    | 0.32       | °C/W         |
| Case to heatsink Module              | $R_{thCS}$ | Flat, greased surface | -       | 0.1  | -          |              |
| Weight                               |            |                       | -       | 30   | -          | g            |
| Mounting torque                      |            | Torque to terminal    | -       | -    | 1.1 (9.7)  | Nm (lbf. in) |
|                                      |            | Torque to heatsink    | -       | -    | 1.8 (15.9) | Nm (lbf. in) |
| Case style                           |            |                       | SOT-227 |      |            |              |

**ELECTRICAL CHARACTERISTICS** ( $T_J = 25\text{ °C}$  unless otherwise specified)

| PARAMETER                                    | SYMBOL                          | TEST CONDITIONS                                                                                                                                        | MIN. | TYP.  | MAX. | UNITS |
|----------------------------------------------|---------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|------|-------|------|-------|
| Drain to source breakdown voltage            | $V_{(BR)DSS}$                   | $V_{GS} = 0\text{ V}$ , $I_D = 200\text{ }\mu\text{A}$                                                                                                 | 1200 | -     | -    | V     |
| Breakdown voltage temperature coefficient    | $\Delta V_{(BR)DSS}/\Delta T_J$ | $I_D = 200\text{ }\mu\text{A}$ (25 °C to 125 °C)                                                                                                       | -    | 0.4   | -    | V/°C  |
| Static drain to source on-resistance         | $R_{DS(on)}$                    | $V_{GS} = 15\text{ V}$ , $I_D = 100\text{ A}$                                                                                                          | -    | 23    | 32.6 | mΩ    |
|                                              |                                 | $V_{GS} = 15\text{ V}$ , $I_D = 100\text{ A}$ , $T_J = 175\text{ °C}$                                                                                  | -    | 43    | -    |       |
| Gate threshold voltage                       | $V_{GS(th)}$                    | $V_{DS} = V_{GS}$ , $I_D = 14.22\text{ mA}$                                                                                                            | 1.7  | 2.61  | 3.7  | V     |
|                                              |                                 | $V_{DS} = V_{GS}$ , $I_D = 14.22\text{ mA}$ , $T_J = 150\text{ °C}$                                                                                    | -    | 2.26  | -    |       |
| Temperature coefficient of threshold voltage | $\Delta V_{GS(th)}/\Delta T_J$  | $V_{DS} = V_{GS}$ , $I_D = 14.22\text{ mA}$ (25 °C to 125 °C)                                                                                          | -    | -2.7  | -    | mV/°C |
| Forward transconductance                     | $g_{fs}$                        | $V_{DS} = 20\text{ V}$ , $I_D = 100\text{ A}$                                                                                                          | -    | 57    | -    | S     |
| Drain to source leakage current              | $I_{DSS}$                       | $V_{DS} = 1200\text{ V}$ , $V_{GS} = 0\text{ V}$                                                                                                       | -    | 0.6   | 100  | μA    |
|                                              |                                 | $V_{DS} = 1200\text{ V}$ , $V_{GS} = 0\text{ V}$ , $T_J = 150\text{ °C}$                                                                               | -    | 2.2   | -    |       |
| Gate to source leakage                       | $I_{GSS}$                       | $V_{GS} = 15\text{ V}$                                                                                                                                 | -    | -     | 250  | nA    |
| Total gate charge                            | $Q_g$                           | $I_D = 50\text{ A}$ ,<br>$V_{DS} = 800\text{ V}$ ,<br>$V_{GS} = -4\text{ V} / +15\text{ V}$                                                            | -    | 168   | -    | nC    |
| Gate to source charge                        | $Q_{gs}$                        |                                                                                                                                                        | -    | 38    | -    |       |
| Gate to drain ("Miller") charge              | $Q_{gd}$                        |                                                                                                                                                        | -    | 69    | -    |       |
| Turn-on switching energy                     | $E_{on}$                        | $V_{DD} = 800\text{ V}$ ,<br>$I_D = 100\text{ A}$ ,<br>$R_g = 2.2\text{ }\Omega$ ,<br>$V_{GS} = -4\text{ V} / +15\text{ V}$                            | -    | 1.709 | -    | mJ    |
| Turn-off switching energy                    | $E_{off}$                       |                                                                                                                                                        | -    | 0.998 | -    |       |
| Turn-on delay time                           | $t_{d(on)}$                     |                                                                                                                                                        | -    | 18.88 | -    | ns    |
| Rise time                                    | $t_r$                           |                                                                                                                                                        | -    | 44.32 | -    |       |
| Turn-off delay time                          | $t_{d(off)}$                    |                                                                                                                                                        | -    | 36    | -    |       |
| Fall time                                    | $t_f$                           |                                                                                                                                                        | -    | 10.56 | -    |       |
| Turn-on switching energy                     | $E_{on}$                        | $V_{DD} = 800\text{ V}$ ,<br>$I_D = 100\text{ A}$ ,<br>$R_g = 2.2\text{ }\Omega$ ,<br>$V_{GS} = -4\text{ V} / +15\text{ V}$ ,<br>$T_J = 125\text{ °C}$ | -    | 1.208 | -    | mJ    |
| Turn-off switching energy                    | $E_{off}$                       |                                                                                                                                                        | -    | 1.036 | -    |       |
| Turn-on delay time                           | $t_{d(on)}$                     |                                                                                                                                                        | -    | 18.4  | -    | ns    |
| Rise time                                    | $t_r$                           |                                                                                                                                                        | -    | 30.56 | -    |       |
| Turn-off delay time                          | $t_{d(off)}$                    |                                                                                                                                                        | -    | 39.68 | -    |       |
| Fall time                                    | $t_f$                           |                                                                                                                                                        | -    | 10.56 | -    |       |
| Input capacitance                            | $C_{iss}$                       | $V_{GS} = 0\text{ V}$ ,<br>$V_{DS} = 1000\text{ V}$ ,<br>$f = 100\text{ kHz}$                                                                          | -    | 4638  | -    | pF    |
| Output capacitance                           | $C_{oss}$                       |                                                                                                                                                        | -    | 82    | -    |       |
| Reverse transfer capacitance                 | $C_{rss}$                       |                                                                                                                                                        | -    | 18    | -    |       |

**SOURCE-DRAIN RATINGS AND CHARACTERISTICS** ( $T_J = 25\text{ }^{\circ}\text{C}$  unless otherwise specified)

| PARAMETER                          | SYMBOL    | TEST CONDITIONS                                                                                                              | MIN. | TYP.  | MAX. | UNITS |
|------------------------------------|-----------|------------------------------------------------------------------------------------------------------------------------------|------|-------|------|-------|
| Pulsed source current (body diode) | $I_{SM}$  | 10 ms sine or 6 ms rectangular pulse, $T_J = 175\text{ }^{\circ}\text{C}$                                                    | -    | -     | 216  | A     |
| Diode forward voltage              | $V_{SD}$  | $I_S = 100\text{ A}$ , $V_{GS} = 0\text{ V}$                                                                                 | -    | 5.68  | 6.05 | V     |
| Reverse recovery time              | $t_{rr}$  | $T_J = 25\text{ }^{\circ}\text{C}$ , $I_F = I_S = 100\text{ A}$ , $dI/dt = 7920\text{ A}/\mu\text{s}$ , $V_R = 800\text{ V}$ | -    | 16.96 | -    | ns    |
| Reverse recovery charge            | $Q_{rr}$  |                                                                                                                              | -    | 196   | -    | nC    |
| Reverse recovery current           | $I_{RRM}$ |                                                                                                                              | -    | 32    | -    | A     |




Fig. 1 - Max. Continuous Drain Current vs. Case Temperature





Fig. 3 - Typical Drain to Source Current Output Characteristics at  $T_J = 150\text{ }^{\circ}\text{C}$ 

Fig. 2 - Typical Drain to Source Current Output Characteristics at  $T_J = 25\text{ }^{\circ}\text{C}$ 


Fig. 4 - Normalized Drain-to-Source On-Resistance vs. Temperature




Fig. 5 - Typical Drain-to-Source On-Resistance vs. Gate to Source Voltage




Fig. 8 - Typical Zero Gate Voltage Drain Current




Fig. 6 - Typical Transfer Characteristics




Fig. 9 - Typical Gate Charge vs. Gate to Source Voltage




Fig. 7 - Typical Gate Threshold Voltage Characteristics










Fig. 10 - Typical Turn-On Energy Loss vs.  $I_D$


Fig. 11 - Typical Turn-On Energy Loss vs.  $R_g$ 

Fig. 14 - Typical Turn-On Switching Time vs.  $I_D$ 

Fig. 12 - Typical Turn-Off Energy Loss vs.  $I_D$ 

Fig. 15 - Typical Turn-On Switching Time vs.  $R_g$ 

Fig. 13 - Typical Turn-Off Energy Loss vs.  $R_g$ 

Fig. 16 - Typical Turn-Off Switching Time vs.  $I_D$




Fig. 17 - Typical Turn-Off Switching Time vs.  $R_g$ 


Fig. 20 - Normalized Body Diode Source-to-Drain vs. Temperature




Fig. 18 - Capacitance vs. Drain-to-Source Voltage




Fig. 21 - Safe Operating Area




Fig. 19 - Typical Body Diode Source-to-Drain Current Characteristics





Fig. 22 - Reverse BIAS Safe Operating Area


Fig. 23 - Maximum Thermal Impedance  $Z_{thJC}$  Characteristics

### ORDERING INFORMATION TABLE

Device code

| VS- | SF | 100 | S | A | 120 |
|-----|----|-----|---|---|-----|
| ①   | ②  | ③   | ④ | ⑤ | ⑥   |


- 1** - Vishay Semiconductors product
- 2** - SF = SiC MOSFET module
- 3** - Current rating (100 = 100 A)
- 4** - Circuit configuration (S = single switch)
- 5** - Package indicator (SOT-227)
- 6** - Voltage rating (120 = 1200 V)

### CIRCUIT CONFIGURATION

| CIRCUIT       | CIRCUIT CONFIGURATION CODE | CIRCUIT DRAWING |
|---------------|----------------------------|-----------------|
| Single switch | S                          |                 |




**DIMENSIONS** in millimeters



## SOT-227 Generation 2

**DIMENSIONS** in millimeters (inches)



### Note

- Controlling dimension: millimeter



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.