



650 V Gen 4 Power Silicon Carbide Schottky Diode, 2 x 30 A



FEATURES

- Positive V_F temperature coefficient for easy paralleling
- Virtually no recovery tail and no switching losses
- Temperature invariant switching behavior
- 175 °C maximum operating junction temperature
- AEC-Q101 qualified, meets JESD 201 class 2 whisker test
- Solder bath temperature 275 °C maximum, 10 s per JESD 22-B106
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

LINKS TO ADDITIONAL RESOURCES



3D Models

PRIMARY CHARACTERISTICS

I_F	2 x 30 A
V_R	650 V
V_F at I_F at 25 °C, typ.	1.33 V
T_J max.	175 °C
I_R at V_R at 175 °C	125 μ A
Q_C ($V_R = 400$ V)	78 nC
Package	TO-247AD 3L
Circuit configuration	Common cathode

DESCRIPTION / APPLICATIONS

Wide band gap SiC based 650 V Schottky diode, designed for high performance and ruggedness.

Optimized for extreme high-speed hard switching across a wide temperature range. This SiC diode is ideal for demanding applications such as high efficiency PFC diodes and ultra-high frequency output rectifiers in AC/DC and DC/DC converters.

MECHANICAL DATA

Case: TO-247AD 3L

Molding compound meets UL 94 V-0 flammability rating
Base P/N HM3 - halogen-free, RoHS-compliant, and AEC-Q101 qualified

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

Mounting torque: 10 in-lbs maximum

MAXIMUM RATINGS ($T_A = 25$ °C unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Peak repetitive reverse voltage per leg	V_{RRM}		650	V
Continuous forward current per leg	$I_F^{(1)}$	$T_C = 148$ °C (DC)	30	A
	$I_F^{(2)}$	$T_C = 140$ °C (DC)	30	A
DC blocking voltage per leg	V_{DC}		650	V
Repetitive peak forward current per leg	I_{FRM}	$T_C = 25$ °C, $f = 50$ Hz, square wave, DC = 25 %	126	A
Non-repetitive peak forward surge current per leg	I_{FSM}	$T_C = 25$ °C, $t_p = 10$ ms, half sine wave	180	A
		$T_C = 110$ °C, $t_p = 10$ ms, half sine wave	160	
Power dissipation per leg	$P_{tot}^{(1)}$	$T_C = 25$ °C	273	W
		$T_C = 110$ °C	118	
	$P_{tot}^{(2)}$	$T_C = 25$ °C	200	W
		$T_C = 110$ °C	87	
I^2t value per leg	$\int i^2 dt$	$T_C = 25$ °C	162	A ² s
		$T_C = 110$ °C	128	
Operating junction and storage temperatures	$T_J^{(3)}, T_{Stg}$		-55 to +175	°C

Notes

(1) Based on typical R_{th}

(2) Based on maximum R_{th}

(3) The heat generated must be less than the thermal conductivity from junction-to-ambient: $dP_D/dT_J < 1/R_{\theta JA}$

**ELECTRICAL SPECIFICATIONS** ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Forward voltage per leg	V_F	$I_F = 30\text{ A}$	-	1.33	1.5	V
		$I_F = 30\text{ A}, T_J = 150\text{ }^{\circ}\text{C}$	-	1.5	1.75	
		$I_F = 30\text{ A}, T_J = 175\text{ }^{\circ}\text{C}$	-	1.60	-	
Reverse leakage current per leg	I_R	$V_R = V_R\text{ rated}$	-	7.0	200	μA
		$V_R = V_R\text{ rated}, T_J = 150\text{ }^{\circ}\text{C}$	-	60	400	
		$V_R = V_R\text{ rated}, T_J = 175\text{ }^{\circ}\text{C}$	-	125	-	
Total capacitance per leg	C	$V_R = 1\text{ V}, f = 1\text{ MHz}$	-	1315	-	pF
		$V_R = 400\text{ V}, f = 1\text{ MHz}$	-	110	-	
Total capacitive charge per leg	Q_C	$V_R = 400\text{ V}, f = 1\text{ MHz}$	-	78	-	nC

THERMAL - MECHANICAL SPECIFICATIONS ($T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

PARAMETER		SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Thermal resistance, junction-to-case	per leg	R_{thJC}		-	0.55	0.75	°C/W
	per device			-	0.27	0.37	°C/W
Marking device				4C60CP07L			




Fig. 1 - Typical Forward Voltage Drop Characteristics Per Leg




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage Per Leg




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage Per Leg




Fig. 4 - Non-Repetitive Peak Forward Surge Current vs. Pulse Duration (Square Wave), Per Leg




Fig. 5 - Thermal Impedance Z_{thJC} - Characteristics Per Leg


Fig. 6 - Peak Forward Current vs. Maximum Allowable Case Temperature Per Leg




Fig. 8 - Capacitance Energy vs. Reverse Voltage Per Leg




Fig. 7 - Allowable Input Power vs. Case Temperature Per Leg




Fig. 9 - Capacitance Change vs. Reverse Voltage Per Leg

**ORDERING INFORMATION TABLE**

Device code	VS-	4C	60	C	P	07	L	H	M3
	1	2	3	4	5	6	7	8	9
1	- Vishay Semiconductors product								
2	- 4C = SiC diode, Generation 4								
3	- Current rating (60 = 60 A)								
4	- C = common cathode								
5	- P = package TO-247								
6	- Voltage rating: 07 = 650 V								
7	- L = long lead								
8	- H = AEC-Q101 qualified								
9	- Environmental digit: M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free								

ORDERING INFORMATION


PREFERRED P/N	UNIT WEIGHT	BASE QUANTITY	PACKAGING DESCRIPTION
VS-4C60CP07LHM3	5.5 g	25 / tube	Antistatic plastic tubes

LINKS TO RELATED DOCUMENTS

Dimensions	www.vishay.com/doc?95626
Part marking information	www.vishay.com/doc?95007

TO-247AD 3L

DIMENSIONS in millimeters and inches



SYMBOL	MILLIMETERS		INCHES		NOTES
	MIN.	MAX.	MIN.	MAX.	
A	4.65	5.31	0.183	0.209	
A1	2.21	2.59	0.087	0.102	
A2	1.50	2.49	0.059	0.098	
b	0.99	1.40	0.039	0.055	
b1	0.99	1.35	0.039	0.053	
b2	1.65	2.39	0.065	0.094	
b3	1.65	2.34	0.065	0.092	
b4	2.59	3.43	0.102	0.135	
b5	2.59	3.38	0.102	0.133	
c	0.38	0.89	0.015	0.035	
c1	0.38	0.84	0.015	0.033	
D	19.71	20.70	0.776	0.815	3
D1	13.08	-	0.515	-	4

SYMBOL	MILLIMETERS		INCHES		NOTES
	MIN.	MAX.	MIN.	MAX.	
D2	0.51	1.30	0.020	0.051	
E	15.29	15.87	0.602	0.625	3
E1	13.46	-	0.53	-	
e	5.46 BSC		0.215 BSC		
Ø K	0.254		0.010		
L	19.81	20.32	0.780	0.800	
L1	3.71	4.29	0.146	0.169	
Ø P	3.56	3.66	0.14	0.144	
Ø P1	-	6.98	-	0.275	
Q	5.31	5.69	0.209	0.224	
R	4.52	5.49	0.178	0.216	
S	5.51 BSC		0.217 BSC		

Notes

- Dimensioning and tolerancing per ASME Y14.5M-1994
- Contour of slot optional
- Dimension D and E do not include mold flash. These dimensions are measured at the outermost extremes of the plastic body
- Thermal pad contour optional with dimensions D1 and E1
- Lead finish uncontrolled in L1
- Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- Outline conforms to JEDEC® outline TO-247 with exception of dimension A min., D, E min., Q min., S, and note 4



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.