



# 650 V Gen 4 Power Silicon Carbide Schottky Diode, 30 A



## FEATURES

- Positive  $V_F$  temperature coefficient for easy paralleling
- Virtually no recovery tail and no switching losses
- Temperature invariant switching behavior
- 175 °C maximum operating junction temperature
- Meets JESD 201 class 1A whisker test
- Solder bath temperature 275 °C maximum, 10 s per JESD 22-B106
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
FREE

## LINKS TO ADDITIONAL RESOURCES



| PRIMARY CHARACTERISTICS       |             |
|-------------------------------|-------------|
| $I_F$                         | 30 A        |
| $V_R$                         | 650 V       |
| $V_F$ at $I_F$ at 25 °C, typ. | 1.33 V      |
| $T_J$ max.                    | 175 °C      |
| $I_R$ at $V_R$ at 175 °C      | 125 $\mu$ A |
| $Q_C$ ( $V_R = 400$ V)        | 78 nC       |
| Package                       | TO-247AD 2L |
| Circuit configuration         | Single      |

## DESCRIPTION / APPLICATIONS

Wide band gap SiC based 650 V Schottky diode, designed for high performance and ruggedness.

Optimized for extreme high-speed hard switching across a wide temperature range. This SiC diode is ideal for demanding applications such as high efficiency PFC diodes and ultra-high frequency output rectifiers in AC/DC and DC/DC converters.

## MECHANICAL DATA

**Case:** TO-247AD 2L

Molding compound meets UL 94 V-0 flammability rating Base P/N -M3 - halogen-free, RoHS-compliant

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

**Mounting torque:** 10 in-lbs maximum

| MAXIMUM RATINGS ( $T_A = 25$ °C unless otherwise specified) |                      |                                                    |             |                  |
|-------------------------------------------------------------|----------------------|----------------------------------------------------|-------------|------------------|
| PARAMETER                                                   | SYMBOL               | TEST CONDITIONS                                    | VALUES      | UNITS            |
| Peak repetitive reverse voltage                             | $V_{RRM}$            |                                                    | 650         | V                |
| Continuous forward current                                  | $I_F^{(1)}$          | $T_C = 148$ °C (DC)                                | 30          | A                |
|                                                             | $I_F^{(2)}$          | $T_C = 140$ °C (DC)                                | 30          | A                |
| DC blocking voltage                                         | $V_{DC}$             |                                                    | 650         | V                |
| Repetitive peak forward current                             | $I_{FRM}$            | $T_C = 25$ °C, $f = 50$ Hz, square wave, DC = 25 % | 126         | A                |
| Non-repetitive peak forward surge current                   | $I_{FSM}$            | $T_C = 25$ °C, $t_p = 10$ ms, half sine wave       | 180         | A                |
|                                                             |                      | $T_C = 110$ °C, $t_p = 10$ ms, half sine wave      | 160         |                  |
| Power dissipation                                           | $P_{tot}^{(1)}$      | $T_C = 25$ °C                                      | 273         | W                |
|                                                             |                      | $T_C = 110$ °C                                     | 118         |                  |
|                                                             | $P_{tot}^{(2)}$      | $T_C = 25$ °C                                      | 200         | W                |
|                                                             |                      | $T_C = 110$ °C                                     | 87          |                  |
| $I^2t$ value                                                | $\int i^2 dt$        | $T_C = 25$ °C                                      | 162         | A <sup>2</sup> s |
|                                                             |                      | $T_C = 110$ °C                                     | 128         |                  |
| Operating junction and storage temperatures                 | $T_J^{(3)}, T_{Stg}$ |                                                    | -55 to +175 | °C               |

## Notes

(1) Based on typical  $R_{th}$

(2) Based on maximum  $R_{th}$

(3) The heat generated must be less than the thermal conductivity from junction-to-ambient:  $dP_D/dT_J < 1/R_{\theta JA}$

| <b>ELECTRICAL SPECIFICATIONS</b> ( $T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified) |        |                                                             |      |      |      |               |
|---------------------------------------------------------------------------------------------------|--------|-------------------------------------------------------------|------|------|------|---------------|
| PARAMETER                                                                                         | SYMBOL | TEST CONDITIONS                                             | MIN. | TYP. | MAX. | UNITS         |
| Forward voltage                                                                                   | $V_F$  | $I_F = 30\text{ A}$                                         | -    | 1.33 | 1.5  | V             |
|                                                                                                   |        | $I_F = 30\text{ A}, T_J = 150\text{ }^{\circ}\text{C}$      | -    | 1.5  | 1.75 |               |
|                                                                                                   |        | $I_F = 30\text{ A}, T_J = 175\text{ }^{\circ}\text{C}$      | -    | 1.60 | -    |               |
| Reverse leakage current                                                                           | $I_R$  | $V_R = V_R\text{ rated}$                                    | -    | 7.0  | 200  | $\mu\text{A}$ |
|                                                                                                   |        | $V_R = V_R\text{ rated}, T_J = 150\text{ }^{\circ}\text{C}$ | -    | 60   | 400  |               |
|                                                                                                   |        | $V_R = V_R\text{ rated}, T_J = 175\text{ }^{\circ}\text{C}$ | -    | 125  | -    |               |
| Total capacitance                                                                                 | C      | $V_R = 1\text{ V}, f = 1\text{ MHz}$                        | -    | 1315 | -    | pF            |
|                                                                                                   |        | $V_R = 400\text{ V}, f = 1\text{ MHz}$                      | -    | 110  | -    |               |
| Total capacitive charge                                                                           | $Q_C$  | $V_R = 400\text{ V}, f = 1\text{ MHz}$                      | -    | 78   | -    | nC            |

| <b>THERMAL AND MECHANICAL SPECIFICATIONS</b> ( $T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise specified) |            |                 |      |           |      |                      |
|---------------------------------------------------------------------------------------------------------------|------------|-----------------|------|-----------|------|----------------------|
| PARAMETER                                                                                                     | SYMBOL     | TEST CONDITIONS | MIN. | TYP.      | MAX. | UNITS                |
| Thermal resistance, junction-to-case                                                                          | $R_{thJC}$ |                 | -    | 0.55      | 0.75 | $^{\circ}\text{C/W}$ |
| Marking device                                                                                                |            |                 |      | 4C30EP07L |      |                      |




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage




Fig. 4 - Non-Repetitive Peak Forward Surge Current vs. Pulse Duration (Square Wave)




Fig. 5 - Thermal Impedance  $Z_{thJC}$  - Characteristics


Fig. 6 - Peak Forward Current vs. Maximum Allowable Case Temperature




Fig. 8 - Capacitance Energy vs. Reverse Voltage




Fig. 7 - Allowable Input Power vs. Case Temperature




Fig. 9 - Capacitance Change vs. Reverse Voltage

**ORDERING INFORMATION TABLE**

|             |     |    |    |   |   |    |   |     |
|-------------|-----|----|----|---|---|----|---|-----|
| Device code | VS- | 4C | 30 | E | P | 07 | L | -M3 |
|             | 1   | 2  | 3  | 4 | 5 | 6  | 7 | 8   |

|   |   |                                                                                            |
|---|---|--------------------------------------------------------------------------------------------|
| 1 | - | Vishay Semiconductors product                                                              |
| 2 | - | 4C = SiC diode, Generation 4                                                               |
| 3 | - | Current rating (30 = 30 A)                                                                 |
| 4 | - | E = single diode                                                                           |
| 5 | - | P = package TO-247                                                                         |
| 6 | - | Voltage rating: 07 = 650 V                                                                 |
| 7 | - | L = long lead                                                                              |
| 8 | - | Environmental digit:<br>-M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free |

**ORDERING INFORMATION**


| PREFERRED P/N   | UNIT WEIGHT | BASE QUANTITY | PACKAGING DESCRIPTION    |
|-----------------|-------------|---------------|--------------------------|
| VS-4C30EP07L-M3 | 5.5 g       | 25 / tube     | Antistatic plastic tubes |

**LINKS TO RELATED DOCUMENTS**

|                          |                                                                        |
|--------------------------|------------------------------------------------------------------------|
| Dimensions               | <a href="http://www.vishay.com/doc?95536">www.vishay.com/doc?95536</a> |
| Part marking information | <a href="http://www.vishay.com/doc?95648">www.vishay.com/doc?95648</a> |

# TO-247AD 2L

**DIMENSIONS** in millimeters and inches



| SYMBOL | MILLIMETERS |       | INCHES |       | NOTES |
|--------|-------------|-------|--------|-------|-------|
|        | MIN.        | MAX.  | MIN.   | MAX.  |       |
| A      | 4.65        | 5.31  | 0.183  | 0.209 |       |
| A1     | 2.21        | 2.59  | 0.087  | 0.102 |       |
| A2     | 1.50        | 2.49  | 0.059  | 0.098 |       |
| b      | 0.99        | 1.40  | 0.039  | 0.055 |       |
| b1     | 0.99        | 1.35  | 0.039  | 0.053 |       |
| b2     | 1.65        | 2.39  | 0.065  | 0.094 |       |
| b3     | 1.65        | 2.34  | 0.065  | 0.092 |       |
| c      | 0.38        | 0.89  | 0.015  | 0.035 |       |
| c1     | 0.38        | 0.84  | 0.015  | 0.033 |       |
| D      | 19.71       | 20.70 | 0.776  | 0.815 | 3     |
| D1     | 13.08       | -     | 0.515  | -     | 4     |
| D2     | 0.51        | 1.35  | 0.020  | 0.053 |       |

| SYMBOL | MILLIMETERS |       | INCHES    |       | NOTES |
|--------|-------------|-------|-----------|-------|-------|
|        | MIN.        | MAX.  | MIN.      | MAX.  |       |
| E      | 15.29       | 15.87 | 0.602     | 0.625 | 3     |
| E1     | 13.46       | -     | 0.53      | -     |       |
| e      | 5.46 BSC    |       | 0.215 BSC |       |       |
| Ø K    | 0.254       |       | 0.010     |       |       |
| L      | 19.81       | 20.32 | 0.780     | 0.800 |       |
| L1     | 3.71        | 4.29  | 0.146     | 0.169 |       |
| Ø P    | 3.56        | 3.66  | 0.14      | 0.144 |       |
| Ø P1   | -           | 6.98  | -         | 0.275 |       |
| Q      | 5.31        | 5.69  | 0.209     | 0.224 |       |
| R      | 4.52        | 5.49  | 0.178     | 0.216 |       |
| S      | 5.51 BSC    |       | 0.217 BSC |       |       |

## Notes

- (1) Dimensioning and tolerancing per ASME Y14.5M-1994
- (2) Contour of slot optional
- (3) Dimension D and E do not include mold flash. These dimensions are measured at the outermost extremes of the plastic body
- (4) Thermal pad contour optional with dimensions D1 and E1
- (5) Lead finish uncontrolled in L1
- (6) Ø P to have a maximum draft angle of 1.5 to the top of the part with a maximum hole diameter of 3.91 mm (0.154")
- (7) Outline conforms to JEDEC® outline TO-247 with exception of dimension A min., D, E min., Q min., S, and note 4



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.