



Ultrafast Rectifier, 2 x 7.5 A FRED Pt®


DFN6546A


FEATURES

- Very low profile - typical height of 0.88 mm
- Ideal for automated placement
- Wettable flanks allows easy inspection with AOI (automated optical inspection). No X-ray necessary
- Low forward voltage drop, low power losses
- Low leakage current
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- For PFC, CRM snubber operation
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE

LINKS TO ADDITIONAL RESOURCES



PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	2 x 7.5 A
V_R	200 V
V_F at I_F	0.75 V
t_{rr} (typ.)	15 ns
I_{FSM}	124 A
T_J max.	175 °C
Package	DFN6546A
Circuit configuration	Common cathode

TYPICAL APPLICATIONS

For use in high frequency inverters, DC/DC converters, freewheeling diodes, clamping and snubber, polarity protection, and LED lighting

MECHANICAL DATA

Case: DFN6546A

Molding compound meets UL 94 V-0 flammability rating

Terminals: matte tin plated leads, solderable per J-STD-002, meets JESD 201 class 2 whisker test

Polarity: color band denotes cathode end

ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Peak repetitive reverse voltage, per leg	V_{RRM}		200	V
Average rectified forward current, per leg	$I_{F(AV)}$	$T_M = 152\text{ °C}$, $D = 0.50$	7.5	A
Non-repetitive peak surge current, per leg	I_{FSM}	$T_J = 25\text{ °C}$, 10 ms sine pulse	124	
Operating junction and storage temperatures	T_J , T_{Stg}		-55 to +175	°C

ELECTRICAL SPECIFICATIONS ($T_J = 25\text{ °C}$ unless otherwise specified)						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Breakdown voltage, blocking voltage, per leg	V_{BR} , V_R	$I_R = 100\text{ }\mu\text{A}$	200	-	-	V
Forward voltage, per leg	V_F	$I_F = 7.5\text{ A}$	-	0.9	1.1	
		$I_F = 7.5\text{ A}$, $T_J = 150\text{ °C}$	-	0.75	0.85	
Reverse leakage current, per leg	I_R	$V_R = V_R$ rated	-	-	1	μA
		$T_J = 150\text{ °C}$, $V_R = V_R$ rated	-	-	150	
Junction capacitance, per leg	C_T	$V_R = 200\text{ V}$	-	25	-	pF

**DYNAMIC RECOVERY CHARACTERISTICS** ($T_J = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Reverse recovery time, per leg	t_{rr}	$I_F = 0.5\text{ A}$, $I_R = 1\text{ A}$, $I_{rr} = 0.25\text{ A}$	-	15	25	ns
		$T_J = 25\text{ }^{\circ}\text{C}$	-	12	-	
		$T_J = 125\text{ }^{\circ}\text{C}$	-	21	-	
Peak recovery current, per leg	I_{RRM}	$T_J = 25\text{ }^{\circ}\text{C}$	-	3.9	-	A
		$T_J = 125\text{ }^{\circ}\text{C}$	-	7.2	-	
		$I_F = 7.5\text{ A}$, $di_F/dt = 500\text{ A}/\mu\text{s}$, $V_R = 200\text{ V}$	-	25	-	
Reverse recovery charge, per leg	Q_{rr}	$T_J = 25\text{ }^{\circ}\text{C}$	-	77	-	nC
		$T_J = 125\text{ }^{\circ}\text{C}$	-	77	-	

THERMAL - MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Maximum junction and storage temperature range	T_J, T_{Stg}		-55	-	175	$^{\circ}\text{C}$
Thermal resistance, junction to mount, per leg	$R_{thJM}^{(1)}$		-	-	3.4	$^{\circ}\text{C}/\text{W}$
Weight			-	0.086	-	9
Marking device		Case style DFN6546A	15CH2			

Note

(1) Thermal resistance junction to mount follows JEDEC® 51-14 transient dual interface test method (TDIM)




Fig. 1 - Typical Forward Voltage Drop Characteristics, per Leg




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage, per Leg




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage, per Leg




Fig. 4 - Maximum Transient Thermal Impedance, Junction to Mount, per Leg




Fig. 5 - Maximum Allowable Mount Temperature vs. Average Forward Current, per Leg




Fig. 6 - Forward Power Loss Characteristics, per Leg

Note

Formula used: $T_M = T_J - (P_d + P_{dREV}) \times R_{thJM}$;
 P_d = forward power loss = $I_{F(AV)} \times V_{FM}$ at $(I_{F(AV)}/D)$ (see fig. 5);
 P_{dREV} = inverse power loss = $V_{R1} \times I_R (1 - D)$; I_R at V_{R1} = rated V_R






Fig. 7 - Typical Reverse Recovery Time vs. di_F/dt , per Leg

Fig. 8 - Typical Stored Charge vs. di_F/dt , per Leg

Fig. 9 - I_{rr} vs. di/dt , per Leg


Fig. 10 - Reverse Recovery Waveform and Definitions

**ORDERING INFORMATION TABLE**

Device code	VS-	15	C	R	H	02	-M3
	1	2	3	4	5	6	7

- | | | |
|----------|---|---|
| 1 | - | Vishay Semiconductors product |
| 2 | - | Current rating (15 = 15 A) |
| 3 | - | Circuit configuration:
C = common cathode |
| 4 | - | R = DFN6546A package |
| 5 | - | Process type,
H = ultrafast recovery |
| 6 | - | Voltage code (02 = 200 V) |
| 7 | - | -M3 = halogen-free, RoHS-compliant, and terminations lead (Pb)-free |

ORDERING INFORMATION (Example)

PREFERRED P/N	PREFERRED PACKAGE CODE	BASE QUANTITY	PACKAGING DESCRIPTION
VS-15CRH02-M3/I	I	6000	13" diameter plastic tape and reel





LINKS TO RELATED DOCUMENTS

Dimensions	www.vishay.com/doc?97347
Part marking information	www.vishay.com/doc?97348
Packaging information	www.vishay.com/doc?98691



DFN6456, FRED Pt®

DIMENSIONS in inches (millimeters)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.