


Surface Mount TRANSZORB[®] Transient Voltage Suppressors


DFN6546A

LINKS TO ADDITIONAL RESOURCES


PRIMARY CHARACTERISTICS	
V_{BR}	12 V to 100 V
V_{WM}	10.2 V to 85.5 V
P_{PPM} (10 x 1000 μ s)	3000 W
T_J max.	175 °C
Polarity	Bidirectional
Package	DFN6546A
Circuit configuration	Single

FEATURES

- Low-profile package - typical height of 0.88 mm
- Leadless DFN package with side-wettable flanks suitable for customer AOI (Automatic Optical Inspection)
- Ideal for automated placement
- Junction passivation optimized design passivated anisotropic rectifier technology
- Bidirectional
- Excellent clamping capability
- Peak pulse power: 3000 W (10/1000 μ s)
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- Compatible to SMPC (TO-277A) package case outline
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
 COMPLIANT
 HALOGEN
FREE
TYPICAL APPLICATIONS

Use in sensitive electronics protection against voltage transients induced by inductive load switching and lightning on ICs, MOSFET, signal lines of sensor units for consumer, computer, industrial, medical, and telecommunication.

MECHANICAL DATA

Case: DFN6546A

Molding compound meets UL 94 V-0 flammability rating
 Base P/N-M3 - halogen-free, RoHS-compliant, and industrial grade

Terminals: matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 2 whisker test

Polarity: no cathode band for bidirectional types

MAXIMUM RATINGS ($T_A = 25$ °C, unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
Peak pulse power dissipation with a 10/1000 μ s waveform (fig. 1) ⁽¹⁾	P_{PPM}	3000	W
Peak pulse current with a 10/1000 μ s waveform (fig. 3) ⁽¹⁾	I_{PPM}	See table next page	A
Operating junction and storage temperature range	T_J, T_{STG}	-65 to +175	°C

Note

⁽¹⁾ Non-repetitive current pulse, per fig. 3 and derated above $T_A = 25$ °C per fig. 2



ELECTRICAL CHARACTERISTICS (T _A = 25 °C, unless otherwise noted)											
DEVICE TYPE	DEVICE MARKING CODE	BREAKDOWN VOLTAGE V _{BR} ⁽¹⁾ AT I _T (V)			TEST CURRENT I _T (mA)	STAND-OFF VOLTAGE V _{WM} (V)	MAXIMUM REVERSE LEAKAGE AT V _{WM} I _R (μA)	MAXIMUM REVERSE LEAKAGE AT V _{WM} T _J = 150 °C I _D (μA)	MAXIMUM PEAK PULSE SURGE CURRENT I _{PPM} ⁽²⁾ (A)	MAXIMUM CLAMPING VOLTAGE AT I _{PPM} V _C (V)	TYPICAL TEMP. COEFFICIENT OF V _{BR} ⁽³⁾ α _T (%/°C)
		MIN.	NOM.	MAX.							
3KDFN12CA	3KNA	11.4	12.0	12.6	1.0	10.2	5.0	50	180	16.7	0.070
3KDFN13CA	3KNB	12.4	13.0	13.7	1.0	11.1	5.0	50	165	18.2	0.072
3KDFN15CA	3KNC	14.3	15.0	15.8	1.0	12.8	2.0	20	142	21.2	0.076
3KDFN16CA	3KND	15.2	16.0	16.8	1.0	13.6	2.0	20	133	22.5	0.078
3KDFN18CA	3KNE	17.1	18.0	18.9	1.0	15.3	1.0	10	118	25.5	0.080
3KDFN20CA	3KNF	19.0	20.0	21.0	1.0	17.1	1.0	10	108	27.7	0.082
3KDFN22CA	3KNG	20.9	22.0	23.1	1.0	18.8	1.0	10	98.0	30.6	0.084
3KDFN24CA	3KNH	22.8	24.0	25.2	1.0	20.5	1.0	10	90.4	33.2	0.085
3KDFN27CA	3KNJ	25.7	27.0	28.4	1.0	23.1	1.0	10	80.0	37.5	0.087
3KDFN30CA	3KNK	28.5	30.0	31.5	1.0	25.6	1.0	10	72.5	41.4	0.088
3KDFN33CA	3KNL	31.4	33.0	34.7	1.0	28.2	1.0	10	65.6	45.7	0.089
3KDFN36CA	3KNM	34.2	36.0	37.8	1.0	30.8	1.0	10	60.1	49.9	0.090
3KDFN39CA	3KNN	37.1	39.0	41.0	1.0	33.3	1.0	10	55.7	53.9	0.091
3KDFN43CA	3KNP	40.9	43.0	45.2	1.0	36.8	1.0	10	50.6	59.3	0.092
3KDFN47CA	3KNQ	44.7	47.0	49.4	1.0	40.2	1.0	10	46.3	64.8	0.092
3KDFN51CA	3KNR	48.5	51.0	53.6	1.0	43.6	1.0	10	42.8	70.1	0.093
3KDFN56CA	3KNS	53.2	56.0	58.8	1.0	47.8	1.0	10	39.0	77.0	0.093
3KDFN62CA	3KNT	58.9	62.0	65.1	1.0	53.0	1.0	10	35.3	85.0	0.094
3KDFN68CA	3KNU	64.6	68.0	71.4	1.0	58.1	1.0	10	32.6	92.0	0.095
3KDFN75CA	3KNV	71.3	75.0	78.8	1.0	64.1	1.0	10	28.8	104	0.095
3KDFN82CA	3KNW	77.9	82.0	86.1	1.0	70.1	1.0	10	26.5	113	0.095
3KDFN91CA	3KNX	86.5	91.0	95.5	1.0	77.8	1.0	10	24.0	125	0.096
3KDFN100CA	3KNY	95.0	100	105	1.0	85.5	1.0	10	21.9	137	0.096

Notes

- (1) Pulse test: t_p ≤ 50 ms
- (2) Surge current waveform per fig. 3 and derated per fig. 2
- (3) To calculate V_{BR} vs. junction temperature, use the following formula: V_{BR} at T_J = V_{BR} at 25 °C x (1 + α_T x (T_J - 25))
- (4) All terms and symbols are consistent with ANSI/IEEE C62.35

THERMAL CHARACTERISTICS (T _A = 25 °C unless otherwise noted)				
PARAMETER	SYMBOL	TYP.	MAX.	UNIT
Thermal resistance	R _{θJA} ⁽¹⁾	76	95	°C/W
	R _{θJM} ⁽²⁾	0.95	1.19	°C/W


Notes

- (5) Thermal resistance junction-to-ambient to follow JEDEC® 51-2A, device mounted on FR4 PCB, 2 oz., 4.8 mm x 4.72 mm
- (6) Thermal resistance junction-to-mount to follow JEDEC® 51-14 using Transient Dual Interface Test Method (TDIM)

IMMUNITY TO STATIC ELECTRICAL DISCHARGE TO THE FOLLOWING STANDARDS (T _A = 25 °C unless otherwise noted)				
STANDARD	TEST TYPE	TEST CONDITIONS	SYMBOL	VALUE
IEC 61000-4-2	Contact discharge	C = 150 pF, R = 330 Ω	ESD	30 kV
	Air discharge			30 kV



ORDERING INFORMATION TABLE



ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
3KDFN12CA-M3/H	0.094	H	1500	7" diameter plastic tape and reel
3KDFN12CA-M3/I	0.094	I	6000	13" diameter plastic tape and reel



RATINGS AND CHARACTERISTICS CURVES ($T_A = 25\text{ }^\circ\text{C}$, unless otherwise noted)




Fig. 1 - Peak Pulse Power Rating Curve




Fig. 4 - Typical Junction Capacitance




Fig. 2 - Pulse Power or Current vs. Initial Junction Temperature




Fig. 5 - Typical Transient Thermal Impedance




Fig. 3 - Pulse Waveform


Note

- Fig. 1, power calculations is based on I_{PPM} times defined maximum clamping voltage by pulse width



PACKAGE OUTLINE DIMENSIONS in inches (millimeters)

DFN6546A





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.