


## SMD (DO-218)

### TAPE INFORMATION in inches (millimeters)




DIMENSIONS in millimeters (inches)							
TAPE SIZE	$D_0$	$E_1$	$P_0$	$P_2$	$S_1$ MIN.	$T$ MAX.	$T_1$ MAX.
24 mm (0.945)	$1.5 \pm 0.1$ ( $0.059 \pm 0.004$ )	$1.75 \pm 0.1$ ( $0.069 \pm 0.004$ )	$4.0 \pm 0.1$ ( $0.157 \pm 0.004$ )	$2.0 \pm 0.1$ ( $0.079 \pm 0.004$ )	0.6 (0.024)	0.6 (0.024)	0.1 (0.004)
$B_1$ MAX.	$D_1$ MIN.	$E_2$ MIN.	$F$	$P_1$	R REF.	$T_2$ MAX.	$W$ MAX.
20.1 (0.791)	1.5 (0.059)	22.25 (0.876)	$11.5 \pm 0.1$ ( $0.453 \pm 0.004$ )	$16.0 \pm 0.1$ ( $0.630 \pm 0.004$ )	25 (0.984)	5.31 (0.209)	24.3 (0.957)

#### Notes

- (1) For machine reference only, including draft and radii concentric around  $B_0$
- (2)  $A_0$ ,  $B_0$ , and  $K_0$  are determined by the maximum dimensions of the component size. The clearance between the component and the cavity must be within 0.15 mm (0.006") min. to 1.0 mm (0.59") max. for 24 mm tape
- (3) All surface mount components are packed in accordance with EIA standard 481-E

### REEL INFORMATION in inches (millimeters)



DIMENSIONS in millimeters (inches)							
PACKAGE CODE	A	B MIN.	C	D MIN.	N MIN.	G MAX.	T MAX.
I (13" reel)	$330 \pm 2.0$ (13.0 $\pm$ 0.079)	1.5 (0.059)	$13.0 \pm 0.20$ (0.51 $\pm$ 0.008)	20.2 (0.795)	50 (1.97)	26.4 (1.039)	30.4 (1.197)