



MaxSiC™ 1200 V N-Channel SiC MOSFET



N-Channel MOSFET

Marking Code: 120A250FW

PRODUCT SUMMARY		
V_{DS} (V) at T_J max.	1200	
$R_{DS(on)}$ typ. (mΩ) at 25 °C	$V_{GS} = 20$ V	250
Q_g typ. (nC)	20	
I_D (A)	10.5	
C_{oss} (pF)	21.2	
P_D (W)	56	
Configuration	Single	

ORDERING INFORMATION	
Package	TO-247 3L
Lead (Pb)-free and halogen-free	MXP120A250FW-Y-GE3

ABSOLUTE MAXIMUM RATINGS ($T_C = 25$ °C, unless otherwise noted)				
PARAMETER		SYMBOL	LIMIT	UNIT
Drain-source voltage ^a		V_{DS}	1200	V
Gate-source voltage		V_{GS}	-10 / +22	
Continuous drain current	$T_C = 25$ °C	I_D	10.5	A
	$T_C = 100$ °C	I_D	6.7	
Pulsed drain current ^b		I_{DM}	21	
Short-circuit withstand time		T_{SC}	3	μs
Maximum power dissipation	$T_C = 25$ °C	P_D	56	W
	$T_C = 100$ °C	P_D	22	
Operating junction and storage temperature range		T_J, T_{stg}	-55 to +150	°C

Notes

a. $T_J = 25$ °C to 150 °C

b. Repetitive rating; pulse width limited by maximum junction temperature

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

FEATURES

- Fast switching speed
- Short circuit withstand time 3 μs
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

APPLICATIONS

- Charger
- Industrial UPS
- Boost inverter
- DC/DC converter








RoHS
COMPLIANT
HALOGEN
FREE







**THERMAL RESISTANCE RATINGS**






PARAMETER	SYMBOL	TYP.	MAX.	UNIT
Maximum junction-to-ambient	R_{thJA}	-	40	°C/W
Maximum junction-to-case (drain)	R_{thJC}	-	2.24	

SPECIFICATIONS ($T_J = 25\text{ °C}$, unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static							
Drain-source breakdown voltage	V _{DS}	V _{GS} = 0 V, I _D = 1 mA		1200	-	-	V
Gate-source threshold voltage (N)	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 10 mA		-	3.1	-	V
		V _{DS} = V _{GS} , I _D = 10 mA, T _J = 150 °C		-	2.3	-	V
Gate-source leakage	I _{GSS}	V _{GS} = +22 V, V _{DS} = 0 V		-	-	100	nA
		V _{GS} = -10 V, V _{DS} = 0 V		-	-	-100	
Zero gate voltage drain current	I _{DSS}	V _{DS} = 960 V, V _{GS} = 0 V		-	-	10	μA
Drain-source on-state resistance	R _{DS(on)}	V _{GS} = 20 V, I _D = 4 A		-	250	313	mΩ
		V _{GS} = 20 V, I _D = 4 A, T _J = 150 °C		-	380	475	
		V _{GS} = 18 V, I _D = 4 A		-	287	359	
		V _{GS} = 18 V, I _D = 4 A, T _J = 150 °C		-	395	494	
Dynamic							
Input capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = 800 V, f = 1 MHz		-	447	-	pF
Output capacitance	C _{oss}			-	21.2	-	
Reverse transfer capacitance	C _{rss}			-	3.2	-	
Total gate charge	Q _g	V _{GS} = 18 V	I _D = 4 A, V _{DS} = 800 V	-	20.3	-	nC
Gate-source charge	Q _{gs}			-	5.5	-	
Gate-drain charge	Q _{gd}			-	7.9	-	
Gate Resistance	R _g	V _{DS} = 0 V, f = 1 MHz		-	34	-	Ω
Switching Characteristics							
Turn-on delay time	t _{d(on)}	V _{GS} = -5 V ~ 18 V, I _D = 4 A, V _{DS} = 800 V, R _{g(ext)} = 4.4 Ω		-	10	-	ns
Rise time	t _r			-	11.5	-	
Turn-off delay time	t _{d(off)}			-	9.5	-	
Fall time	t _f			-	15	-	
Turn-on switching energy	E _{on}			-	76	-	μJ
Turn-off switching energy	E _{off}			-	5	-	
Reverse Diode Characteristics							
Reverse recovery time	t _{rr}	V _{GS} = -5 V, I _{SD} = 4 A, V _R = 800 V di/dt = 1000 A/μs		-	7.5	-	ns
Reverse recovery charge	Q _{rr}			-	12	-	nC
Reverse recovery current	I _{rrm}			-	2.8	-	A

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)

Fig. 1 - Typical Output Characteristics

Fig. 4 - Typical Transfer Characteristics

Fig. 2 - Typical Output Characteristics

Fig. 5 - Forward Transconductance vs. Drain Current

Fig. 3 - Typical Output Characteristics

Fig. 6 - Normalized On-Resistance vs. Drain-to-Source Current


Fig. 7 - Typical Capacitance vs. Drain-to-Source Voltage

Fig. 10 - Temperature vs. Drain-to-Source Voltage

Fig. 8 - Typical Gate Charge vs. Gate-to-Source Voltage

Fig. 11 - Typical Source-Drain Diode Forward Voltage

Fig. 9 - Normalized On-Resistance vs. Temperature

Fig. 12 - On-Resistance vs. Gate-to-Source Voltage


Fig. 13 - Threshold Voltage vs. Case Temperature

Fig. 15 - Output Capacitance and its Stored Energy vs. Drain-to-Source Voltage

Fig. 14 - Drain Current vs. Case Temperature

Fig. 16 - Power, Dissipated P_D vs. Case Temperature

Fig. 17 - Safe Operating Area










Fig. 18 - Normalized Effective Transient Thermal Impedance


Fig. 19 - Waveforms of Switching Time

Fig. 22 - Waveforms for Gate Charge

Fig. 20 - Waveforms for Switching Energy

Fig. 23 - Waveforms for Reverse Recovery

Fig. 21 - Switching and Reverse Diode Characteristics Measurement Circuit

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see www.vishay.com/ppg?92814



Case Outline for TO-247AD 3L


FACILITY CODE: N


Notes

- All metal surfaces: tin plated (MATTE), except area of cut
- Dimensioning and tolerancing confirm to ASME Y14.5M-1994
- All dimensions are in millimeters
- This drawing will meet all dimensions requirement of JEDEC outlines TO-247 AD



FACILITY CODE: 9





DIM.	MILLIMETERS		
	MIN.	NOM.	MAX.
A	4.83	5.02	5.21
A1	2.29	2.41	2.55
A2	1.50	2.00	2.49
b	1.12	1.20	1.33
b2 ⁽¹⁾	1.91	2.00	2.39
b4 ⁽¹⁾	2.87	3.00	3.22
c	0.55	0.60	0.69
D ⁽²⁾	20.80	20.95	21.10
D1 ⁽³⁾	16.25	16.55	17.65
D2	0.51	1.19	1.35
E ⁽²⁾	15.75	15.94	16.13
E1 ⁽³⁾	13.46	14.02	14.16
E2	4.32	4.91	5.49
e	5.44 BSC.		
L	19.81	20.07	20.32
L1 ⁽⁴⁾	4.10	4.19	4.40
ØP ⁽⁵⁾	3.56	3.61	3.65
ØP1	7.19 ref.		
Q	5.39	5.79	6.20
S	6.04	6.17	6.30
ECN: E24-0229-Rev. A, 13-May-2024 DWG: 6118			

Notes

- Package reference: JEDEC TO-247, variation AD
- All dimensions are in mm
- Slot required, notch may be rounded
- ⁽¹⁾ Dimension b2 and b4 does not include dambar protrusion
- ⁽²⁾ Dimension D and E do not include mold flash
- ⁽³⁾ Thermal pad contour optional within dimension D1 and E1
- ⁽⁴⁾ Lead Finish Uncontrolled In L1
- ⁽⁵⁾ ØP to have a draft angle of 1.5 ° ref. to the top of the part with hole diameter of 3.91mm



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.