



# High Current Density Surface-Mount TMBS® (Trench MOS Barrier Schottky) Rectifier

Ultra Low  $V_F = 0.56 \text{ V}$  at  $I_F = 2.5 \text{ A}$



DFN6546A



## LINKS TO ADDITIONAL RESOURCES



| PRIMARY CHARACTERISTICS                                    |                |
|------------------------------------------------------------|----------------|
| $I_{F(AV)}$                                                | 2 x 5 A        |
| $V_{RRM}$                                                  | 150 V          |
| $I_{FSM}$                                                  | 120 A          |
| $V_F$ at $I_F = 5 \text{ A}$ ( $T_J = 125^\circ\text{C}$ ) | 0.63 V         |
| $T_J$ max.                                                 | 150 °C         |
| Package                                                    | DFN6546A       |
| Circuit configuration                                      | Common cathode |

## FEATURES

- Low profile package - typical height of 0.88 mm
- Leadless DFN package with side-wettable flanks suitable for customer AOI (Automatic Optical Inspection)
- Very low forward voltage by TMBS Gen3 technology
- Low power losses, high efficiency
- Compatible to SMPC (TO-277A) package case outline
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
  - Automotive ordering code; base P/NHM3
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
FREE

## TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

## MECHANICAL DATA

**Case:** DFN6546A

Molding compound meets UL 94 V-0 flammability rating  
Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3 - halogen-free, RoHS-compliant, and AEC-Q101 qualified

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 and HM3 suffix meets JESD 201 class 2 whisker test

| MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)                          |                            |             |      |
|---------------------------------------------------------------------------------------------|----------------------------|-------------|------|
| PARAMETER                                                                                   | SYMBOL                     | V10N6153C   | UNIT |
| Device marking code                                                                         |                            | 10PC        |      |
| Maximum repetitive peak reverse voltage                                                     | $V_{RRM}$                  | 150         | V    |
| Maximum average forward rectified current (fig. 1)                                          | $I_{F(AV)}$ <sup>(1)</sup> | 10          | A    |
| per device<br>per diode                                                                     |                            | 5           |      |
| Peak forward surge current 10 ms single half sine-wave superimposed on rated load per diode | $I_{FSM}$                  | 120         | A    |
| Operating junction temperature range                                                        | $T_J$ <sup>(2)</sup>       | -40 to +150 | °C   |
| Storage temperature range                                                                   | $T_{STG}$                  | -55 to +150 | °C   |

## Notes

<sup>(1)</sup> With infinite heatsink

<sup>(2)</sup> The heat generated must be less than the thermal conductivity from junction-to-ambient:  $dP_D/dT_J < 1/R_{\theta JA}$



| ELECTRICAL CHARACTERISTICS (T <sub>J</sub> = 25 °C unless otherwise noted) |                        |                         |                               |        |      |      |
|----------------------------------------------------------------------------|------------------------|-------------------------|-------------------------------|--------|------|------|
| PARAMETER                                                                  | TEST CONDITIONS        |                         | SYMBOL                        | TYP.   | MAX. | UNIT |
| Instantaneous forward voltage per diode                                    | I <sub>F</sub> = 2.5 A | T <sub>J</sub> = 25 °C  | V <sub>F</sub> <sup>(1)</sup> | 0.69   | -    | V    |
|                                                                            | I <sub>F</sub> = 5 A   |                         |                               | 0.84   | 0.95 |      |
|                                                                            | I <sub>F</sub> = 2.5 A | T <sub>J</sub> = 125 °C |                               | 0.56   | -    |      |
|                                                                            | I <sub>F</sub> = 5 A   |                         |                               | 0.63   | 0.69 |      |
| Reverse current per diode                                                  | V <sub>R</sub> = 100 V | T <sub>J</sub> = 25 °C  | I <sub>R</sub> <sup>(2)</sup> | 0.0005 | -    | mA   |
|                                                                            |                        | T <sub>J</sub> = 125 °C |                               | 0.6    | -    |      |
|                                                                            | V <sub>R</sub> = 150 V | T <sub>J</sub> = 25 °C  |                               | -      | 0.05 |      |
|                                                                            |                        | T <sub>J</sub> = 125 °C |                               | 1.5    | 5    |      |
| Typical junction capacitance per diode                                     | 4.0 V, 1 MHz           |                         | C <sub>J</sub>                | 265    | -    | pF   |

**Notes**(1) Pulse test: 300  $\mu\text{s}$  pulse width, 1 % duty cycle(2) Pulse test: pulse width  $\leq 5\text{ ms}$ 

| THERMAL CHARACTERISTICS ( $T_A = 25\text{ }^{\circ}\text{C}$ unless otherwise noted) |                       |      |      |                      |
|--------------------------------------------------------------------------------------|-----------------------|------|------|----------------------|
| PARAMETER                                                                            | SYMBOL                | TYP. | MAX. | UNIT                 |
| Thermal resistance per device                                                        | $R_{\theta JM}^{(1)}$ | 2    | 2.5  | $^{\circ}\text{C/W}$ |

**Note**

(1) Thermal resistance junction to mount follows JEDEC® 51-14 transient dual interface test method (TDIM)

**ORDERING INFORMATION TABLE**

| Device code | V | 10                                                                                                       | N6 | 15 | 3 | C | H | M3 |
|-------------|---|----------------------------------------------------------------------------------------------------------|----|----|---|---|---|----|
|             | ① | ②                                                                                                        | ③  | ④  | ⑤ | ⑥ | ⑦ | ⑧  |
| ①           | - | Vishay TMBS product                                                                                      |    |    |   |   |   |    |
| ②           | - | Current rating (10 = 10 A)                                                                               |    |    |   |   |   |    |
| ③           | - | Package type (N6 = DFN6546A package)                                                                     |    |    |   |   |   |    |
| ④           | - | Voltage rating (15 = 150 V)                                                                              |    |    |   |   |   |    |
| ⑤           | - | TMBS generation option (3 = Gen 3)                                                                       |    |    |   |   |   |    |
| ⑥           | - | Circuit configuration (C = Common cathode)                                                               |    |    |   |   |   |    |
| ⑦           | - | Quality grade (H = AEC-Q101 qualified, otherwise = industry grade)                                       |    |    |   |   |   |    |
| ⑧           | - | Material / environmental category<br>(M3 = halogen-free, RoHS-compliant, and termination lead (Pb)-free) |    |    |   |   |   |    |

| ORDERING INFORMATION (Example) |                 |                        |               |                                    |
|--------------------------------|-----------------|------------------------|---------------|------------------------------------|
| PREFERRED P/N                  | UNIT WEIGHT (g) | PREFERRED PACKAGE CODE | BASE QUANTITY | DELIVERY MODE                      |
| V10N6153C-M3/I                 | 0.086           | I                      | 6000          | 13" diameter plastic tape and reel |
| V10N6153CHM3/I <sup>(1)</sup>  | 0.086           | I                      | 6000          | 13" diameter plastic tape and reel |

**Note**

(1) AEC-Q101 qualified


**RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted)


Fig. 1 - Forward Current Derating Curve




Fig. 4 - Typical Reverse Leakage Characteristics Per Diode




Fig. 2 - Forward Power Loss Characteristics Per Diode




Fig. 5 - Typical Junction Capacitance Per Diode




Fig. 3 - Typical Instantaneous Forward Characteristics Per Diode





Fig. 6 - Typical Transient Thermal Impedance



**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.