



Molded, Commercial, Single In-Line Thin Film Resistor, Through Hole Network (Custom)



Designed to meet MIL-PRF-83401 characteristic “V” and “H”

Military grade networks designed to meet MIL-PRF-83401 characteristics “V” and “H” available in 6 pins, 8 pins and 10 pins sizes in high and low profile. The molded style features a direct thermal compression bonded lead attachment in a rugged molded construction.

SCHEMATIC



Custom schematics available. Please consult factory.

FEATURES

- Lead (Pb)-free gold plated terminals standard
- Gold to gold terminations (no internal solder)
- Exceptional ratio stability over time and temperature ($\Delta R \pm 0.015\%$ 2000 h at 70 °C)
- Rugged low profile molded case 6 pins, 8 pins, and 10 pins available
- Compatible with automatic insertion equipment
- Compliant to RoHS Directive 2002/95/EC



RoHS*
COMPLIANT

Note

* Pb containing terminations are not RoHS compliant, exemptions may apply

TYPICAL PERFORMANCE

▲	ABSOLUTE	TRACKING
	TCR	10
	ABSOLUTE	RATIO
TOL.	0.05	0.025

STANDARD ELECTRICAL SPECIFICATIONS		
TEST	SPECIFICATIONS	CONDITIONS
Material	Passivated nichrome	-
Pin/Lead Number	6, 8, 10	-
Resistance Range	20 Ω to 500 k Ω total	-
TCR: Absolute	± 10 ppm/°C to ± 25 ppm/°C	- 55 °C to + 125 °C
TCR: Tracking	± 2 ppm/°C (typical less 1 ppm/°C equal values)	- 55 °C to + 125 °C
Tolerance: Absolute	$\pm 0.05\%$ to $\pm 0.5\%$	+ 25 °C
Tolerance: Ratio	$\pm 0.025\%$ to 0.1 %	+ 25 °C
Power Rating: Resistor	100 mW (per element typical at + 25 °C)	Maximum at + 70 °C
Power Rating: Package	500 mW	Maximum at + 70 °C
Stability: Absolute	$\Delta R \pm 0.05\%$	2000 h at + 70 °C
Stability: Ratio	$\Delta R \pm 0.015\%$	2000 h at + 70 °C
Voltage Coefficient	< 0.0015 ppm/V	-
Working Voltage	100 V	-
Operating Temperature Range	- 55 °C to + 125 °C	-
Storage Temperature Range	- 55 °C to + 150 °C	-
Noise	< - 30 dB	-
Thermal EMF	< 0.08 μ V/°C	-
Shelf Life Stability: Absolute	$\Delta R \pm 0.01\%$	1 year at + 25 °C
Shelf Life Stability: Ratio	$\Delta R \pm 0.002\%$	1 year at + 25 °C

Note

- Tantalum Nitride film is custom, consult factory

DIMENSIONS AND IMPRINTING in inches and millimeters			
	DIMENSION	INCHES	MILLIMETERS
	A	0.035	0.89
	B	0.040	1.02
	C	0.100 ± 0.005 non-accum.	2.54 ± 0.13
	D	0.019 ± 0.006 typical	0.48 ± 0.15
	E	0.187 ± 0.010	4.75 ± 0.25
	F	0.135	3.43
	G	0.095	2.41
	H	0.012 ± 0.004	0.31 ± 0.10
	L (6 Pins)	0.583 ± 0.015	14.81 ± 0.38
	L (8 Pins)	0.783 ± 0.015	19.89 ± 0.38
	L (10 Pins)	0.983 ± 0.015	24.97 ± 0.38





MECHANICAL SPECIFICATIONS	
Resistive Element	Passivated nichrome or tantalum nitride
Substrate Material	Alumina
Body Molded	Epoxy
Terminals	Copper alloy
Plating	Nickel/gold
Model TSP - Lead (Pb)-free Standard	Gold plated
Model TSPS - Lead (Pb)-free Solder Coated Option	Sn63
Model TSPL - Tin/Lead Solder Coated Option	Sn96.5, Ag3.0, Cu0.5
Tin/Lead and Lead (Pb)-free Finish	Hot solder dip

ORDERING INFORMATION CHECK LIST (Customs)	
Special requirements should be identified in advance, but as a minimum, you should have the following information ready.	
ELECTRICAL	MECHANICAL
<ol style="list-style-type: none"> Resistors, by value and tolerance Reference resistor(s) and matching of which resistors to which reference resistors Resistance by ratio Absolute temperature coefficient of resistivity Temperature tracking of subordinate resistors to reference resistor(s) Maximum operating voltage Resistor power ratings Operating temperature range 	<ol style="list-style-type: none"> Maximum allowable seated height (from PC board to top of network) Special marking concerns Schematic pin out of package Specify if solder coated terminals are required
For additional assistance refer to Vishay Thin Film's guide to understanding Thin Film precision. Resistor networks or application engineering. All standard products may be ordered directly from Vishay Thin Film.	




GLOBAL PART NUMBER INFORMATION

New Global Part Numbering: TSP1xx-xxxUF



Historical Part Number example: 1xx-xxx (for reference purposes only)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.