


PowerPAK[®]
MLP(QFN), 4 x 4 / 3 x 3
DFN-10, 3 x 3
MLP33-8 / 10
PPAIR[®] 3 x 3


Notes

- (1) 10 sprocket hole pitch cumulative tolerance ± 0.2
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually
- (3) Material: PS + C
- (4) A_0 and B_0 measured as indicated
- (5) K_0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier
- (6) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole
- (7) All sizes in mm unless specified
- (8) Vishay part number must be labeled at all reels of cover and carrier tape
- (9) Surface resistivity - 10^5 max. Ω/sq

VERSION	PACKAGE	A_0	B_0	K_0
- 1	MLP(QFN), 4 x 4	4.35 ± 0.1	4.35 ± 0.1	1.11 ± 0.1
- 2	MLP(QFN), 3 x 3	3.30 ± 0.1	3.30 ± 0.1	1.11 ± 0.1
	MLP33-8 / 10			
	DFN-10, 3 x 3			
	PPAIR, 3 x 3			
ECN T17-0499-Rev. J, 18-Sep-17 DWG: 93-5225-X				