


Surface Mount Crystal



This part is an ultra miniature package with size of 6.0 mm x 3.5 mm x 1.0 mm. With its ceramic base and metal cover it provides the durability and reliability necessary for strenuous process like infrared and vapor phase reflow.

FEATURES

- Ultra-miniature size: 6.0 x 3.5 x 1.0 (mm)
- Seam sealing
- Ceramic package
- Emboss taping
- Reflow soldering
- Compliant to RoHS directive 2002/95/EC


RoHS
COMPLIANT


STANDARD ELECTRICAL SPECIFICATIONS

PARAMETER	SYMBOL	CONDITION	UNIT	MIN.	TYP.	MAX.
Frequency range	F_O		MHz	10.000	-	30.000
Frequency tolerance	$\Delta F/F_O$	at 25 °C	ppm	-	± 30	-
Temperature stability	T_C	ref. to 25 °C	ppm	-	± 30	-
Operating temperature range	T_{OPR}		°C	- 10	-	+ 60
Storage temperature range	T_{STG}		°C	- 40	-	+ 85
Shunt capacitance	C_0		pF	-	-	7
Load capacitance	C_L	customer specified	pF	10	-	series
Insulation resistance	I_R	100 V _{DC}	MΩ	500	-	-
Drive level	D_L		μW	-	10	100
Aging	Fa	at 25 °C, per year	ppm	- 5	-	+ 5

EQUIVALENT SERIES RESISTANCE (ESR) AND MODE OF VIBRATION (MODE)

FREQUENCY RANGE (MHz)	MAX. ESR (Ω)	MODE	FREQUENCY RANGE (MHz)	MAX. ESR (Ω)	MODE
10.000 to 11.999	60	fundamental	19.000 to 19.999	40	fundamental
12.000 to 12.099	50	fundamental	20.000 to 29.999	35	fundamental
13.000 to 18.999	45	fundamental	30.000	30	fundamental

DIMENSIONS in inches [millimeters]



ORDERING INFORMATION

XT46C	-20	25M	e4
MODEL	LOAD blank = series -20 = 20 pF standard -32 = 32 pF	FREQUENCY/MHz	JEDEC LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

X T 4 6	2 0	A	2 5 M
MODEL	LOAD	PACKAGE CODE	FREQUENCY

GLOBAL PART NUMBERING

X	T	9	S
MODEL NUMBER			
XT9S = XT49S XT9M = XT49M XTU1 = XTUM1			

2	0
LOAD CAPACITANCE	
18 = 18 pF 20 = 20 pF NL = series to be specified by customer	

A
PACKAGE CODE
Tape and reel G = RF5 (XT9S) H = RF7 (XT9M)
Bulk A = B04 (all models)

N	A
OPTIONS	
NA = no additional options RR = extended temperature of - 40 °C to + 85 °C Contact factory for all other options	

4	0	M
FREQUENCY		
4M = 4 MHz 40M = 40 MHz 100M = 100 MHz 12M288 = 12.288 MHz M is used as decimal place holder in frequency		

Example: XT49S-20 40M

X	T	3	6
MODEL NUMBER			
XT46 = XT46C XT36 = XT36C			

2	0
LOAD CAPACITANCE	
18 = 18 pF 20 = 20 pF NL = series to be specified by customer	

A
PACKAGE CODE
Tape and reel H = RF7
Bulk A = B04 (all models)

1	2	M
FREQUENCY		
4M = 4 MHz 40M = 40 MHz 100M = 100 MHz 12M288 = 12.288 MHz M is used as decimal place holder in frequency		

Example: XT36C-20 12M



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.