



## 1 Form A Solid-State Relay (Normally Open)



### FEATURES

- Isolation test voltage 5300 V<sub>RMS</sub>
- Load voltage 250 V
- Load current 155 mA / 300 mA
- Clean bounce free switching
- Low power consumption
- Material categorization:  
for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

### APPLICATIONS

- General telecom switching
- Instrumentation
- Industrial controls
- Automatic test equipment

### LINKS TO ADDITIONAL RESOURCES



### DESCRIPTION

The LH1518 is an SPST normally open switch (1 Form A) that can replace electromechanical relays in many applications. The relay is constructed using a GaAlAs LED for actuation control and high reliable MOSFETs for the output switch.

### AGENCY APPROVALS

- [UL 1577](#)
- [cUL](#)
- [DIN EN 60747-5-5 \(VDE 0884-5\)](#)
- [FIMKO](#)

| ORDERING INFORMATION |   |   |   |   |   |                            |                    |   |   |                  |  |  |  |
|----------------------|---|---|---|---|---|----------------------------|--------------------|---|---|------------------|--|--|--|
| L                    | H | 1 | 5 | 1 | 8 | #                          | #                  | # | T | R                |  |  |  |
| PART NUMBER          |   |   |   |   |   | ELECTR.<br>VARIATION       | PACKAGE<br>CONFIG. |   |   | TAPE AND<br>REEL |  |  |  |
| <b>PACKAGE</b>       |   |   |   |   |   | <b>UL, cUL, FIMKO, VDE</b> |                    |   |   |                  |  |  |  |
| SMD-6, tube          |   |   |   |   |   | LH1518AAB                  |                    |   |   |                  |  |  |  |
| SMD-6, tape and reel |   |   |   |   |   | LH1518AABTR                |                    |   |   |                  |  |  |  |
| DIP-6, tube          |   |   |   |   |   | LH1518AT                   |                    |   |   |                  |  |  |  |



| <b>ABSOLUTE MAXIMUM RATINGS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |               |            |             |                    |
|--|---------------|------------|-------------|--------------------|
| PARAMETER  | CONDITION     | SYMBOL     | VALUE       | UNIT               |
| <b>INPUT</b>   |               |            |             |                    |
| IRED continuous forward current  |               | $I_F$      | 50          | mA                 |
| IRED reverse voltage   |               | $V_R$      | 5           | V                  |
| Input power dissipation  |               | $P_{diss}$ | 80          | mW                 |
| <b>OUTPUT</b>  |               |            |             |                    |
| DC or peak AC load voltage   |               | $V_L$      | 250         | V                  |
| Continuous load current (AC/DC configuration)  |               | $I_L$      | 155         | mA                 |
| Continuous load current (DC only configuration)  |               | $I_L$      | 300         | mA                 |
| SSR output power dissipation (continuous)  |               | $P_{diss}$ | 550         | mW                 |
| <b>SSR</b>   |               |            |             |                    |
| Ambient temperature range  |               | $T_{amb}$  | -40 to +85  | $^{\circ}\text{C}$ |
| Storage temperature range  |               | $T_{stg}$  | -40 to +150 | $^{\circ}\text{C}$ |
| Soldering temperature  | t = 10 s max. | $T_{slid}$ | 260         | $^{\circ}\text{C}$ |

**Note**

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.

| <b>ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |   |            |      |      |      |            |
|--|---|------------|------|------|------|------------|
| PARAMETER  | TEST CONDITION                                    | SYMBOL     | MIN. | TYP. | MAX. | UNIT       |
| <b>INPUT</b>   |   |            |      |      |      |            |
| IRED forward current, switch turn-on   | $I_L = 100\text{ mA}$ , t = 10 ms                 | $I_{Fon}$  | -    | 0.4  | 2    | mA         |
| IRED forward current, switch turn-off  | $V_L = \pm 200\text{ V}$                          | $I_{Foff}$ | 0.05 | 0.35 | -    | mA         |
| IRED forward voltage   | $I_F = 10\text{ mA}$                              | $V_F$      | 1.15 | 1.4  | 1.6  | V          |
| <b>OUTPUT</b>  |   |            |      |      |      |            |
| On-resistance (AC/DC configuration)  | $I_F = 5\text{ mA}$ , $I_L = 50\text{ mA}$        | $R_{ON}$   | 6    | 12   | 20   | $\Omega$   |
| On-resistance (DC only configuration)  | $I_F = 5\text{ mA}$ , $I_L = 100\text{ mA}$       | $R_{ON}$   | 1.5  | 3.2  | 5    | $\Omega$   |
| Off-resistance   | $I_F = 0\text{ mA}$ , $V_L = \pm 100\text{ V}$    | $R_{OFF}$  | 0.5  | 5000 | -    | G $\Omega$ |
| Off-state leakage current  | $I_F = 0\text{ mA}$ , $V_L = \pm 100\text{ V}$    | $I_O$      | -    | < 1  | 200  | nA         |
|  | $I_F = 0\text{ mA}$ , $V_L = \pm 250\text{ V}$    | $I_O$      | -    | < 1  | 1000 | nA         |
| Output capacitance (AC/DC configuration)   | $I_F = 0\text{ mA}$ , $V_L = 1\text{ V}$ , 1 MHz  | $C_O$      | -    | 39   | -    | pF         |
|  | $I_F = 0\text{ mA}$ , $V_L = 50\text{ V}$ , 1 MHz | $C_O$      | -    | 6    | -    | pF         |
| <b>TRANSFER</b>  |   |            |      |      |      |            |
| Capacitance (input to output)  | $V_{IO} = 1\text{ V}$                             | $C_{IO}$   | -    | 0.4  | -    | pF         |

**Note**

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.


**PIN CONFIGURATION**


Fig. 1 - Pin Configuration

| <b>SWITCHING CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified) |  |           |      |      |      |      |
|---|--|-----------|------|------|------|------|
| PARAMETER   | TEST CONDITION                             | SYMBOL    | MIN. | TYP. | MAX. | UNIT |
| Turn-on time  | $I_F = 5\text{ mA}$ , $I_L = 50\text{ mA}$ | $t_{on}$  | -    | 0.20 | 3    | ms   |
| Turn-off time   | $I_F = 5\text{ mA}$ , $I_L = 50\text{ mA}$ | $t_{off}$ | -    | 0.03 | 3    | ms   |




Fig. 2 - Timing Schematic

| <b>SAFETY AND INSULATION RATINGS</b>         |  |            |                |                    |
|--|--|------------|----------------|--------------------|
| PARAMETER                                    | CONDITION  | SYMBOL     | VALUE          | UNIT               |
| Climatic classification                      | According to IEC 68 part 1   |            | 40 / 85 / 21   |                    |
| Pollution degree                             | According to DIN VDE 0109  |            | 2              |                    |
| Comparative tracking index                   | Insulation group IIIa  | CTI        | 175            |                    |
| Maximum rated withstanding isolation voltage | According to UL1577, $t = 1\text{ min}$  | $V_{ISO}$  | 5300           | $V_{RMS}$          |
| Maximum transient isolation voltage          | According to DIN EN 60747-5-5  | $V_{IOTM}$ | 8000           | $V_{peak}$         |
| Maximum repetitive peak isolation voltage    | According to DIN EN 60747-5-5  | $V_{IORM}$ | 890            | $V_{peak}$         |
| Insulation resistance                        | $V_{IO} = 500\text{ V}$ , $T_{amb} = 25\text{ }^{\circ}\text{C}$   | $R_{IO}$   | $\geq 10^{12}$ | $\Omega$           |
|  | $V_{IO} = 500\text{ V}$ , $T_{amb} = 100\text{ }^{\circ}\text{C}$  | $R_{IO}$   | $\geq 10^{11}$ | $\Omega$           |
| Output safety power                          |  | $P_{SO}$   | 700            | mW                 |
| Input safety current                         |  | $I_{SI}$   | 240            | mA                 |
| Safety temperature                           |  | $T_S$      | 175            | $^{\circ}\text{C}$ |
| Creepage distance                            |  |            | $\geq 7$       | mm                 |
| Clearance distance                           |  |            | $\geq 7$       | mm                 |
| Insulation thickness                         |  | DTI        | $\geq 0.4$     | mm                 |
| Input to output test voltage, method B       | $V_{IORM} \times 1.875 = V_{PR}$ , 100 % production test with $t_M = 1\text{ s}$ , partial discharge $< 5\text{ pC}$ | $V_{PR}$   | 1669           | $V_{peak}$         |
| Input to output test voltage, method A       | $V_{IORM} \times 1.6 = V_{PR}$ , 100 % sample test with $t_M = 10\text{ s}$ , partial discharge $< 5\text{ pC}$      | $V_{PR}$   | 1424           | $V_{peak}$         |

**Note**

- As per IEC 60747-5-5, § 7.4.3.8.2, this optocoupler is suitable for "safe electrical insulation" only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.




Fig. 3 - Output Safety Power vs. Ambient Temperature




Fig. 4 - Input Safety Current vs. Ambient Temperature

**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)




Fig. 5 - Load Current vs. Ambient Temperature




Fig. 7 - Forward Current vs. Forward Voltage




Fig. 6 - Forward Voltage vs. Ambient Temperature




Fig. 8 - Normalized Forward Current for Switch Turn-On vs. Ambient Temperature




Fig. 9 - Normalized On-Resistance vs. Ambient Temperature




Fig. 12 - Turn-On Time vs. Forward Current




Fig. 10 - Switch Capacitance vs. Applied Voltage




Fig. 13 - Normalized Turn-On Time vs. Ambient Temperature




Fig. 11 - Off-State Leakage Current vs. Load Voltage




Fig. 14 - Turn-Off Time vs. Forward Current




Fig. 15 - Normalized Turn-Off Time vs. Ambient Temperature

**PACKAGE DIMENSIONS** (in millimeters)

**SMD-6**




Fig. 16 - Package Drawings



## DIP-6




Fig. 17 - Package Drawings

## PACKAGE MARKING




Fig. 18 - LH1518

### Notes

- XXXX = LMC (lot marking code)
- Tape and reel suffix (TR) is not part of the package marking

## PACKING INFORMATION (in millimeters)




Fig. 19 - Tape and Reel Packing

| TAPE AND REEL PACKING |            |
|-----------------------|------------|
| TYPE                  | UNITS/REEL |
| SMD-6                 | 1000       |

| TUBE PACKING |            |           |           |
|--------------|------------|-----------|-----------|
| TYPE         | UNITS/TUBE | TUBES/BOX | UNITS/BOX |
| SMD-6        | 50         | 40        | 2000      |
| DIP-6        | 50         | 40        | 2000      |

## SOLDER PROFILES




Fig. 20 - Wave Soldering Double Wave Profile According to J-STD-020 for DIP Devices




Fig. 21 - Lead (Pb)-free Reflow Solder Profile According to J-STD-020 for SMD Devices

## HANDLING AND STORAGE CONDITIONS

ESD level: HBM class 2

Floor life: unlimited

Conditions:  $T_{amb} < 30\text{ °C}$ , RH < 60 %

Moisture sensitivity level 1, according to J-STD-020






## Footprint and Schematic Information for LH1518AAB, LH1518AABTR, LH1518AT

The footprint and schematic symbols for the following parts can be accessed using the associated links. They are available in Eagle, Altium, KiCad, OrCAD / Allegro, Pulsonix, and PADS.

Note that the 3D models for these parts can be found on the Vishay product page.

| PART NUMBER | FOOTPRINT / SCHEMATIC  |
|-------------|--|
| LH1518AAB   | <a href="http://www.snapeda.com/parts/LH1518AAB/Vishay/view-part">www.snapeda.com/parts/LH1518AAB/Vishay/view-part</a>     |
| LH1518AABTR | <a href="http://www.snapeda.com/parts/LH1518AABTR/Vishay/view-part">www.snapeda.com/parts/LH1518AABTR/Vishay/view-part</a> |
| LH1518AT    | <a href="http://www.snapeda.com/parts/LH1518AT/Vishay/view-part">www.snapeda.com/parts/LH1518AT/Vishay/view-part</a>       |

For technical issues and product support, please contact [optocoupleranswers@vishay.com](mailto:optocoupleranswers@vishay.com).





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.