

## Optocoupler



### CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO.: CQC13001088690

Valid from: Aug.15,2023

Valid until:Aug.14,2028

**NAME AND REGISTERED ADDRESS OF THE APPLICANT** Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

**NAME AND REGISTERED ADDRESS OF THE MANUFACTURER** Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

**NAME AND LOCATION OF THE FACTORY** Vishay Semiconductor Malaysia Sdn Bhd  
No. 1710-1, Kawasan Perindustrian Krubong75250 Melaka

**PRODUCT NAME, MODEL AND SPECIFICATION** Opto Coupler  
See appendix : Reinforced Insulation, pass thermal cycling test at 110°C ( Altitude up to 5000m )

**THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS** GB 4943.1-2022

**TYPE OF CERTIFICATION SCHEMES** Type Testing of Product + Follow up Factory Inspection

This is to certify that the above mentioned product(s) complies with the requirements of certification rules of CQC11-471543-2022.

Date of original issued: Feb.19,2013

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

The certificate information is available through the QR code below or CNCA's website: www.cnca.gov.cn



SIGNATURE:



CHINA QUALITY CERTIFICATION CENTRE



http://www.cqc.com.cn

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666



CERTIFICATE OF PRODUCT CERTIFICATION

CERTIFICATE NO. : CQC13001088690

page 1 of 2

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

型号	内部爬电距离 规格 (mm)	外部爬电距离 规格 (mm)	内部穿透距离 (绝缘厚度) 规 格 (mm)
ILD(1,2,5)-xxxx、ILD(1,2,5)-xxxxT、 ILD(1,2,5)-xxxxWP、 ILD(1,2,5)-xxxxTWP、 ILD61(0,5)-(1,2,3,4)xxxx、 ILD61(0,5)-(1,2,3,4)xxxxT、 ILD61(0,5)-Exxxx、ILD621-xxxx、 ILD621-xxxxT、ILD621GB-xxxx、 ILD621GB-xxxxT、ILD74-xxxx、 ILD74-xxxxT、6N13(5,6)-xxxx、 6N13(5,6)-xxxxT、 SFH613(5,6,8,9)-xxxx、 SFH613(5,6,8,9)-xxxxT、 SFH632(5,6)-xxxx、SFH632(5,6)-xxxxT、 SFH632(5,6)-Exxxx、SFH6345-xxxx、 SFH6345-xxxxT、SFH670(1,2,5)-xxxx、 SFH670(1,2,5)-xxxxT、 SFH671(1,2,9)-xxxx、 SFH671(1,2,9)-xxxxT、MCT6-xxxx、 MCT6-xxxxT、IL300-xxxx、 IL300-xxxxT、IL300-yyyy-xxxx、 IL300-yyyy-xxxxT、IL300A-xxxx、 IL300A-xxxxT、IL300A-yyyy-xxxx、 IL300A-yyyy-xxxxT、 VOA300-yyyy-xxxxT (注: yyyy-K3分 箱; xxxx - 封装形式或VDE局部放电或 客户的代号; T是指表面粘接式封装,	N/A	DIP封装形式: >7.4 其他封装形 式: >8.0	≥0.4



CHINA QUALITY CERTIFICATION CENTRE



CERTIFICATE OF PRODUCT CERTIFICATION


CERTIFICATE NO. : CQC13001088690

page2of2

paper:

This certificate and attachments shall be used at the same time, and the verification instructions can be found in the main certificate.

包装形式可以是编带和卷轴或是料管。)			
--------------------	--	--	--



CHINA QUALITY CERTIFICATION CENTRE

<http://www.cqc.com.cn>

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

Tel: +86 10 83886666