

Automotive Multilayer Chip Ferrite Beads



LINKS TO ADDITIONAL RESOURCES



White Paper

MECHANICAL SPECIFICATIONS

Solderability: per J-STD-002

Resistance to Solder Heat: 255 °C, 30 s max., 3x max. through reflow

Terminal Strength: 17.7 N force for 60 s

Flex: 0.079" [2 mm] mounted on 0.063" [1.6 mm] thick PC board

FEATURES

- 1.6 mm x 0.8 mm x 0.8 mm package
- Multilayer chip ferrite bead for high current filtering
- Wide variety of impedance values
- Extended current rating
- Multiple performance curves to target specific frequencies
- Silver (Ag) inner conductor with Cu / Ni / Sn electrode plating
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

ENVIRONMENTAL SPECIFICATIONS

Operating Temperature: -55 °C to +125 °C

Thermal Shock: 1000 cycles, -55 °C (for 30 min ± 3 min) to +125 °C (for 30 min ± 3 min) with 20 s max. transition interval

Biased Humidity: 85 % RH at 85 °C, 1000 h at full rated current

STANDARD ELECTRICAL SPECIFICATIONS

PART NUMBER	Z ± 25 % AT 100 MHz (Ω)	DCR MAX. AT 25 °C (mΩ)	RATED DC CURRENT TYP. AT 85 °C ⁽¹⁾ (A)	Z _{pk} ⁽²⁾ (Ω)	F AT Z _{pk} ⁽³⁾ (MHz)	Z TYP. AT 100 MHz (Ω)	F AT Z _{DO} ⁽⁴⁾ (MHz)	XL / XR x OVER ⁽⁵⁾ (MHz)
ILHB0603ER220VHC41	22	10	6	28	522	22	2921	32.5
ILHB0603ER260VHC41	26	7	6	32.6	710	26.5	2806	33
ILHB0603ER280VHC41	28	10	6	38	475	28	2297	27.7
ILHB0603ER300VHC42	30	10	5	48	691	30	2920	83
ILHB0603ER300VHC31	30	30	3	50	1000	30	8000	108
ILHB0603ER300VHC32	30	30	3	38	489	30	2921	26
ILHB0603ER300VGP11	30	50	2	52	890	30	7000	111
ILHB0603ER300VGP12	30	50	2	38	489	30	2920	31
ILHB0603ER300VHC41	30	60	1.8	238	638	28	4000	439
ILHB0603ER600VHC42	60	20	3.5	89	710	60	2921	76
ILHB0603ER600VHC33	60	40	2.5	78	475	60	1957	30
ILHB0603ER600VHC31	60	80	2	104	867	60	5000	114
ILHB0603ER600VGP11	60	100	0.5	110	1000	60	4000	114
ILHB0603ER600VGP12	60	100	0.5	76	522	60	4000	36
ILHB0603ER600VHC41	60	100	1.2	489	558	60	4000	400
ILHB0603ER600VHC32	60	100	1.4	100	769	65	4000	75
ILHB0603ER700VHC41	70	20	4	87	457	70	1560	37
ILHB0603ER750VHC31	75	150	1	142	903	75	5000	134
ILHB0603ER800VGP11	80	150	0.4	313	759	80	3000	110
ILHB0603ER101VHC42	100	30	3	144	495	100	1459	69
ILHB0603ER101VHC41	100	150	1	1250	390	100	1960	350
ILHB0603ER101VGP11	100	200	0.3	158	566	100	1831	105
ILHB0603ER121VHC32	120	50	2	148	416	120	1277	32
ILHB0603ER121VGP11	120	200	0.3	200	673	120	2423	108
ILHB0603ER121VGP12	120	200	0.3	185	457	128	1581	65
ILHB0603ER121VGP13	120	200	0.3	155	482	120	1880	33
ILHB0603ER121VHC31	120	200	1	200	613	120	2360	111
ILHB0603ER181VHC41	180	50	2.2	254	340	180	880	73

**STANDARD ELECTRICAL SPECIFICATIONS**

PART NUMBER	Z $\pm$ 25 % AT 100 MHz (Ω)	DCR MAX. AT 25 °C (m Ω)	RATED DC CURRENT TYP. AT 85 °C ⁽¹⁾ (A)	Z _{pk} ⁽²⁾ (Ω)	F AT Z _{pk} ⁽³⁾ (MHz)	Z TYP. AT 100 MHz (Ω)	F AT Z _{DO} ⁽⁴⁾ (MHz)	XL / XR x OVER ⁽⁵⁾ (MHz)
ILHB0603ER181VGP11	180	300	0.3	244	336	180	770	70
ILHB0603ER181VHF11	180	550	0.2	242	428	180	1580	32
ILHB0603ER221VHC41	220	50	2.2	255	235	220	445	35
ILHB0603ER221VHC42	220	50	2.2	300	302	220	691	72
ILHB0603ER221VHC32	220	100	1.4	259	234	220	515	34
ILHB0603ER221VHC31	220	200	1	310	323	220	750	89
ILHB0603ER221VGP11	220	300	0.3	325	360	220	879	99
ILHB0603ER221VGP12	220	300	0.3	254	244	220	489	32
ILHB0603ER301VGP11	300	350	0.2	390	231	300	428	86
ILHB0603ER301VGP12	300	350	0.2	358	251	300	495	30
ILHB0603ER301VHF11	300	750	0.2	434	395	314	1500	53
ILHB0603ER331VHC41	330	70	1.5	383	208	330	390	34
ILHB0603ER331VHC42	330	80	1.7	429	265	330	544	64
ILHB0603ER331VHC31	330	140	1.2	381	205	330	395	34
ILHB0603ER391VHC41	390	120	1.5	383	203	400	244	32
ILHB0603ER391VHC31	390	140	1	432	173	390	283	32
ILHB0603ER471VHC41	470	120	1.5	524	173	470	295	31
ILHB0603ER471VHC31	470	200	1	512	168	470	251	32
ILHB0603ER471VGP12	470	400	0.2	513	168	470	283	31
ILHB0603ER471VGP11	470	450	0.2	580	185	470	310	83
ILHB0603ER471VHF12	470	850	0.2	624	395	460	1195	26
ILHB0603ER471VHF11	470	1200	0.1	1233	682	470	2390	205
ILHB0603ER601VHC42	600	150	1	677	173	600	268	55
ILHB0603ER601VHC41	600	150	1.3	630	141	600	202	31
ILHB0603ER601VHC31	600	350	0.5	805	219	600	400	86
ILHB0603ER601VGP11	600	450	0.2	714	159	600	247	82
ILHB0603ER601VGP12	600	450	0.2	725	197	600	345	62
ILHB0603ER601VGP13	600	500	0.2	640	157	600	231	30
ILHB0603ER601VHF12	600	1000	0.2	806	389	585	1080	32
ILHB0603ER601VHF11	600	1500	0.1	1567	551	600	1906	200
ILHB0603ER751VGP11	750	500	0.2	893	155	750	225	80
ILHB0603ER102VGP11	1000	600	0.2	1100	130	1000	182	75
ILHB0603ER102VGP12	1000	600	0.2	1060	134	1000	185	54
ILHB0603ER102VGP13	1000	600	0.2	1003	100	1000	1000	27
ILHB0603ER102VHF12	1000	1600	0.1	1367	350	1000	940	31
ILHB0603ER102VHF11	1000	1800	0.05	2526	439	1000	1384	187
ILHB0603ER152VGP11	1500	700	0.15	1516	113	1500	125	68
ILHB0603ER182VGP11	1800	900	0.1	1952	124	1800	157	75
ILHB0603ER202VGP11	2000	1200	0.1	2045	105	2000	116	65
ILHB0603ER222VGP11	2200	1200	0.1	2200	100	2200	100	65
ILHB0603ER252VGP11	2500	1200	0.1	2300	78	2000	n/a	59

Notes

- All test data is referenced to 25 °C ambient (unless otherwise indicated)
- Operating temperature range: -55 °C to +125 °C
- Storage condition: < 40 °C and < 70 % RH (in packaging)
- The part temperature (ambient + temp. rise) should not exceed the maximum rating under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application

⁽¹⁾ Rated current is the DC current that causes a 40 °C temperature rise at 20 °C ambient

⁽²⁾ Z_{pk} = peak of impedance curve

⁽³⁾ F at Z_{pk} = frequency of Z_{pk}

⁽⁴⁾ F at Z_{DO} = frequency above 100 MHz where Z drops to nominal Z

⁽⁵⁾ XL / XR x over = crossover point for inductive reactance and resistance impedance

GLOBAL PART NUMBER
I L H B

PRODUCT FAMILY

0 6 0 3

SIZE

E R

PACKAGE
CODE

ER = tape and reel

3 0 1

INDUCTANCE
VALUE


301 = Ω
V

IMPEDANCE
TOLERANCE


V = $\pm 25\%$
H C 1

APPLICATION

HCxx = high current
HFxx = high frequency
GPxx = general purpose







DIMENSIONS in inches [millimeters]








Dimensional outline















Typical pad layout







SIZE	A	B	C	D	E	F	G
0603	0.063 $\pm$ 0.006 [1.6 $\pm$ 0.15]	0.031 $\pm$ 0.006 [0.8 $\pm$ 0.15]	0.031 $\pm$ 0.006 [0.8 $\pm$ 0.15]	0.016 $\pm$ 0.008 [0.4 $\pm$ 0.20]	0.085 [2.15]	0.025 [0.63]	0.041 [1.05]







PERFORMANCE GRAPHS








PERFORMANCE GRAPHS








PERFORMANCE GRAPHS








PERFORMANCE GRAPHS








PERFORMANCE GRAPHS








PERFORMANCE GRAPHS





PERFORMANCE GRAPHS


PERFORMANCE GRAPHS


PERFORMANCE GRAPHS


PERFORMANCE GRAPHS


PERFORMANCE GRAPHS


PERFORMANCE GRAPHS




Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.