

# Proximity Sensor With VCSEL in Ultra Thin Small Package, I<sup>2</sup>C Interface



## LINKS TO ADDITIONAL RESOURCES



3D Models



Application Notes

## DESCRIPTION

The VCNL36829UM is a fully integrated proximity sensor. It combines a vertical-cavity surface-emitting laser (VCSEL), photodiode, and application-specific integrated circuit (ASIC) within a ultra thin small package. The VCNL36829UM has been developed for proximity detection applications that offers quite some advanced features including dual slave address, low power consumption, smallest volume package design with isolation wall for the best signal to noise ratio performance with the flexible of mechanical design. In addition, given the typical rated supply voltage of 1.8 V to reduce power consumption, the sensor is intended for battery-powered applications.

## FEATURES

- Package type: transparent mold with isolation wall
- Dimensions (L x W x H in mm): 1.6 x 1.0 x 0.35
- Integrated modules: vertical-cavity surface-emitting laser (VCSEL) and a proximity sensor (PS)
- Support both 1.2 V and 1.8 V I<sup>2</sup>C I / O with 1.8 V supply voltage
- I<sup>2</sup>C interface up to 1 MHz (fast mode plus)
- Present on I<sup>3</sup>C bus (spike filter implemented)
- Low power consumption with 5  $\mu$ A idle current
- A small package allows a design with a small window size
- Smart dual I<sup>2</sup>C slave address in one package
- Immunity to red glow (940 nm VCSEL)
- Programmable I<sub>VCSEL</sub> sink current
- Intelligent cancellation to reduce cross talk phenomenon
- Smart persistence scheme to reduce measurement response time
- Interrupt functionality
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
**HALOGEN**  
**FREE**  
**GREEN**  
(5-2008)

## APPLICATIONS

- True wireless stereo (TWS) earbuds
- VR / AR headsets and smart glasses
- Smart wearables / IOT devices
- Touchless button / dispensing

## PRODUCT SUMMARY


PART NUMBER	OPERATING RANGE (mm)	OPERATING VOLTAGE RANGE (V)	I <sup>2</sup> C BUS VOLTAGE RANGE (V)	MAX. VCSEL DRIVING CURRENT (mA)	ADC RESOLUTION PROXIMITY / AMBIENT LIGHT
VCNL36829UM	50	1.65 to 2.00	1.08 to 3.6	18	16 bit / -

## ORDERING INFORMATION

ORDERING CODE	PACKAGING	VOLUME <sup>(1)</sup>	REMARKS
VCNL36829UM	Tape and reel	MOQ: 5000 pcs, 5000 pcs/reel	1.6 mm x 1.0 mm x 0.35 mm

### Note

<sup>(1)</sup> MOQ: minimum order quantity

**PIN DEFINITION**


PIN DESCRIPTION			
PIN NUMBER	PIN NAME	TYPE	DESCRIPTION
1	INT	O (open drain)	Interrupt
2	V <sub>DD</sub>	I	Supply voltage
3	GND	I	Ground
4	VCSEL <sub>A</sub>	I	VCSEL anode
5	SCL <sup>(1)</sup>	I / O (open drain)	I <sup>2</sup> C serial clock
6	SDA <sup>(1)</sup>	I / O (open drain)	I <sup>2</sup> C serial data

**Note**

<sup>(1)</sup> Pin 5 (SCL) and pin 6 (SDA) can be swapped to change the slave address from 0x60 to 0x51; please refer to Table 1


ABSOLUTE MAXIMUM RATINGS (T <sub>amb</sub> = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	MIN.	MAX.	UNIT
Supply voltage		V <sub>DD</sub>	0	2	V
Ambient temperature range		T <sub>amb</sub>	-40	+85	°C
Storage temperature range		T <sub>stg</sub>	-40	+100	°C

<b>BASIC CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
<b>ASIC</b>						
Supply voltage		$V_{DD}$	1.65	1.80	2.00	V
Supply current <sup>(1)</sup>	Shutdown state; light condition = dark; $V_{DD} = 1.8\text{ V}$	$I_{DD}$	-	1	-	$\mu\text{A}$
	Idle state <sup>(2)</sup> ; $V_{DD} = 1.8\text{ V}$		-	5	-	
	Active state <sup>(2)</sup> ; $V_{DD} = 1.8\text{ V}$		-	310	-	
I <sup>2</sup> C supply voltage		$V_{PULL\ UP}$	1.08	1.8	3.6	V
I <sup>2</sup> C signal input, logic high	$V_{DD} = 1.8\text{ V}$	$V_{IH}$	0.9	-	-	V
I <sup>2</sup> C signal input, logic low	$V_{DD} = 1.8\text{ V}$	$V_{IL}$	-	-	0.45	V
<b>VCSEL</b>						
Supply voltage of the VCSEL <sup>(3)</sup>		$V_{VCSEL}$	2.8	-	3.6	V
Forward voltage	$I_F = 9\text{ mA}$	$V_F$	-	2	-	V
Forward current		$I_F$	8	-	18	mA
Angle of half intensity	FWHM	$\phi$	-	$\pm 4.5$	-	$^{\circ}$
Peak wavelength	$I_F = 9\text{ mA}$	$\lambda_p$	930	940	955	nm
Spectral bandwidth	$I_F = 9\text{ mA}$	$\Delta\lambda$	-	3	-	nm
<b>PHOTODIODE</b>						
Angle of half sensitivity		$\phi$	-	$\pm 60$	-	$^{\circ}$
Peak sensitivity wavelength		$\lambda_p$	-	850	-	nm

**Notes**

- (1) Actual current consumption depends on the register settings. Please refer to the application note on the current consumption
- (2) Excluding VCSEL driving current
- (3)  $V_{VCSEL}$  should at least match the minimum required supply voltage for the VCSEL  $V_{VCSEL, min}$ . Please refer to the  $V_{VCSEL, min}$  table


<b><math>V_{VCSEL, min}</math></b>						
PS_CURRENT ( $I_F$ )	8 mA	10 mA	12 mA	14 mA	16 mA	18 mA
$V_{VCSEL, min.}$	2.80 V	2.90 V	3.00 V	3.08 V	3.16 V	3.22 V
$V_{VCSEL, max.}$	3.6 V					

**LASER CLASS**

**Note**

- Product specification with IEC / EN 60825-1:2014 compliance and above label




## BLOCK DIAGRAM



<b>I<sup>2</sup>C BUS TIMING CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)						
PARAMETER	SYMBOL	STANDARD MODE		FAST MODE		UNIT
		MIN.	MAX.	MIN.	MAX.	
Clock frequency	$f_{(I2CCLK)}$	10	100	10	400	kHz
Bus free time between start and stop condition	$t_{(BUF)}$	4.7	-	1.3	-	$\mu\text{s}$
Hold time after (repeated) start condition; after this period, the first clock is generated	$t_{(HDSTA)}$	4.0	-	0.6	-	$\mu\text{s}$
Repeated start condition setup time	$t_{(SUSTA)}$	4.7	-	0.6	-	$\mu\text{s}$
Stop condition setup time	$t_{(SUSTO)}$	4.0	-	0.6	-	$\mu\text{s}$
Data hold time	$t_{(HDDAT)}$	0	3450	0	900	ns
Data setup time	$t_{(SUDAT)}$	250	-	100	-	ns
I <sup>2</sup> C clock (SCL) low period	$t_{(LOW)}$	4.7	-	1.3	-	$\mu\text{s}$
I <sup>2</sup> C clock (SCL) high period	$t_{(HIGH)}$	4.0	-	0.6	-	$\mu\text{s}$
Clock / data fall time	$t_{(f)}$	-	300	-	300	ns
Clock / data rise time	$t_{(r)}$	-	1000	-	300	ns

**Note**

- Data based on standard I<sup>2</sup>C protocol requirement, not tested in production


Fig. 1 - I<sup>2</sup>C Bus Timing Diagram



## PARAMETER TIMING INFORMATION




Fig. 2 - I<sup>2</sup>C Bus Timing for Sending Word Command Format




Fig. 3 - I<sup>2</sup>C Bus Timing for Receiving Word Command Format


**TYPICAL PERFORMANCE CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)


Fig. 4 - Supply Current vs. Ambient Temperature




Fig. 7 - Relative Radiant Intensity vs. Wavelength of the VCSEL




Fig. 5 - Forward Current vs. Forward Voltage of the VCSEL




Fig. 8 - Relative Sensitivity vs. Angular Displacement of the Photodiode




Fig. 6 - Relative Radiant Intensity vs. Angular Displacement of the VCSEL




Fig. 9 - Relative Spectral Sensitivity vs. Wavelength of the Photodiode




Fig. 10 - Proximity Value vs. Distance (IT = 2T)




Fig. 11 - Proximity Value vs. Distance (IT = 8T)

## APPLICATION INFORMATION

### Slave Address Selection

The VCNL36829UM supports a smart dual slave address where the designer can change the slave address by swapping the SCL and SDA pins, as shown in Table 1.

TABLE 1 - SLAVE ADDRESS TABLE				
PIN 5	PIN 6	7 BIT SLAVE ADDRESS	8 BIT SLAVE ADDRESS (WRITE)	8 BIT SLAVE ADDRESS (READ)
SCL	SDA	0x60	0xC0	0xC1
SDA	SCL	0x51	0xA2	0xA3

A smart dual slave address provides the flexibility for the designer to connect two devices from two different slave addresses on the same I<sup>2</sup>C bus. Besides that, the two slave address options allow designers to select a different slave address if one is used by the other slave devices on the same I<sup>2</sup>C bus in a single device application.

To ensure more stable slave address recognition, especially in systems with higher noise levels, it is recommended to follow a specific power-on sequence: apply power to the I<sup>2</sup>C bus first, followed by V<sub>DD</sub>. This sequence helps the IC determine the correct slave address more reliably in noisy environments.

### Application Circuit With a Single Device - Slave Address 0x60

Fig. 12 shows an application circuit example with a single device. As described in Table 1, when pins 5 and 6 are connected to the clock and data signal from the microcontroller, as shown in Fig. 12, they will then be configured as an SCL pin and SDA pin, respectively. The 7 bit slave address option of 0x60 will be automatically selected.




Fig. 12 - Application Circuit Example for a Single VCNL36829UM - Slave Address 0x60



### Application Circuit With a Single Device - Slave Address 0x51

On the other hand, when pins 5 and 6 are connected to the data and clock signal from the microcontroller, as shown in Fig. 13, they will then be configured as an SDA pin and SCL pin, respectively. The 7 bit slave address option of 0x51 will be automatically selected.




Fig. 13 - Application Circuit Example for a Single VCNL36829UM - Slave Address 0x51

Table 2 shows the required values and the explanation for the individual application circuit parameters.

TABLE 2 - APPLICATION CIRCUIT PARAMETERS		
CIRCUIT PARAMETER	VALUE	DESCRIPTION
$V_{DD}$	1.65 V to 2.00 V	A stable power supply such as a low dropout regulator or a switching regulator is required; the power supply isolation can be further improved with a decoupling capacitor $C_1$
$V_{VCSEL}$	2.80 V to 3.60 V	A stable power supply such as a low dropout regulator or a switching regulator that can supply an adequate amount of power (max. VCSEL pulse driving current of 18 mA) is required; the power supply isolation can be further improved with a decoupling capacitor $C_2$ ; the minimum voltage depends on the selected driving current of the VCSEL; please refer to Table $V_{VCSEL, min.}$ for reference
$V_{PULL UP}$	1.2 V to 3.6 V	A stable power supply such as a low dropout regulator or a switching regulator is required; a voltage level shifter is required if the I <sup>2</sup> C bus voltage from the microcontroller is higher than 3.6 V
$C_1 - C_4$	100 nF to 1 $\mu$ F	Decoupling capacitors are recommended to reduce the noise in the supply voltage
$R_1 - R_2$	2.2 k $\Omega$ to 4.7 k $\Omega$	Pull-up resistors within the range of 2.2 k $\Omega$ to 4.7 k $\Omega$ are recommended; any increase in bus capacitance or resistance will increase the logic high transition time
$R_3$	4.7 k $\Omega$ to 22 k $\Omega$	Pull-up resistor within the range of 4.7 k $\Omega$ to 22 k $\Omega$ is recommended

### Application Circuit With a Smart Dual Slave Address

Fig. 14 shows an application circuit example with a smart dual slave address. By swapping the SCL and SDA pins of the second device, as shown in Table 1, the designer can change the 7 bit slave address of the VCNL36829UM. This provides the flexibility for the designer to connect two devices from two different slave addresses on the same I<sup>2</sup>C bus.





Fig. 14 - Application Circuit Example for Two VCNL36829UMs - Smart Dual Slave Address


### I<sup>2</sup>C Write and Read Protocol

The communication with the VCNL36829UM can be performed via I<sup>2</sup>C. The I<sup>2</sup>C write and read protocol when communicating with the proximity sensor is shown in Fig. 15.

Send byte → write command to VCNL36829UM



Receive byte → read data from VCNL36829UM



S = start condition  
P = stop condition  
A = acknowledge  
N = not acknowledge

☐ Host action  
☒ VCNL36829UM response

Fig. 15 - I<sup>2</sup>C Write and Read Protocol

It is imperative that only the restart condition for the I<sup>2</sup>C read is implemented instead of the stop and restart condition.



## Function Description

**TABLE 3 - COMMAND CODE AND REGISTER DESCRIPTION**

COMMAND CODE	DATA BYTE LOW / HIGH	REGISTER NAME	DEFAULT VALUE	FUNCTION	ACCESS
0x00	L	PS_CONF1_L	0x00	Internal calibration setting	Write and read
				Active force mode trigger setting	
				Switch the sensor on / off	
	H	PS_CONF1_H	0x01	Interrupt setting	
				Persistence setting	
				Shutdown setting	
0x01	L	PS_CONF2_L	0x00	Wait time setting	
	H	PS_CONF2_H	0x00	Integration time setting	
0x02	L	PS_CONF3_L	0x00	VCSEL driving current setting	
	H	PS_CONF3_H	0x00	High gain setting	
0x03	L	PS_CONF4_L	0x00	Reserved	
	H	PS_CONF4_H	0x00	Sunlight cancellation setting	
0x04	L	PS_THDL_L	0x00	Low threshold interrupt value setting (low byte)	
	H	PS_THDL_H	0x00	Low threshold interrupt value setting (high byte)	
0x05	L	PS_THDH_L	0x00	High threshold interrupt value setting (low byte)	
	H	PS_THDH_H	0x00	High threshold interrupt value setting (high byte)	
0x06	L	PS_CANC_L	0x00	Offset count cancellation value setting (low byte)	
	H	PS_CANC_H	0x00	Offset count cancellation value setting (high byte)	
0x08	L	PS_CONF5_L	0x00	Reserved (must be set to 0xA0)	
	H	PS_CONF5_H	0x00	Reserved	
0xF8	L	PS_DATA_L	0x00	Proximity output data (low byte)	Read only
	H	PS_DATA_H	0x00	Proximity output data (high byte)	
0xF9	L	Reserved	0x00 to 0xFF	Reserved	
	H	INT_FLAG	0x00	PS interrupt flag	
0xFA	L	VCNL36829UM_ID_L	0x29	Device ID	
	H	VCNL36829UM_ID_H	0x00 / 0x10	Device ID <sup>(1)</sup> Slave address: 0x60; ID = 0x00 Slave address: 0x51; ID = 0x10	

**Notes**

- All of the reserved registers are used for internal test. These values must be kept constant.
- <sup>(1)</sup> The default ID depends on the connection of the SCL and SDA pins on the VCNL36829UM with the SCL and SDA pins on the host MCU. If pins 5 and 6 on the VCNL36829UM are connected to the SCL and SDA pins on the host, the default value will be 0x00. On the other hand, if pins 5 and 6 on the VCNL36829UM are connected to the SDA and SCL pins on the host, the default value will be 0x10. Please refer to Fig. 13.



## Command Register Format

**TABLE 4 - REGISTER NAME: PS\_CONF1\_L**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
PS_CAL	Reserved	PS_TRIG	PS_MODE	Reserved			PS_ON
<b>COMMAND CODE</b>					<b>0x00</b>		
Bit Name	Function		Bit	Value	Description		
PS_CAL	Enable / disable the internal calibration		7	0x0 (0b0)	Disable (default)		
				0x1 (0b1)	Enable		
Reserved	Reserved		6	0x0 (0b0)	Should be kept default		
PS_TRIG	Set the active force mode trigger; This bit will be reset to 0 after the measurement cycle		5	0x0 (0b0)	Off (default)		
				0x1 (0b1)	Trigger		
PS_MODE	Set the measurement mode of the sensor		4	0x0 (0b0)	Auto Mode (default)		
				0x1 (0b1)	Active force mode		
Reserved	Reserved		3:1	0x0 (0b000)	Should be kept default		
PS_ON	Switch the sensor on / off		0	0x0 (0b0)	Turn off the sensor (shutdown) (default)		
				0x1 (0b1)	Turn on the sensor		

**TABLE 5 - REGISTER NAME: PS\_CONF1\_H**

Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
PS_INT		PS_PERS		PS_SMART_PERS	PS_SP_INT	PS_START_INT	PS_SD
COMMAND CODE					0x00		
Bit Name		Function		Bit	Value	Description	
PS_INT	Set the interrupt mode setting		15 : 14	0x0 (0b00)	Interrupt disable (default)		
				0x1 (0b01)	Logic High/Low mode		
				0x2 (0b10)	First high		
				0x3 (0b11)	Trigger by each high/low threshold event		
PS_PERS	Set the amount of consecutive threshold crossing events necessary to trigger interrupt		13 : 12	0x0 (0b00)	1 time (default)		
				0x1 (0b01)	2 times		
				0x2 (0b10)	3 times		
				0x3 (0b11)	4 times		
PS_SMART_PERS	Enable / disable the smart persistence setting when the interrupt event is triggered		11	0x0 (0b0)	Disable (default)		
				0x1 (0b1)	Enable		
PS_SP_INT	Enable / disable the sunlight protection mode interrupt setting		10	0x0 (0b0)	Disable (default)		
				0x1 (0b1)	Enable		
PS_START_INT	After PS_SD disable, PS 1st detection Interrupt enable setting		9	0x0 (0b0)	Disable (default)		
				0x1 (0b1)	Enable		
PS_SD	PS shutdown setting		8	0x0 (0b0)	Disable		
				0x1 (0b1)	Enable (default)		

**TABLE 6 - REGISTER NAME: PS\_CONF2\_L**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
PS_WAIT							
<b>COMMAND CODE</b>				<b>0x01</b>			
Bit Name	Function		Bit	Value	Description		
PS_WAIT	PS wait time after PS detection		7 : 0	0 to 254	2.5 ms x (PS_WAIT + 1)		

**TABLE 7 - REGISTER NAME: PS\_CONF2\_H**

Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
Reserved				PS_IT			
COMMAND CODE					0x01		
Bit Name	Function		Bit	Value	Description		
Reserved	Reserved		15 : 12	0x0 (0b0000)	Should be kept default		
PS_IT	Set the integration time for one measurement		11 : 8	0x0 (0b0000)	12.5 $\mu$ s (default)		
				1 to 15	25 $\mu$ s x PS_IT		

**TABLE 8 - REGISTER NAME: PS\_CONF3\_L**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
Reserved				PS_CURRENT_EN	PS_CURRENT		
COMMAND CODE					0x02		
Bit Name	Function		Bit	Value	Description		
Reserved	Reserved		7 : 4	0x0 (0b0000)	Should be kept default		
PS_CURRENT_EN	VCSEL driver enable setting		3	0x0 (0b0)	Disable (default)		
				0x1 (0b1)	Enable		
PS_CURRENT	Set the VCSEL driving current		2 : 0	0x0 (0b000)	Reserved (default)		
				0x1 (0b001)	Reserved		
				0x2 (0b010)	8 mA		
				0x3 (0b011)	10 mA		
				0x4 (0b100)	12 mA		
				0x5 (0b101)	14 mA		
				0x6 (0b110)	16 mA		
				0x7 (0b111)	18 mA		

**TABLE 9 - REGISTER NAME: PS\_CONF3\_H**

Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
Reserved	PS_HG	PS_GAIN		Reserved	PD3_EN	PD2_EN	PD1_EN
COMMAND CODE					0x02		
Bit Name		Function		Bit	Value	Description	
Reserved		Reserved		15	0x0 (0b0)	Should be kept default	
PS_HG		Set the gain of the ADC		14	0x0 (0b0)	x1 gain (default)	
					0x1 (0b1)	x2 gain	
PS_GAIN		Set the gain of the ADC		13 : 12	0x0 (0b00)	x4 gain (default)	
					0x1 (0b01)	x2 gain	
					0x2 (0b10)	x1 gain	
					0x3 (0b11)	Reserved	
Reserved		Reserved		11	0x0 (0b0)	Should be kept default	
PD3_EN		PD3 enable setting		10	0x0 (0b0)	Disable (default)	
					0x1 (0b1)	Enable	
PD2_EN		PD2 enable setting		9	0x0 (0b0)	Disable (default)	
					0x1 (0b1)	Enable	
PD1_EN		PD1 enable setting		8	0x0 (0b0)	Disable (default)	
					0x1 (0b1)	Enable	

**TABLE 10 - REGISTER NAME: PS\_CONF4\_L**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
Reserved							
COMMAND CODE				0x03			
Bit Name	Function		Bit	Value	Description		
Reserved	Reserved		7 : 0	0x0 (0b00000000)	Should be kept default		

**TABLE 11 - REGISTER NAME: PS\_CONF4\_H**

Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
Reserved				PS_SC_LEVEL		PS_SC	Reserved
COMMAND CODE				0x03			
Bit Name	Function		Bit	Value	Description		
Reserved	Reserved		15 : 12	0xF (0b1111)	Should be kept default		
PS_SC_LEVEL	Sunlight cancellation level setting		11 : 10	0x0 (0b00)	Level 1 (default)		
				0x1 (0b01)	Level 2		
				0x2 (0b10)	Level 3		
				0x3 (0b11)	Level 4		
PS_SC	Enable / disable the sunlight cancellation		9	0x0 (0b0)	Disable (default)		
				0x1 (0b1)	Enable		
Reserved	Reserved		8	0x0 (0b0)	Should be kept default		

**TABLE 12 - REGISTER NAME: PS\_THDL**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
PS_THDL_L							
Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
PS_THDL_H							
COMMAND CODE				0x04			
Bit Name	Function		Bit	Value	Description		
PS_THDL_L	Set the low threshold interrupt value		7 : 0	0 to 65 535	Low byte		
PS_THDL_H			15 : 8		High byte		

**TABLE 13 - REGISTER NAME: PS\_THDH**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
PS_THDH_L							
Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
PS_THDH_H							
COMMAND CODE				0x05			
Bit Name	Function		Bit	Value	Description		
PS_THDH_L	Set the high threshold interrupt value		7 : 0	0 to 65 535	Low byte		
PS_THDH_H			15 : 8		High byte		

**TABLE 14 - REGISTER NAME: PS\_CANC**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
PS_CANC_L							
Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
Reserved				PS_CANC_H			
COMMAND CODE				0x06			
Bit Name	Function		Bit	Value	Description		
PS_CANC_L	Set the offset count cancellation value		7 : 0	0 to 4095	Low byte		
PS_CANC_H			11 : 8		High byte		
Reserved	Reserved		15 : 12	0x0 (0b0000)	Should be kept default		

**TABLE 15 - REGISTER NAME: PS\_CONF5**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
Reserved							
Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
Reserved							
COMMAND CODE				0x08			
Bit Name	Function		Bit	Value	Description		
Reserved	Reserved		7 : 4	0x0 (0b0000)	Must be set to "0xA (0b1010)"		
Reserved	Reserved		3 : 0	0x0 (0b0000)	Should be kept default		
Reserved	Reserved		15 : 8	0x0 (0b00000000)	Should be kept default		

**TABLE 16 - REGISTER NAME: PS\_DATA**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
PS_DATA_L							
Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
PS_DATA_H							
COMMAND CODE				0xF8			
Bit Name	Function		Bit	Value	Description		
PS_DATA_L	Read the proximity output data		7 : 0	0 to 65 535	Low byte		
PS_DATA_H			15 : 8		High byte		

**TABLE 17 - REGISTER NAME: INT\_FLAG**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
Reserved							
Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
Reserved				PS_START_FLAG	PS_SPFLAG	PS_IF_CLOSE	PS_IF_AWAY
COMMAND CODE				0xF9			
Bit Name	Function		Bit	Value	Description		
Reserved	Reserved		7 : 0	0x00 - 0xFF (0b00000000 - 0b11111111)	Should be kept default		
Reserved	Reserved		15 : 12	0x0 (0b0000)	Should be kept default		
PS_START_FLAG	PS finish 1 <sup>st</sup> detection after SD disable		11	0x0 (0b0)	No 1 <sup>st</sup> detection flag		
				0x1 (0b1)	Finish 1 <sup>st</sup> detection flag		
PS_SPFLAG	Read the sunlight protection mode interrupt event flag		10	0x0 (0b0)	No sunlight protection mode flag		
				0x1 (0b1)	Sunlight protection mode flag		
PS_IF_CLOSE	Read the high threshold crossing interrupt event flag		9	0x0 (0b0)	No high threshold crossing interrupt event flag		
				0x1 (0b1)	High threshold crossing interrupt event flag		
PS_IF_AWAY	Read the low threshold crossing interrupt event flag		8	0x0 (0b0)	No low threshold crossing interrupt event flag		
				0x1 (0b1)	Low threshold crossing interrupt event flag		

**TABLE 18 - REGISTER NAME: VCNL36829UM\_ID**

Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
VCNL36829UM_ID_L							
Bit 15	Bit 14	Bit 13	Bit 12	Bit 11	Bit 10	Bit 9	Bit 8
VCNL36829UM_ID_H							
COMMAND CODE				0xFA			
Bit Name	Function			Bit	Value	Description	
VCNL36829UM_ID_L	Read the device ID			7 : 0	0x29 (0b00101001)	Should be kept default	
				15 : 8	0x00 (0b00000000)	Device with a slave address of 0x60	
VCNL36829UM_ID_H					0x10 (0b00010000)	Device with a slave address of 0x51	


**PACKAGE INFORMATION** in millimeters


Fig. 16 - VCNL36829UM Package Dimensions




**RECOMMENDED LAYOUT PAD INFORMATION** in millimeters


Fig. 17 - VCNL36829UM PCB Layout Footprint

**RECOMMENDED INFRARED REFLOW**

Soldering conditions which are based on J-STD-020C

IR REFLOW PROFILE CONDITION			
PARAMETER	CONDITIONS	TEMPERATURE	TIME
Peak temperature		260 °C + 5 °C / - 5 °C (max.: 265 °C)	10 s
Preheat temperature range and timing		150 °C to 200 °C	60 s to 180 s
Timing within 5 °C to peak temperature		-	10 s to 30 s
Timing maintained above temperature / time		217 °C	60 s to 150 s
Timing from 25 °C to peak temperature		-	8 min (max.)
Ramp-up rate		3 °C/s (max.)	-
Ramp-down rate		6 °C/s (max.)	-

Recommend normal solder reflow is 235 °C to 265 °C





Fig. 18 - VCNL36829UM Solder Reflow Profile Chart



**TAPE PACKAGING INFORMATION** in millimeters





## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.